

Description: BNC male crimp dual ferrule for RG58/59

Part No: 27-9010

Application: For Cable RG58,RG59,RG59 PLENUM

Crimp Tool: 24-9960P

Impedance: 50 Ohms



Frequency Range: 0-4 GHz

Temperature Range: -55°C TO +85°C



Material: Body Brass Nickel plated
Contact Phos Bronze Gold plated
Insulator Delrin
Crimp Sleeve Brass Nickel plated
Coupling Nut Zinc Nickel plated

RoHS Compliance: Yes

Technical Detail: Refer to AIM-Cambridge Document P/N 27-0000



DIM OUTLINE

 <small>This PROPRIETARY Document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is not to be traced or copied without permission and is returnable upon demand.</small> <small>INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018.</small>	Model No.	27-9010-CUST	AIM-Cambridge		
	RoHS <input checked="" type="checkbox"/> (EU)2015/863 COMPLIANT	Cage Code	N/A	Title: BNC MALE CRIMP DUAL FERRULE FOR RG58/59	
	UNLESS OTHERWISE SPECIFIED UNITS: MM X ±.5 X ±.3 .XX ±.10 ANGLES ±.5°	3RD ANGLE PROJECTION		Drawing No.	Rev.
	Drawn by: JEAN.JIN	Date: 2009/03/11	Size A	27-9010-CUST	1
		DO NOT SCALE DRAWING	Workmanship Std: N/A	Sheet 1 of 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[27-9010](#)