




| TROMPETER<br>MODEL NO. | Ø"A" | Ø"B" |
|------------------------|------|------|
| CBBJR79                | .24  | .063 |
| CBBJR79A               | .34  | .070 |



TRB JACK INTERFACE  
PER MIL-STD-348  
FIGURE 201-2



CBBJR79 SHOWN


NOTES: UNLESS OTHERWISE SPECIFIED:

- MATERIAL & FINISH:
  - BODY: TIN PLATED BRASS
  - INSULATOR & DIELECTRIC: PTFE (TEFLON)
  - INTERMEDIATE CONTACT: GOLD PLATED BRASS
  - CENTER CONTACT: GOLD PLATED BERYLLIUM COPPER
  - MOUNTING HARDWARE: TIN PLATED COPPER ALLOY


- ELECTRICAL:
  - FREQUENCY (MAX): 500 MHz
  - IMPEDANCE: NON-CONSTANT

- PANEL NUT TORQUE (MAX): 35 INCH POUNDS

- PANEL THICKNESS (MAX): .125



RECOMMENDED  
PANEL CUTOUT



|  |  |                      |                                       |
|--|--|----------------------|---------------------------------------|
| <p>NOTICE: The information in this drawing is PROPRIETARY and must not be used without the permission of Cinch Connectivity Solutions. It may contain data whose export is restricted. Verify status prior to exporting.</p> <p>INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018</p> | <p>3RD ANGLE PROJECTION</p> <p>RoHS2 <input checked="" type="checkbox"/> 2015/863/EU</p> <p>UNLESS OTHERWISE SPECIFIED UNITS: INCH</p> <p>.XX ±.02<br/>.XXX ±.010<br/>ANGLES ±2°</p> | TROMPETER            |                                       |
|  |  | Title:               | TRB RIGHT ANGLE<br>CIRCUIT BOARD JACK |
|  |  | Model No.            | CBBJR79X                              |
|  |  | Size                 | A                                     |
|  |  | DO NOT SCALE DRAWING | Date: 9/15/2021                       |
|  |  | Sheet                | 1 OF 1                                |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[CBBJR79A](#)