




MODEL NO.	"A"	Ø"B"
CBBJR79TL	.24	.063
CBBJR79TLA	.34	.070





TRB INTERFACE
PER MIL-STD-348
FIGURE 201-2



CBBJR79TL SHOWN

NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIALS AND FINISH:
 - 1.1 BODY: TIN PLATED BRASS
 - 1.2 OUTER INSULATOR: PTFE (TEFLON)
 - 1.3 INTERMEDIATE CONTACT: GOLD PLATED BRASS
 - 1.4 DIELECTRIC: PTFE (TEFLON)
 - 1.5 CENTER CONTACT: GOLD PLATED BERYLLIUM COPPER
 - 1.6 MOUNTING HARDWARE: TIN PLATED COPPER ALLOY
2. ELECTRICAL:
 - 2.1 IMPEDANCE: NON-CONSTANT
 - 2.2 FREQUENCY (MAX): 500MHz
3. PANEL THICKNESS (MAX): .125
4. PANEL NUT TORQUE (MAX): 35 INCH POUNDS



<p>NOTICE: The information in this drawing is PROPRIETARY and must not be used without the permission of Cinch Connectivity Solutions. It may contain data whose export is restricted. Verify status prior to exporting.</p> <p>INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018</p>	<p>RoHS2 <input checked="" type="checkbox"/> 2015/863/EU</p> <p>UNLESS OTHERWISE SPECIFIED UNITS: INCH</p> <p>.XX ±.02 .XXX ±.005 ANGLES ±2°</p>	<p>TROMPETER</p>	
		<p>Title: TRB RIGHT ANGLE CIRCUIT BOARD JACK</p> <p>Model No. CBBJR79TL/A</p> <p>Size A DO NOT SCALE DRAWING Date: 10/18/2021 Sheet 1 OF 1</p>	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[CBBJR79TL](#)