

LDD3-1205

3W DIN Rail DC-DC Converter

The LDD family of DC/DC converters is an optimal response to the applications where compactness and high reliability are requested. All are isolated and offer a wide range of input voltages.

Simple but elegant look and ease of installation make them ideal for various industrial applications.



Key Features & Benefits

- Compact Design
- High Efficiency
- Plastic Enclosure, circuit breaker shape
- Overload 150%
- Up to 70°C Operating Temperature

Applications

- Industrial machine control
- Process control
- Energy management
- Remote control systems

1. MODEL SELECTION

MODEL	INPUT VOLTAGE	INPUT CURRENT	OUTPUT VOLTAGE	OUTPUT CURRENT
LDD3-1205	12 VDC (9 - 18 VDC)	0.6 A	5 VDC	0.6 A

2. INPUT SPECIFICATIONS

Technical parameters are typical, measured in laboratory environment at 25°C and 12 VDC, at nominal values, after minimum 5 minutes of operation.

PARAMETER	DESCRIPTION / CONDITION	SPECIFICATION
Input DC Voltage	Rated Operating	12 VDC 9 - 18 VDC
Input DC Current		0.6 A
Internal Protection Fuse	Not user replaceable	Fuse 1.25 AT / 250 VAC

3. OUTPUT SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION	SPECIFICATION
Output Power		3 W
Rated Voltage		5 VDC (± 3% max.)
Continuous Current		0.6 A
Overload Limit		0.85 A
Short Circuit Peak Current		1.1 A
Load Regulation		≤ 1%
Ripple & Noise ¹		≤ 30 mVpp
Hold up Time		≥ 10 ms
Protections	Overload, short circuit with hiccup mode	
Status Signals	Green LED = DC OK	
Parallel Connection	Possible for redundancy (with external ORing module)	
Efficiency		> 68%
Dissipated Power		< 1.4 W

¹ Ripple and Noise are measured with 20 MHz bandwidth, probe terminated with a 0.1µF MKP parallel capacitor.

NOTE: Power rating, losses, efficiency, ripple, thermal behaviour and start-up may change outside of the nominal rated input range. Contact factory for details.

4. ENVIRONMENTAL, EMC & SAFETY SPECIFICATIONS


PARAMETER	DESCRIPTION / CONDITION	SPECIFICATION
Temperature	Operating (Start-up type tested: - 40°C)* Storage	- 40°C to + 70°C - 40°C to + 80°C
Derating		0.08 W/°C over 60°C
Humidity	Non-condensing	5 - 95% RH
Life Time Expectancy	At 25°C ambient full load	211118 h (24.1 years)
Overvoltage Category		I (EN50178)
Pollution Degree		2 (IEC60664-1)
Protection Class		Class II
Isolation Voltage	Input to Output	1.5 kVDC

Safety Standards & Approvals	UL508 (reference) EN60950 (reference) EN50178 (reference)	
EMC Standards	Emission	EN55011 (CISPR11) EN55022 (CISPR22)
	Immunity	Class B
		Class B
		Level 3
		Level 3
		Level 4
Protection Degree	EN61000-4-2 EN61000-4-3 EN61000-4-4 EN61000-4-5 EN61000-4-11	Level 2
		Level 2
		IP20
		IP20
Vibration sinusoidal	IEC 60068-2-6	5-17.8 Hz: ± 1.6 mm; 17.8-500 Hz: 2g 2Hours / axis (X,Y,Z)
Shock	IEC 60068-2-27	30 g 6 ms, 20 g 11 ms; 3 bumps / direction, 18 bumps total

* Possible with load derating.

5. MECHANICAL SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION	SPECIFICATION
Weight		100 g
Dimensions		35 x 90 x 61.5 mm
Mounting Rail		IEC 60715/H15/TH35-7.5(-15)
Connection Terminals	Screw type Header (24 - 12 AWG)	2.5 mm ²
Case Material	ABS, Flame retardant UL94 V-0	



INPUT CONNECTION	OUTPUT CONNECTION
+ = Positive DC (11)	+ = Positive DC (5)
- = Negative DC (12)	- = Negative DC (6)



Figure 1. Mechanical Drawing

For more information on these products consult: tech.support@psbel.com

NUCLEAR AND MEDICAL APPLICATIONS - Products are not designed or intended for use as critical components in life support systems, equipment used in hazardous environments, or nuclear control systems.

TECHNICAL REVISIONS - The appearance of products, including safety agency certifications pictured on labels, may change depending on the date manufactured. Specifications are subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bel Power Solutions:](#)

[LDD3-1205](#)