



1. Surface mount inductors designed for high speed switch mode applications requiring low inductance and high current.
2. 125°C operating temperature.
3. Inductance range from 0.05uH to 0.20uH.
3. High Current - up to 75 Amps.

ELECTRICAL CHARACTERISTICS

[illegible]

- (1). Inductance tolerance $\pm 20\%$ tested at 0.25V, 0ADC and 25°C
- (2). DCR measured at 25°C.
- (3). The DC current at which the inductance decreases by 30% from its initial value.
- (4). The DC current that results in a 40°C temperature rise from 25°C ambient.

[Click here for QUANTITY PER REEL & PACKING INFORMATION](#)

Custom versions available upon request.

© 2019 Signal Transformer –Specification subject to change without notice. 12.19

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bel:

[SCPS6450-R15](#) [SCPS6450-R20](#) [SCPS6450-R10](#) [SCPS6450-050](#)