

# Actuator

31-  
801.002



<https://eao.com/p/31-801.002>

Your product:

---



## 31-801.002 Actuator

### FRONT

Front dimension:	24 mm x 18 mm
Front form:	rectangular
Front bezel colour:	Black
Front bezel material:	Plastic

### MOUNTING

Design:	raised
Mounting cut-out:	Ø 16 mm
Mounting type:	Panel mounting

### ELECTRICAL CHARACTERISTICS

Operating voltage:	10 - 26 V DC
Switching voltage and switching current:	Typ. 10 VDC ... 26 VDC, ≤ 20mA

### MECHANICAL CHARACTERISTIC

Terminal:	Plug-in terminal, 2.8 x 0.5 mm
Tightening torque:	Fixing nut max. 0.5 Nm
Weight:	0.015 kg

### ACOUSTICAL CHARACTERISTICS

Tone frequency:	ca. 2.0 kHz
-----------------	-------------


## AMBIENT CONDITION

<b>IP Protection:</b>	IP40
<b>Operating temperature:</b>	– 25 °C ... + 55 °C
<b>Storage temperature:</b>	– 40 °C ... + 85 °C

## CERTIFICATE


<b>Approbations:</b>	DNV
<b>Conformities:</b>	CE, UKCA, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)
<b>REACH:</b>	REACH compliant
<b>RoHS:</b>	RoHS compliant

## OTHER


<b>Short Description:</b>	Actuator, Ø 16 mm, 24 mm x 18 mm, rectangular, Black, Plastic, Plug-in terminal, 2.8 x 0.5 mm
<b>Housing colour:</b>	Black
<b>Housing material:</b>	Plastic
<b>Buzzer system:</b>	Electronic non-contacting buzzer with IC oscillator
<b>Wiring diagrams:</b>	

A = Continuous tone  
B = Interval tone 2Hz

**Mounting cut-outs:**



**Dimension drawings:**



A = Solder terminal

B = Plug-in terminal 2.8 mm x 0.5 mm

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[31-801.002](#)