

# Actuator

45-  
2134.4F10.000



<https://eao.com/p/45-2134.4F10.000>

Your product:

---



## 45-2134.4F10.000

### Actuator

#### FRONT

**Front dimension:** Ø 38 mm

**Front form:** round

**Front bezel colour:** Sand grey

**Front bezel material:** Metal

#### MOUNTING

**Design:** flush

**Mounting cut-out:** Ø 30.5 mm

**Mounting type:** Panel mounting

#### OPERATING-/INDICATION PART

**Lens colour:** Black

**Lens material:** Plastic

**Lens illumination:** non illuminative

**Lens shape:** flush

**Lens optics:** opaque

#### MECHANICAL CHARACTERISTIC

**Switching action:** Maintained

**Switching system:** Slow-make switching element

**Mechanical lifetime:** 10 Mio. cycles of operation

**Operating frequency:** Max. 1 800/h

**Weight:** 0.072 kg

## AMBIENT CONDITION

**IP front protection:** IP66, IP67, IP69K

**Operating temperature:** – 25 °C ... + 70 °C

**Storage temperature:** – 40 °C ... + 80 °C

**Shock resistance:** According to IEC 60068-2-27: Sinusoidal half-wave 50 g / 11 ms

**Vibration resistance:** According to IEC 60068-2-6: 20 ... 500 Hz: 5 g

**Climate resistance:** During operation according to IEC 60721: 3K6, 3C3, 3S2, 3M6

## CERTIFICATE

**REACH:** REACH compliant

**RoHS:** RoHS compliant

## OTHER


**Short Description:** Actuator, Ø 30.5 mm, Ø 38 mm, flush, non illuminative, Black, Plastic, opaque, round, Sand grey, Metal, Maintained, IP66, IP67, IP69K

**Housing colour:** Silver


**Housing material:** Metal

**Hints:** Push to unlatch

**Wiring diagrams:**



**Dimension drawings:**



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[45-2134.4F10.000](#)