

MBC150 Series


Open Frame Power Supplies

Medical

The MBC150 Series of open-frame medical power supplies, with its wide universal input range 90-264 VAC, is available at 150 W of output power with forced-air cooling and a variety of single output voltages.

The MBC series is designed and approved to the latest Medical standards (EN/IEC 60601-1), providing 2 x MOPP (Means of Patient Protection) isolation for Class I & Class II applications.

These power supplies are ideal for medical, telecom, datacom, industrial equipment and other applications.



Key Features & Benefits

- 4 x 2 x 1.3 Inch Form Factor
- 150 W with Forced-Air Cooling
- Approved to EN/IEC 60601-1
- 12 V @ 0.5 A fan voltage auxiliary output
- High Efficiency > 86%
- Low conducted and radiated noise
- Light weight
- IEC Protection Class Options:
 - Class I: Earthing Tab J4 (no suffix)
 - Class II: No Earthing Tab (-2 suffix)
- Medical Safety Agency Approvals
- RoHS Compliant

Applications

- Diagnostic
- Drug Pump
- Monitoring
- Dialysis
- Home Health Care
- Portable Equipment

1. MODEL SELECTION

MODEL ¹	CONNECTOR	OUTPUT VOLTAGE	MAX LOAD ²		MIN LOAD	POWER
			CONVECTION	300 LFM		
MBC150-1005G	JST (Header)	5 VDC	16.0 A	16.0 A	0.0 A	80 W
MBC150-1T05G	Screw Terminal			20.0 A		100 W
MBC150-1012G	JST (Header)	12 VDC	8.33 A	12.5 A	0.0 A	150 W
MBC150-1T12G	Screw Terminal					
MBC150-1015G	JST (Header)	15 VDC	6.67 A	10.0 A	0.0 A	150 W
MBC150-1T15G	Screw Terminal					
MBC150-1024G	JST (Header)	24 VDC	4.17 A	6.25 A	0.0 A	150 W
MBC150-1T24G	Screw Terminal					
MBC150-1048G	JST (Header)	48 VDC	2.08 A	3.13 A	0.0 A	150 W
MBC150-1T48G	Screw Terminal					
COVER-150-XBC ³	Metal Cover Kit (accessory)					

¹ Class I products have an Earthing tab. For Class II version (without Earthing tab) add suffix -2 (e.g.: MBC150-1012G-2).

² Combined output power from V1 and VFAN should not exceed the total output power rating.

³ When used in Cover Kit, de-rate output power to 70 % under all operating conditions.

2. INPUT SPECIFICATIONS

Specifications are for nominal input voltage, 25°C unless otherwise stated.

PARAMETER	DESCRIPTION / CONDITION	SPECIFICATION
Input Voltage	Universal	90 – 264 VAC / 120 – 390 VDC
Input Frequency		47 – 63 Hz
Input Current	120 VAC: 230 VAC:	1.70 A max. 0.85 A max.
No Load Power		1.2 W
Inrush Current	120 VAC: 230 VAC:	35 A max. 65 A max.
Leakage Current	120 VAC: 230 VAC:	< 140 µA < 250 µA
No Load Power		1.2 W
Switching Frequency	PFC converter (variable) Resonant converter (variable)	35 – 250 kHz, 90 kHz typical 35 – 250 kHz, 90 kHz typical

3. OUTPUT SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION	SPECIFICATION
Output Voltage	Refer to Model Selection table	5 V to 48 V
Output Power ⁴	Peak Power: 170 W for 2 s	150 W
Fan Output ⁵	@ 5 A	12 V
Efficiency	120 VAC: 230 VAC:	84% typical 86% typical
Hold Up Time	120 VAC: 230 VAC:	6 ms 10 ms
Power Factor	120 VAC: 230 VAC:	0.99 0.95
Line Regulation		± 0.5%
Load Regulation		± 2.0%
Transient Response	50 to 100% load change, 50 Hz, 50% duty cycle, 0.1 A / μ s	< 10%, recovery time < 5 ms
Ripple ⁶	All outputs	1.0 % max
Rise Time		< 100 ms
Set Point Accuracy	Main output	± 1%
Output Voltage Adjustment	V1	± 3 %
Over Current Protection		110% typical above rating
Over Voltage Protection	V1	110 to 150%
Short Circuit Protection	Short term, Automatic recovery	
Cooling	Convection 300 LFM	80 W (5 V model), 100 W (other models) 100 W (5 V model), 150 W (other models)

⁴ Derate output power linearly to 80% from 90 VAC to 80 VAC input.

⁵ Fan output voltage tolerance is +/-20 %. Peak current for fan output is 1 A.

⁶ Ripple is 2 % up to 20 % load and < 1 % above 20 % load. Ripple is peak to peak with 20 MHz bandwidth and 10 μ F (Electrolytic capacitor) in parallel with a 0.1 μ F capacitor at rated line voltage and load ranges.

4. EMC SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION	SPECIFICATION
Conducted Emissions	EN 55011-B, CISPR22-B, FCC PART15-B	Pass
Radiated Emissions	EN 55011 B	Pass
Input Current Harmonics	EN 61000-3-2	Class D
Voltage Fluctuation and Flicker	EN 61000-3-3	Pass
ESD Immunity	EN 61000-4-2	Level 4, Criterion A
Radiated Field Immunity	EN 61000-4-3	Level 3, Criterion A
Electrical Fast Transient Immunity	EN 61000-4-4	Level 3, Criterion A
Surge Immunity	EN 61000-4-5	Level 3, Criterion A
Conducted Immunity	EN 61000-4-6	Level 3, Criterion A
Magnetic Field Immunity	EN 61000-4-8	Level 4, Criterion A
Voltage Dips, Interruptions	EN 61000-4-11	Criterion A & B


5. SAFETY SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION	SPECIFICATION
Isolation Voltage	Input to Output:	Min. 5900 VDC
Safety Standards	EN 60601-1, IEC 60601-1 (ed.3), ANSI / AAMI ES 60601 - 1, CSA C22.2 No. 60601-1	
Agency Approvals	Nemko, UL, C-UL	
CE mark	Complies with LVD Directive	

6. ENVIRONMENTAL SPECIFICATIONS


PARAMETER	DESCRIPTION / CONDITION	SPECIFICATION
Operating Temperature ⁷	-20 to 0°C start-up is guaranteed	-20 to 70°C
Storage Temperature		-40 to 70°C
Humidity	Non Condensing	95%
Altitude	Operating: Non-Operating:	10,000 ft. 40,000 ft.
Reliability	MTBF according to Telcordia -SR332-Issue 3	2.4 million hours

⁷ Refer to derating curves



Convection load: 80 W up to 50 °C
De-rate above 50 °C @ 3.125% per °C

Forced air cooled load: 100W up to 50°C
De-rate above 50 °C @ 2.5% per °C



Convection load: 100 W up to 50 °C
De-rate above 50 °C @ 2.5% per °C

Forced air cooled load : 150 W up to 50°C
De-rate above 50 °C @ 1.67% per °C

Figure 1. Derating Curves

7. CONNECTOR & PIN DESCRIPTION

CONNECTOR	PIN	DESCRIPTION / CONDITION		MANUFACTURER / PN
AC Input Connector	J1	Pin 1	AC Line	Molex: 26-60-4030 or equivalent
		Pin 2	AC Neutral	Mating: 09-50-3031; Pins: 08-50-0106
DC Output Connector	J2	Pin 1, 2	V1	Option 1: Tyco: 1776112-4 or equivalent
		Pin 3, 4	RTN	Mating: 13 AWG wire
				Option 2: JST: B4P-VH-B (LF) (SN) or B4P-VH (LF) (SN) or equivalent
				Mating: VHR-4M; Pins: SVH-41T-P1.1
Fan (Aux) Connector	J3	Pin 1	VFAN (12 V / 0.5 A)	Tyco: 640456-2 or equivalent
		Pin 2	RTN	Mating: 640440-2
Earth ⁸ (Spade Connector)	J4			Molex: 19705-4301 or equivalent
				Mating: 190030001

⁸ Class I product only

8. MECHANICAL SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION
Weight	150 g (0.33 lbs.)
Dimensions	101.6 x 50.8 x 33.6 mm (4.0 x 2.0 x 1.3 inch)




Figure 2. Mechanical Drawing

NOTES: In case the PCB is mounted in a metal enclosure, using metal hardware ensure the following:

- 1 Stand off, used to mount PCB has OD of 5.4 mm max.
- 2 Screws, used to fix PCB on stand off, have head dia of 6.0 mm max.
- 3 Washer, if used, to have dia of 6.5 mm max.




Figure 3. Mechanical Drawing with Cover Kit

For more information on these products consult: tech.support@psbel.com

NUCLEAR AND MEDICAL APPLICATIONS - Products are not designed or intended for use as critical components in life support systems, equipment used in hazardous environments, or nuclear control systems.

TECHNICAL REVISIONS - The appearance of products, including safety agency certifications pictured on labels, may change depending on the date manufactured. Specifications are subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bel Power Solutions:

[MBC150-1T05G](#) [MBC150-1T12G](#) [MBC150-1T24G](#) [MBC150-1T48G](#) [MBC150-1024G](#) [MBC150-1015G](#) [MBC150-1048G](#) [MBC150-1012G](#) [MBC150-1005G](#) [MBC150-1T15G](#)