



MBS601 Series

600 W AC-DC Power Supplies

Sealed IP66/67/68



The MBS601 Series of AC-DC power supplies provides up to 600 W of regulated output power through a wide input voltage range 85 – 264 VAC in a single output of 24 VDC or 48 VDC.

The MBS601 Series comes in a 4.92 x 9.86 x 2.36 inch form factor with a full set of protection features.

The MBS601 Series is available in an aluminium extruded chassis having fins for an optimal heat dispersion via natural convection. The input / output connections are fixed to the chassis through water tight glands, which combined with the sealed enclosure, give the power supply an IP66/67/68 ingress protection grade.

The -SL option offers a 5 V_{DC} stand-by output and a set of control signals: +/- remote sense, remote On/Off (-PS_Inhibit), power good (PS_Ok), I-share (ISHARE1+V_SLOGIC).

The MBS601 Series complies with the latest edition of the IEC/EN 60601-1 safety standards for medical equipment requiring 2x MoPP protection grade and displays the CE Mark for the European Low Voltage Directive (LVD).

Key Features & Benefits

- Sealed enclosure, IP66/67/68 Ingress Protection grade
- High efficiency up to 94% (50% to 100% load)
- Low stand-by power consumption (< 0.35 W)
- Universal input voltage range 85 – 264 VAC
- Input inrush current limiting <30 A
- 800 W peak power (up to 10 s)
- Single 24, 48 VDC voltages
- Active PFC, EN61000-3-2 compliant (Class C, >25% load)
- Low earth / touch leakage current
- Over temperature, OV, OC and SC protections.
- Stand by +5 V, 1.5 A output.
- Remote On / Off signal
- Overall dimensions 125.0 x 250.5 x 60.0 mm (4.92 x 9.86 x 2.36 in)
- Medical safety approval to IEC 60601-1 3rd edition, 2xMoPP protection grade BF appliances compatible IEC 60601-1-2 4th edition EMC compliant

Applications

- Clinical Analysers
- Dental units / chairs
- MRI / Full Body TC Systems
- Medical Diagnostic & Imaging Systems

1. MODEL SELECTION

MODEL NUMBER	PACKAGE & COOLING	INPUT VOLTAGE RANGE [VAC]	NOM. OUTPUT VOLTAGE [VDC]	MAX. OUTPUT POWER [W]	MAX. OUTPUT CURRENT [A]	DIMENSIONS
MBS601-1T24	Sealed Chassis Natural Convection	85 - 305	24	600	25	125.0 x 250.5 x 60.0 mm 4.92 x 9.86 x 2.36 in
MBS601-1T24-SL	Sealed Chassis Natural Convection + Control Signals	85 - 305	24	600	25	
MBS601-1T48	Sealed Chassis Natural Convection	85 - 305	48	600	12.5	
MBS601-1T48-SL	Sealed Chassis Natural Convection + Control Signals	85 - 305	48	600	12.5	

2. INPUT SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION	MIN	NOM	MAX	UNIT
AC Input Voltage	MoPP grade	85	100-240	264	V _{RMS}
	MoOP grade	85	100-277	305	
	PS starts and operates at 85 V _{AC} at all load conditions				
DC Input Voltage	Built in fuses has been safety certified up to 250 V _{DC} . Operating the MBS601 above that limit up to 300 V _{DC} does require an external fuse protection.	170	-	300	V _{DC}
Input Frequency	440 Hz with reduced PFC and output power rating. Consult factory for details.	47	50/60	63	Hz
Input Current	RMS at 180 V _{AC} , maximum load, 50 / 60 Hz	-	-	4.0	A
	RMS at 85 V _{AC} , maximum load, 50 / 60 Hz	-	-	8.5	
Inrush Current	Cold start, 25 °C ambient, full load				
	115 V _{AC}	-	-	20	A
	230 V _{AC}	-	-	30	
Fusing	High breaking, 10 A, 250 V on each AC lines.	-	-	10	A
Efficiency	At 115 V _{AC}	20% rated load	89	-	%
		50% rated load	93	-	
		100% rated load	92	-	
	At 230 / 264 V _{AC}	20% rated load	90	-	
		50% rated load	94	-	
		100% rated load	94	-	
Input Power Consumption	Power on, 115 V _{AC} , no load	-	-	5	W
	Power on, 230 V _{AC} , no load	-	-	4	
	Stand by, 115, 230 V _{AC} , no load	-	-	0.35	
Power Factor	From 50 to 100% of rated load, 230, 115 V _{AC} , 50 / 60 Hz input voltages.	0.90	-	-	-
THDi	From 50 to 100% rated load, 115, 230, 264 V _{AC} 50 / 60 Hz.	-	-	20	%
Harmonic Current Fluctuations and Flicker	Complies with EN 61000-3-2 at 230 V _{AC} , 50/60 Hz, Class A, D. Complies with EN 61000-3-2 Class C at 230 V _{AC} , 50/60 Hz, >150 W load. Complies with EN 61000-3-3 at nominal voltages and full load.				
Earth Leakage Current	Normal conditions				
	115 V _{RMS} , 60 Hz	-	170	-	μA
	230 V _{RMS} , 50 Hz	-	290	-	
	264 V _{RMS} , 60 Hz (worst case)	-	-	460	

3. OUTPUT SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION	MIN	NOM	MAX	UNIT
V1 Output Voltages	±0.5% set point accuracy RS+ closed on +V1, RS- closed on V1 RTN, at 20% load (option SL).	-	24 48	-	V
V1 Output Power Rating *	Convection cooling (Refer to the de-rating curves below) Peak (less than 10 s, after P_OK high)			600 800	W
V1 Output Current *	V1: 24 V _{DC} V1: 48 V _{DC}			25.0 12.5	A
V1 Voltage Adjustment Range	Manually by push up and down buttons	-	±5	-	%V1
V1 Line Regulation	V _{AC} : 85 – 264 V _{RMS}	-	-	±0.1	%V1
V1 Load-Line-Cross Regulation	V _{AC} : 85 – 264 V _{RMS} ; I ₁ : 0 – 100%	-	-	±2	%V1
V1 Ripple and Noise	Rated load, Peak-to-peak, 20 MHz BW. (100 nF ceramic, 10 µF tantalum at load)	-	-	1	%V1
Transient Response: V1, 5V _{SB} Voltage Deviation	25% load changes at 1 A/µs 24 V at 1000 µF load / I _{OUT} > 2.5 A 48 V at 560 µF load / I _{OUT} > 1.25 A 5 V _{SB} at 560 µF load / I _{OUT} > 0.1 A	-	-	±5	%V1 %V _{SB}
V1 Start-up Rise Time	85 < V _{IN} < 264, any load conditions.	10	-	100	ms
V1 Hold-up Time	At nominal V _{IN} , full load	16	-	-	ms
V1 Current Sharing Accuracy	Two units in parallel at I ₁ rated load. VS-Logic and I-Share signals connected together. RS+, RS- signals connected together and to the load	45.5	-	54.5	%I ₁
Start-up Delay	V1 in regulation after de-asserting PS_Inhibit V1 in regulation after AC is applied (worst case: 85 V _{AC}) 5V _{SB} in regulation after AC is applied (worst case: 85 V _{AC})	- - -	- - -	450 2050 1500	ms
Turn-on Overshoot		- -	- -	10 10	%V1 %V _{SB}
Minimum Load	V1, 5V _{SB}	0	-	-	A
Maximum Load Capacitance	V1: 24 V _{DC} V1: 48 V _{DC}	- -	- -	16000 8000	µF
5 V _{SB} Output Voltage	±3% set point accuracy, 20% load.	-	5	-	V
5 V _{SB} Output Current		-	-	1.5	A
5 V _{SB} Load-Line-Cross Regulation	V _{AC} : 85 – 264 V _{RMS} ; I _{SB} : 0 – 100%	-	-	±5	%V _{SB}

* Rated currents and combined power are referred to 55 °C ambient and V_{AC} ≥ 180 V_{RMS}.




Figure 1. Mounting Orientation

3.1 OUTPUT POWER DE-RATING CURVES




Figure 2. Power Derating Curves of MBS601 Series V1 P_{OUT} to T_{AMB}

Note: The de-rating curves are effective regardless mounting orientation


4. SIGNALS, CONTROLS & TIMING SPECIFICATIONS

Base signals and controls are accessible from signal connector P204.


SIGNAL	DESCRIPTION / CONDITION	MIN	NOM	MAX	UNIT
-PS_Inhibit	Active low. Input low voltage	0	-	1.5	V
	Input high voltage ($I_{IN}=300\ \mu\text{A}$)	3.5	-	5.5	V
	V1 disabled when -PS_Inhibit is pulled low				
	5V _{SB} not affected by -PS_Inhibit				
P_OK*	V1 enabled when -PS_Inhibit is floating or high				
	Logic level low (<10 mA sinking)	-	-	0.7	V
	Logic level high (100 μA sourcing)	2.4	-	5.5	V
	Low to high time after V1 in regulation	40	-	350	ms
5V _{SB} Output	Power down warning time	1	-	-	ms
	Active and in regulation after a $85 < V_{AC} < 264$ is applied	-	-	1500	ms
	5V _{SB} not affected by PS_Inhibit				

* When V1 is On, a P_OK low may indicate V1 under voltage condition. When two MBS601 operate in parallel, P_OK low in one unit indicates that it is not sharing the expected amount of current (current sharing fault). A 10 k Ω internal pull up to 5V_{SB} is used; do not add any other external pull up.

AC/DC INPUT OFF-TO-ON AND ON-TO-OFF TIMINGS



5V _{SB} On – V1 On	250 ms ≤ T1 ≤ 550 ms
V1 rise time	10 ms ≤ T2 ≤ 100 ms
5V _{SB} rise time	3 ms ≤ T10 ≤ 40 ms
V1 On – POWER_OK delay	200 ms ≤ T3 ≤ 350 ms
Power down warning	T4 ≥ 1 ms
V1 Off – 5V _{SB} Off	T5 ≥ 0.5 s (V1 load > 25 W)
AC Off – POWER_OK low	T6 ≥ 15 ms
AC_On – 5V _{SB} turn on time	T7 ≤ 1.5 s

PS_INHIBIT OFF-TO-ON AND ON-TO-OFF TIMINGS

V1 rise time	$10\text{ ms} \leq T2 \leq 100\text{ ms}$
V1 On – POWER_OK delay	$200\text{ ms} \leq T3 \leq 350\text{ ms}$
Power down warning	$T4 \geq 1\text{ ms}$
PS_Inhibit – POWER_OK low timing	$T8 \leq 2\text{ ms}$
PS_Inhibit – V1 On delay	$T9 \leq 450\text{ ms}$

5. PROTECTION SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION	MIN	NOM	MAX	UNIT
Input Under Voltage	Auto-recovering	58	75	82	V_{AC}
Input Fuse	High breaking, 10 A, 250 V on L and L1.	-	-	10	A
Over Current	At nominal input voltages				
	V1: Hiccup mode, auto-recovering (>10 s)	108	-	132	$\%I_{1\text{Rated}}$
	V1: Hiccup mode, auto-recovering (<10 s)	135	-	163	$\%I_{1\text{Rated}}$
Short Circuit	5 V _{SB} : Hiccup mode, auto-recovering:	1.6	-	3.6	A
	At nominal input voltages				
	V1: Hiccup mode, auto-recovering.	-	-	-	
Over Voltage	5V _{SB} : Hiccup mode, auto-recovering.				
	V1, Power shut down, latch off.	120	-	145	$\%V_{NOM}$
	5V _{SB} , Hiccup mode, auto-recovering.	-	-	150	
Over Temperature (on primary stage)	Shut down, latch off.	-	-	-	°C
Over Temperature (on secondary side)	Hiccup mode, auto-recovering.	-	-	-	°C
Isolation: Primary-to-Secondary	Reinforced (2x MoPP)	5660	-	-	V_{DC}
		4000	-	-	V_{AC}
Isolation: Input-to-Earth	Basic (1x MoPP)	2121	-	-	V_{DC}
	Production tested at 2121 V _{DC}	1500	-	-	V_{AC}
Isolation: V1-to-5V _{SB}	Basic	100	-	-	V_{AC}
Isolation: Output-to-Earth	Basic (1x MoPP)	1500	-	-	V_{AC}
Equipment Protection Class	Class I, compatible with BF (Body Floating) ME (Medical Equipment)				

6. ENVIRONMENTAL SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION	MIN	NOM	MAX	UNIT
Operating Temperature Range	No de-rating up to 55°C, at $\geq 180 V_{AC}$	-30	-	55	°C
Operating Temperature Range with Derating	See derating curves and conditions in the Output Specifications section	-	-	70	°C
Storage Temperature	As per IEC/EN 60721-3-1 Class 1K4	-40	-	85	°C
Transportation Temperature	As per IEC/EN 60721-3-2 Class 2K4				
Humidity	RH, Non-condensing Operating.	-	-	90	%
	Non-operating			95	%
Operating Altitude	Medical grade MoPP (100-240 V_{AC} , 50/60 Hz)	-	-	4000	m
	Medical grade MoOP (100-277 V_{AC} , 50/60 Hz)	-	-	5000	m
Shock	EN 60068-2-27 Operating: Half sine, 30 g, 18 ms, 3 axes, 6x each (3 positive and 3 negative). Non-Operating: Half sine, 50 g, 11 ms, 3 axes, 6x each (3 positive and 3 negative).				
Vibration	EN 60068-2-64 Operating: Sine, 10 – 500 Hz, 1 g, 3 axes, 1 oct/min., 60 min. Random, 5 – 500 Hz, 0.02 g^2/Hz , 1 g_{RMS} , 3 axes, 30 min. Non-Operating: 5 – 500 Hz, 2.46 g_{RMS} (0.0122 g^2/Hz), 3 axes, 30 min.				
MTBF	Full Load, 40 °C ambient 80% Duty cycle, Telcordia SR-332 Issue 2	200000	-	-	Hours
Useful Life	Nominal V_{IN} , 80% load, 40 °C ambient (IPC9592)	-	10	-	Years

7. ELECTROMAGNETIC COMPATIBILITY (EMC) – EMISSIONS

PARAMETER	DESCRIPTION / CONDITION	STANDARD	PERFORMANCE CLASS
Conducted	115, 230, 277 V_{RMS} , Maximum load	EN 55011 (ISM) EN 60601-1-2 (Medical) FCC Part 15	B
Radiated	The “SL” variant compliance to the Class B is conditioned by the use of a common ground plane between the power supply and its load	EN 55011 (ISM) EN 60601-1-2 (Medical) FCC Part 15	B
Line Voltage Fluctuation & Flicker	At 20%, 50% and 100% maximum load Nominal input voltages	EN 61000-3-3	
Harmonic Current Emission	230 VAC input voltage, 50 / 60 Hz 230 VAC 50 / 60 Hz, >150 W load	EN 61000-3-2 EN 61000-3-2	A, D C

8. ELECTROMAGNETIC COMPATIBILITY (EMC) – IMMUNITY

PARAMETER	DESCRIPTION / CONDITION	STANDARD	TEST LEVEL	CRITERIA
	Reference standard for the medical version	EN 60601-1-2, 4 th edition		
ESD	15 kV air discharge, 8 kV contact, at any point of the system.	EN 61000-4-2	4	A
Radiated Field	10 V/m, 20-2700 MHz, 1 KHz, 80% AM.	EN 61000-4-3	3	A
Electric Fast Transient	± 2 kV on AC power port for 1 minute	EN 61000-4-4	3	A
Surge	± 2 kV line to line; ± 4 kV line to earth on AC power port	EN 61000-4-5	4	A
Conducted RF Immunity	10 V_{RMS} , 0.15-80 MHz, 1 kHz, 80% AM	EN 61000-4-6	3	A
Dips and Interruptions	200 – 277 V_{AC} :	Drop-out to 0% for 10 ms	EN61000-4-11	A
		Dip to 40% for 5 cycles (100 ms)	EN61000-4-11	A
		Dip to 70% for 25 cycles (500 ms)	EN61000-4-11	A
		Drop-out to 0% for 5 s	EN61000-4-11	B
	100 – 127 V_{AC} :	Drop-out to 0% for 10 ms	EN 61000-4-11	A
		Dip to 40% for 5 cycles (100 ms)	EN 61000-4-11	A (derate to 150 W)
		Dip to 70% for 25 cycles (500 ms)	EN 61000-4-11	A (derate to 400 W)
		Drop-out to 0% for 5 s	EN 61000-4-11	B

9. SAFETY AGENCIES APPROVALS

CERTIFICATION BODY	SAFETY STANDARDS	CATEGORY
CSA / UL	CSA C22.2 No.60601-1, ANSI/AAMI ES60601-1 3rd edition + A1 Including Risk Management Assessment	Medical
IEC IECEE CB Certification	IEC/EN 60601-1 3rd edition+A1 Including Risk Management Assessment	Medical
CE	Directive 93/42/CEE: Safety Requirement of the Medical Device Directive 2014/30/EU: Electromagnetic Compatibility (EMC) Directive 2011/65/EU: RoHS 2	Medical
	Designed to meet IEC/EN/UL/CSA 61010-1 2 nd edition	

10. MECHANICAL SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION
Weight	2770 g (6.11 lb) 2850 g (6.28 lb) – SL models
Overall Dimensions	125.0 x 250.5 x 60.0 mm (4.92 x 9.86 x 2.36 in)





Figure 3. Mechanical drawing


11. CONNECTIONS

INPUT CABLE




WIRE COLOR	FUNCTION
BLACK	Line
GREEN	PG
WHITE	Neutral

OUTPUT CABLE







WIRE COLOR	FUNCTION
RED	+V1
BLUE	V1 RTN

SIGNAL CABLE



WIRE COLOR	FUNCTION
BLACK	RTN
RED	+5 VSB
BROWN	RS-
GREEN	P_OK
YELLOW	- PSINHIBIT
GREY	VS_LOGIC
BLUE	I SHARE 1
WHITE	RS+



For more information on these products consult: tech.support@psbel.com

NUCLEAR AND MEDICAL APPLICATIONS - Products are not designed or intended for use as critical components in life support systems, equipment used in hazardous environments, or nuclear control systems.

TECHNICAL REVISIONS - The appearance of products, including safety agency certifications pictured on labels, may change depending on the date manufactured. Specifications are subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bel Power Solutions:

[MBS601-1T24](#) [MBS601-1T24-SL](#) [MBS601-1T48](#) [MBS601-1T48-SL](#)