


SMB Non-Magnetic RF Connectors


For Flexible Cable


Right Angle Crimp Type Plug - Captivated Contact





CABLE TYPE	GOLD PLATED	
RG-316/u, 188, 174, 179, 187	131-9403-101	














- Identify connector parts. (4 piece parts: crimp sleeve, body assembly, expansion cap and covering ring. Die cast body only.)
- Strip cable to dimensions shown. Do not nick braid or center conductor. A wire stripper of correct size is recommended for this step. Twist stranded center conductor into tight bundle and tin (optional). Slide crimp sleeve onto cable as shown.
- Flare braid and slide cable into body assembly making certain that the cable insulation bottoms on center contact. Solder center conductor to contact through the rear and side access ports. Use a minimum amount of solder for a good joint. .020 (0.51) diameter solder is recommended.
- 4. Arrange braid uniformly around crimp stem of body assembly. Slide crimp sleeve over braid and crimp securely using recommended crimp tool. Place expansion cap in access port and seat with a .125 (3.17) diameter flat punch. Snap cover ring over side access port.



SMB Non-Magnetic RF Connectors Specifications

INCHES (MILLIMETERS)
CUSTOMER DRAWINGS AVAILABLE UPON REQUEST

ELECTRICAL RATINGS Impedance: 50 ohms				
Frequency Range: 0-4 GHz				
VSWR: (f = GHz)	Straight	Right Angle		
	Cabled	Cabled		
RG-316	1.25 + .04	lf 1.35 + .04f		
Uncabled receptacles	N/A			
Working Voltage: (Vrms maximum)†				
Connectors for Cable Type	Sea Level	70K Feet		
RG-316, uncabled connectors	335	85		
Dielectric Withstanding Voltage: (VRMS minimum at sea level)†				
Connectors for RG-316, uncabled recept	tacles	1000		
Corona Level: (Volts minimum at 70,000 f	eet)†			
Connectors for RG-316				
Uncabled receptacles		N/A		
Insertion Loss: (dB maximum, tested at 1	.5 GHz)			
Straight cable connectors		0.30 dB		
Right angle cable connectors		0.60 dB		
Uncabled receptacles		N/A		
Insulation Resistance: 1000 megohms m				
Contact Resistance: (milliohms maximum	ı) <u>Initial</u> <u>A</u>	fter Environmental		
Center contact (straight cabled connectors				
and uncabled receptacles)		8.0		
Center contact (right angle cabled connected		16.0		
Outer contact (gold plated connectors)		1.5		
Braid to body (gold plated connectors)	1.0	N/A		

RF Leakage: (dB minimum tested at 2.5 GHz) Cable connectors Uncabled receptacles		
RF High Potential Withstanding Voltage: (Vrn Connectors for RG-316 Uncabled receptacles	ns minimum, tested at 4	and 7 MHz)† 700
Power Rating (Dummy Load): 0.5 watt @ +2:		
MECHANICAL RATINGS		
Engagement Design: MIL-STD-348, Series SN Engagement/Disengagment Force: 2 pounds		kimum axial
force Contact Retention: 4 lbs. min axial force (capt 1 inch-ounce min torque		
Cable Retention:	Axial Force*	Torque
Connectors for RG-316 *or cable breaking strength whichever is less. Durability: 500 cycles minimum	(pounds) 20	<u>(in-oz)</u> N/A
ENVIRONMENTAL RATINGS (Meets or exceed the applicable paragraph of Temperature Range: - 65°C to + 165°C Thermal Shock: MIL-STD-202, Method 101, Condition of Corrosion: MIL-STD-202, Method 101, Condition of Corrosion of Corr	ondition B	
Shock: MIL-STD-202, Method 213, Condition E Vibration: MIL-STD-202, Method 204, Condition	3	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cinch Connectivity Solutions: 131-9403-101