


# Switching element

61-8574.22



<https://eao.com/p/61-8574.22>

Your product:



# 61-8574.22

## Switching element

**ELECTRICAL CHARACTERISTICS**

|                                          |                                                                                                             |          |         |
|------------------------------------------|-------------------------------------------------------------------------------------------------------------|----------|---------|
| Contacts:                                | 1 NC / 1 NO                                                                                                 |          |         |
| Switching voltage and switching current: | Switch rating AC with silver contact or silver contact with gold plating                                    |          |         |
|                                          | Service category AC-15                                                                                      |          |         |
|                                          | according to EN IEC 60947-5-1                                                                               |          |         |
|                                          | Voltage                                                                                                     |          | 125 VAC |
|                                          | Current                                                                                                     |          | 2.5 A   |
|                                          | Switch rating DC with silver contact or silver contact with gold plating                                    |          |         |
|                                          | Service category DC-13                                                                                      |          |         |
|                                          | according to EN IEC 60947-5-1                                                                               |          |         |
|                                          | Voltage                                                                                                     |          | 250 VDC |
|                                          | Current                                                                                                     |          | 0.15 A  |
|                                          |                                                                                                             |          |         |
| Rated Operational Voltage Ue:            | 250 VAC/DC according to EN IEC 60947-1                                                                      |          |         |
| Rated impulse withstand voltage Uimp:    | 4 kV, according to EN/IEC 60947-5-1                                                                         |          |         |
| Rated insulation voltage Ui:             | 320 VAC, according to EN / IEC 60947-5-1                                                                    |          |         |
| Recommended minimum operational data:    | Voltage                                                                                                     | 5 VAC/DC |         |
|                                          | Current                                                                                                     | 10 mA    |         |
| Switching rating:                        | 250 V AC/DC @ A                                                                                             |          |         |
| Electrical lifetime:                     | ≥50 000 cycles of operation at 250VAC, 2A, cosφ 0.95,                                                       |          |         |
| Electric strength:                       | 2500 VAC, 50 Hz, 1 minute, as per DIN / IEC 60512-2 between all terminals and earth                         |          |         |
| Overvoltage category:                    | III, according to EN / IEC 60947-5-1                                                                        |          |         |
| Pollution degree:                        | 3, according to EN IEC 60947-1                                                                              |          |         |
| Protection class:                        | II, according to EN / IEC 61058-1                                                                           |          |         |
| Standards:                               | The switches comply with the “Standards for low-voltage switching devices” EN IEC 61058-1, EN IEC 60947-5-1 |          |         |
| Thermal current Ith:                     | 5 A                                                                                                         |          |         |

**MECHANICAL CHARATERISTIC**

|                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
|-----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Terminal:</b>            | Plug-in terminal, 2.8 x 0.5 mm                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| <b>Contact material:</b>    | Gold                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| <b>Switching system:</b>    | Snap-action switching element                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| <b>Switching system:</b>    | <p>Self-cleaning, double-break snap-action switching system with contact opening width 2mm x 0.5mm (switch with small contact opening width as per EN IEC 61058-1).</p> <p>The switching elements are optionally equipped with the following switching functions: One to three normally open (NO) or normally closed (NC), or any combination of NO and NC plus connections for T1 3/4 LED or lamp.</p> <p>The number of switching elements cannot exceed three. The switching elements provided for the 3-position switch actuators are equipped with max. 2 NC or 2 NO or any combination. The number of switching elements cannot exceed two.</p> |
| <b>Switching positions:</b> | 3 positions                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| <b>Wire cross section:</b>  | <p>1 wire flexible: 0.5 ... 0.75 mm<sup>2</sup></p> <p>1 wire super flexible: 0.5 mm<sup>2</sup></p> <p>1 wire rigid: 0.5 ... 1.5 mm<sup>2</sup></p> <p>2 wires rigid: 0.75 mm<sup>2</sup></p> <p>2 wires flexible: 0.5 mm<sup>2</sup></p>                                                                                                                                                                                                                                                                                                                                                                                                           |
| <b>Weight:</b>              | 0.008 kg                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |

## AMBIENT CONDITION

|                               |                                                                                                                                                                                                                                                                                                              |
|-------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Operating temperature:</b> | – 25 °C ... + 55 °C                                                                                                                                                                                                                                                                                          |
| <b>Storage temperature:</b>   | – 40 °C ... + 85 °C                                                                                                                                                                                                                                                                                          |
| <b>Shock resistance:</b>      | Max. 100 m / s <sup>2</sup> , pulse width, 3-axis (sinusoidal EN IEC 60068-2-27)                                                                                                                                                                                                                             |
| <b>Vibration resistance:</b>  | Max. 100 m / s <sup>2</sup> from 10 Hz ... 500 Hz, (sinusoidal EN IEC 60068-2-6)                                                                                                                                                                                                                             |
| <b>Climate resistance:</b>    | <p>Damp heat, cyclic: 96 hours, + 25 °C/97 %, + 55 °C/93 % relative humidity, as per EN IEC 60068-2-30</p> <p>Damp heat, steady: 56 days, + 40 °C/93 % relative humidity, according to EN IEC 60068-2-78</p> <p>Rapid change of temperature: 100 cycles, – 40 °C ... + 80 °C, as per EN / IEC 60068-2-14</p> |

## CERTIFICATE

|                      |                                                                                                                                                |
|----------------------|------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Approbations:</b> | CB (IEC 60947-5-1), CB (IEC 61058-1), CENELEC CCA-NTR (EN 60947-5-1), CQC, CSA, DNV, EAC, ENEC (EN 61058-1), NFF, SEV (EN / IEC 60947-5-1), UL |
| <b>Conformities:</b> | CE, UKCA, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)                                                                                          |
| <b>REACH:</b>        | REACH compliant                                                                                                                                |
| <b>RoHS:</b>         | RoHS compliant                                                                                                                                 |

## OTHER



|                           |                                                                                                                      |
|---------------------------|----------------------------------------------------------------------------------------------------------------------|
| <b>Short Description:</b> | Switching element, Snap-action switching element, 250 V AC/DC @ A, Gold, 1 NC / 1 NO, Plug-in terminal, 2.8 x 0.5 mm |
|---------------------------|----------------------------------------------------------------------------------------------------------------------|

**Material:**

Plastic, according to UL 94 V0

**Hints:**

With lamp terminal

**Wiring diagrams:****Component layouts:**

Where to Buy

|                                                                                   | Distributor        | Quantity in Stock |                                                                                                         |
|-----------------------------------------------------------------------------------|--------------------|-------------------|---------------------------------------------------------------------------------------------------------|
|  | Digi-Key           | 187 in stock      | <a href="#">Buy</a>  |
|  | Sager              | 36 in stock       | <a href="#">Buy</a>  |
|  | Distrelec          | 13 in stock       | <a href="#">Buy</a>  |
|  | Mouser Electronics | 9 in stock        | <a href="#">Buy</a>  |
|  | RS Americas        | 2 in stock        | <a href="#">Buy</a>  |

[Show more](#) 

Powered by [oemsecrets.com](https://oemsecrets.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[61-8574.22](#)