

## Specification Sheet

Part Number: 151-02737


One-piece ratchet closure allows for easy installation during pre- or final assembly.

Easy release feature simplifies quick adjustments and maintenance.

Low fire hazard PA666V0 material is designed specifically for rail applications.

Stainless steel mounting plate tolerates high torque and provides superior corrosion resistance against chemicals, salt spray and contact with dissimilar metals.

Straight, 180° mounting plate is ideal for applications requiring a flush mount set off from the mounting hole.



Ratchet P-Clamp, 0.76 - 1.42" Bundle Dia, 180° Short, 0.33" Hole Dia, PA666V0/SS304, Black, 160/ctn

Article Number	151-02737
Type	RCC180SM8SS
Color	Black (BK)
Quantity Per	bag

<b>Product Description</b>	The Ratchet P-Clamp family offers versatility when managing wires, cables and hoses. The robust design and durable materials make it ideal for heavy duty applications, both indoors and out. The one-piece adjustable clamp can be closed by hand to the desired diameter. The release feature provides easy and nondestructive removal of cables simply by using a flat-head screwdriver. This nondestructive release allows the clamp to be reused without removing or replacing any bolts or screws. Low fire hazard material is designed specifically for rail applications.
<b>Short Description</b>	Ratchet P-Clamp, 0.76 - 1.42" Bundle Dia, 180° Short, 0.33" Hole Dia, PA666V0/SS304, Black, 160/ctn
<b>Global Part Name</b>	RCC180SM8SS-PA666V0/SS304-BK
<b>Minimum Tensile Strength (Imperial)</b>	100.0
<b>Minimum Tensile Strength (Metric)</b>	445.0
<b>Length L (Imperial)</b>	6.15
<b>Length L (Metric)</b>	156.1
<b>Fixation Method</b>	Screw Mounting
<b>Variant</b>	Short
<b>Width W (Imperial)</b>	1.37
<b>Width W (Metric)</b>	34.9
<b>Bundle Diameter Min (Imperial)</b>	0.76
<b>Bundle Diameter Min (Metric)</b>	19.4

<b>Bundle Diameter Max (Imperial)</b>	1.42
<b>Bundle Diameter Max (Metric)</b>	36.0
<b>Mounting Hole Diameter D (Imperial)</b>	0.33
<b>Mounting Hole Diameter D (Metric)</b>	8.4 mm
<b>Stud Diameter (Metric)</b>	M8
<b>Mounting Hole Centers (Imperial)</b>	2.45
<b>Material</b>	Polyamide 6.6 + Polyamide 6 V0 (PA66/6V0) Stainless Steel (SS304)
<b>Material Shortcut</b>	SS304 PA666V0
<b>Flammability</b>	Low generation of toxic gases and corrosive acid UL 94 V-0 Halogen-free Limited fire hazard Low smoke generation
<b>Halogen Free</b>	Yes
<b>UV Resistant (Yes/No)</b>	Yes
<b>Operating Temperature</b>	-40°F to +248°F (-40°C to +120°C)
<b>Reach Compliant (Article 33)</b>	Yes
<b>ROHS Compliant</b>	Yes
<b>Certification/Specification</b>	EN [45545-2] ASTM E 162 ASTM E 662 ASTM 1354

<b>Package Quantity (Imperial)</b>	160
<b>Package Quantity (Metric)</b>	160
<b>Customs Number</b>	3926909988

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-02737](#)