

Specification Sheet

Part Number: 156-00953



Friction tab inside the fir tree allows the tie to sit in mount without falling out prior to installation.

Fir tree provides low insertion effort yet demonstrates high extraction resistance.

Disc feature prevents rattling in high-vibration applications and protects against debris ingress.

2-Piece Cable Tie/Fir Tree Mount, 5.8"L, Bundle Dia. 0.16"-1.97" , PA66HIRHSUV/PA66HS, Black, 500/pkg

Article Number	156-00953
Type	T30RFT4
Color	Black (BK)
Quantity Per	carton
Product Description	HellermannTyton's fir tree mounts provide a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. Fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold as an assembly with the cable tie.
Short Description	2-Piece Cable Tie/Fir Tree Mount, 5.8"L, Bundle Dia. 0.16"-1.97" , PA66HIRHSUV/PA66HS, Black, 500/pkg

Global Part Name	T30RFT4-PA66HIRHSUV/PA66HS-BK
------------------	-------------------------------

Minimum Tensile Strength (Imperial)	30.0
-------------------------------------	------

Minimum Tensile Strength (Metric)	135
-----------------------------------	-----

Length L (Imperial)	6.0
---------------------	-----

Length L (Metric)	148.0
-------------------	-------

Fixation Method	Fir Tree
-----------------	----------

Identification Plate Position	none
-------------------------------	------

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.14
--------------------	------

Width W (Metric)	3.6
------------------	-----

Bundle Diameter Min (Imperial)	0.06
--------------------------------	------

Bundle Diameter Min (Metric)	1.5
------------------------------	-----

Bundle Diameter Max (Imperial)	1.4
--------------------------------	-----

Bundle Diameter Max (Metric)	35.0
------------------------------	------

Height H (Imperial)	0.48
---------------------	------

Height H (Metric)	11.8
Panel Thickness Min (Imperial)	0.039
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	3.0
Mounting Hole Diameter D (Imperial)	0.13 - 0.16
Mounting Hole Diameter D (Metric)	3.3 - 4.0 mm
Mounting Hole Diameter D Min (Imperial)	0.13
Mounting Hole Diameter D Max (Imperial)	0.16
Mounting Hole Diameter D Max (Metric)	4.0
Disc Diameter (Metric)	13
Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HS PA66HIRHSUV
Operating Temperature	-40°F to +257°F (-40°C to +125°C) -40°F to +221°F (-40°C to +105°C)

ROHS Compliant	Yes
-----------------------	-----

Package Quantity (Imperial)	500
------------------------------------	-----

Package Quantity (Metric)	500
----------------------------------	-----

Customs Number	3926909988
-----------------------	------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-00953](#)