

Specification Sheet

Part Number: 156-02283



Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement. Controlled flex and angled entry promote easy installation. Independent rotation allows for adjustable routing orientation.

MOC Clip to MOC Clip, 5 mm, 8 mm, PA66HIRHSUV, Black, 2000/ctn

Article Number	156-02283
Type	MOC5FMOC8M
Color	Black (BK)
Quantity Per	carton
Product Description	The MOC to MOC is a rotatable dual routing clip that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.
Short Description	MOC Clip to MOC Clip, 5 mm, 8 mm, PA66HIRHSUV, Black, 2000/ctn
Global Part Name	MOC5FMOC8M-PA66HIRHSUV-BK

Length L (Imperial)	1.10
----------------------------	------

Length L (Metric)	27.9
--------------------------	------

Variant	Clip to Clip
----------------	--------------

Bundle Diameter Min (Imperial)	0.16
---------------------------------------	------

Bundle Diameter Min (Metric)	4.0
-------------------------------------	-----

Bundle Diameter Max (Imperial)	0.22
---------------------------------------	------

Bundle Diameter Max (Metric)	5.5
-------------------------------------	-----

Height H (Imperial)	0.60
----------------------------	------

Height H (Metric)	15.2
--------------------------	------

Depth D (Imperial)	0.39
---------------------------	------

Depth D (Metric)	10.0
-------------------------	------

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
-----------------	--

Material Shortcut	PA66HIRHSUV
--------------------------	-------------

Flammability	UL 94 HB
---------------------	----------

Halogen Free	Yes
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-02283](#)