

EAO – Your Expert Partner for Human Machine Interfaces

82-6151.0114 - Indicator 22 mm stainless-steel

82-6151.0114 - Indicator 22 mm stainless-steel



Attention: The preview is based on a sample product. This can differ from your current configuration.

Mounting

Mounting cut-out
Design Ø 22,3 mm
flush

Front

Front dimension Ø 25 mm
Front shape round
Front ring shape flush
Front bezel material Stainless steel

Other Attributes

Operating voltage 24 V AC/DC
Weight 0,018 kg
Operation current 7 mA

Operating-/Indication part

Lens optics opaque
Lens material Stainless steel
Lens profile flat
Lens illumination illuminative
Lens colour Stainless steel

IP-Rating

Front protection IP65, IP67

Connection Method

Terminal Solder 2.8 x 0.5 mm

Illumination

Illumination Ring with red LED


Function

Indicator


EAO – Your Expert Partner for Human Machine Interfaces

82-6151.0114 - Indicator 22 mm stainless-steel


Dimensions




Mounting cut-outs



Wiring diagram



Component layout



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[82-6151.0114](#)