

Specification Sheet

Part Number: 157-00212



All-in-one bundling and fastening solution reduces costs and assembly time.

Variety of fir tree diameters and offset lengths address most offset applications.

High-spec materials and superior design deliver excellent performance and value.

1-Piece Cable Tie/Fir Tree Mount/Disc, 8.5"L, 12.5mm Offset, M6 Hole, PA46, Brown, 500/bg

Article Number	157-00212
----------------	-----------

Type	T50ROSFTM6SO12.5A
------	-------------------

Color	Brown (BN)
-------	------------

Quantity Per	carton
--------------	--------

Product Description	HellermannTyton's offset fir tree cable tie family creates an offset routing solution for our customers who are moving away from using tape. The offset branch creates a strong offset that reduces flexing and shifting of the bundle.
---------------------	---

Short Description	1-Piece Cable Tie/Fir Tree Mount/Disc, 8.5"L, 12.5mm Offset, M6 Hole, PA46, Brown, 500/bg
-------------------	---

Global Part Name	T50ROSFTM6SO12.5A-PA46-BN
------------------	---------------------------

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	8.5
Length L (Metric)	215.9
Offset Length (Imperial)	0.49
Offset Length (Metric)	12.5
Fixation Method	Fir tree for round holes
Identification Plate Position	none
Releasable Closure	No
Width W (Imperial)	0.19
Width W (Metric)	4.7
Bundle Diameter Min (Imperial)	0.08
Bundle Diameter Min (Metric)	2.0
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Height H (Imperial)	0.80

Height H (Metric)	21.40
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.26
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	5.5
Mounting Hole Diameter D (Imperial)	0.24
Mounting Hole Diameter D (Metric)	M8
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.24
Mounting Hole Diameter D Max (Metric)	6.0
Disc Diameter (Metric)	15.0
Disc Diameter (Imperial)	0.59

Material Polyamide 4.6 (PA46)

Material Shortcut PA46

Material Cable Tie Polyamide 4.6 (PA46)

UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +266°F (-40°C to +130°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[157-00212](#)