

Specification Sheet

Part Number: 161-63501



- Designed for applications that demand high flame retardant materials
- Unique open design allows for easy branch-offs at any point along the harness
- Overwrap formation provides abrasion protection and accommodates multiple bundle configurations
- Flexible construction and design is well suited for applications that involve movement and vibration
- Easy-to-use installation tool makes assembly fast and easy

Helawrap, HWPAV030, 1-1/4" (30mm) Dia., PA6V0, Black, 82ft/Reel

Article Number	161-63501
Type	HWPAV030
Color	Black (BK)
Quantity Per	reel
Product Description	The Helawrap cable management system is the flexible routing and protection solution for industrial, datacom and electrical applications. Helawrap easily wraps around cables with a "zipper-like" motion to protect against abrasion and mechanical stress caused by movement and bending. A handy application tool is included in every package for faster installations.

Short Description	Helawrap, HWPAV030, 1-1/4" (30mm) Dia., PA6V0, Black, 82ft/Reel
Global Part Name	HWPAV030-PA6V0-BK
Contents of pkg/kit	25m + tool
Length L (Imperial)	82.0
Length L (Metric)	25
Variant	Spiral Binding
Bundle Diameter Min (Imperial)	1.14
Bundle Diameter Min (Metric)	29
Bundle Diameter Max (Imperial)	1.26
Bundle Diameter Max (Metric)	32
Diameter D (Imperial)	1.25
Diameter D (Metric)	30.0
Nominal Diameter (Imperial)	1.19
Nominal Diameter (Metric)	30
Wall Thickness WT (Imperial)	0.050
Wall Thickness WT (Metric)	1.30

Material	Polyamide 6 V0 (PA6V0)
Material Shortcut	PA6V0
Flammability	UL 94 V-0
Halogen Free	Yes
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	EN [45545-2] UL UL 1441
UL Recognized (US)	Yes
Package Quantity (Imperial)	82.0
Package Quantity (Metric)	25
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[161-63501](#)