

EAO – Your Expert Partner for Human Machine Interfaces

10-4H21.1034P - Multi-LED Fail Safe

10-4H21.1034P - Multi-LED Fail Safe



Attention: The preview is based on a sample product. This can differ from your current configuration.

Other Attributes

Weight	0,002 kg
Operation current	2,2 mA -30%/+25%
Operating voltage	72 V AC/DC -30%/+25%

Illumination

Socket	BA9s
LED colour	Multi-LED yellow


Optics

Lumi. intensity	4 x 112 mcd
Dom. wavelength	589 nm


EAO – Your Expert Partner for Human Machine Interfaces

10-4H21.1034P - Multi-LED Fail Safe

Dimensions



Wiring diagram



Additional information

The max. overall length of the lamp may not exceed 25mm

Electrical and optical data are measured at 25 °C

The specified 72 and 110 VAC/VDC versions are built with a protection diode

Specified 72 and 110 VAC/VDC versions are built with a bridge rectifier

In case one LED fails, the other pair of still functioning LED's is working. The light output then is half in order to indicate the malfunction and shows this way the need for replacement

Luminosity and wave length variations caused by LED manufacturing processes may cause slight differences regarding the illumination

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

EAO:

[10-4H21.1034P](#)