

Specification Sheet

Part Number: 553-60007



Halogen free, for low smoke propagation, density and toxicity.
50 mm, 25 mm and 16 mm pre-cut marker options as standard, for ability to get multiple labels out of one tag.

Delivery in convenient storage boxes for protection.

ShrinkTrak Labels, 2-Sided, Unslit, Halogen Free, 1.97" x 1.69", Polyolefin, White, 1000/pkg

Article Number	553-60007
Type	TLFX254DS-1x50WH
Color	White (WH)
Quantity Per	pack

Product Description	ShrinkTrak DS is a halogen-free, double-sided heat shrinkable marker with a 2:1 shrink ratio. HellermannTyton's unique ladder-style design assists in removing markers off the carrier. The side slits have been designed to ensure the wire entry gap is as large as possible while remaining on the carrier strip, enabling the user to quickly insert wire and cable into the marker. For a complete labeling solution, ShrinkTrak DS can be printed using HellermannTyton's TagPrint® Pro professional label creation software and thermal transfer printers. For double-sided printing, HellermannTyton's TrakMark DS double-sided printer produces excellent results. Choose among multiple ribbon types to create a permanent print that resists most solvents when shrunk and applied.
Short Description	ShrinkTrak Labels, 2-Sided, Unslit, Halogen Free, 1.97" x 1.69", Polyolefin, White, 1000/pkg
Global Part Name	TLFX254DS-1x50WH-PO-X-WH
Length L (Imperial)	2.0
Length L (Metric)	50.0
Fixation Method	Others
Variant	Thin-Wall
Width W (Imperial)	2.0
Width W (Metric)	50.0
Thickness T (Imperial)	.0130
Thickness T (Metric)	.29
Height H (Imperial)	1.69

Height H (Metric)	43.0
Width of Liner (Metric)	88.9
Width of Liner (Imperial)	3.50
Outside Diameter Max (Imperial)	1.0
Outside Diameter Max (Metric)	25.4
Wall Thickness WT (Imperial)	0.036
Wall Thickness WT (Metric)	0.925
Material	Polyolefin, cross-linked (PO-X)
Material Shortcut	PO-X
US MIL SPEC	MIL-STD-202J SAE AS5942 3.4.1
Flammability	UL 224 Halogen-free Low smoke generation Low generation of toxic gases and corrosive acid Limited fire hazard
Halogen Free	Yes
Operating Temperature	-67°F to +221°F (-55°C to +105°C)
Reach Compliant (Article 33)	Yes

ROHS Compliant	Yes
Certification/Specification	ASTM E 162 DIN EN [45545-2] ASTM E 662 ASTM 1354
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[553-60007](#)