

Specification Sheet

Part Number: 553-60021



Halogen free, for low smoke propagation, density and toxicity.
50 mm, 25 mm and 16 mm pre-cut marker options as standard, for ability to get multiple labels out of one tag.

Delivery in convenient storage boxes for protection.

ShrinkTrak Labels, 2-Sided, 1-Slit, Halogen Free, .98" x .24", Polyolefin, White, 10,000/pkg

Article Number	553-60021
Type	TLFX32DS-2x25WH
Color	White (WH)
Quantity Per	pack

Product Description	ShrinkTrak DS is a halogen-free, double-sided heat shrinkable marker with a 2:1 shrink ratio. HellermannTyton's unique ladder-style design assists in removing markers off the carrier. The side slits have been designed to ensure the wire entry gap is as large as possible while remaining on the carrier strip, enabling the user to quickly insert wire and cable into the marker. For a complete labeling solution, ShrinkTrak DS can be printed using HellermannTyton's TagPrint® Pro professional label creation software and thermal transfer printers. For double-sided printing, HellermannTyton's TrakMark DS double-sided printer produces excellent results. Choose among multiple ribbon types to create a permanent print that resists most solvents when shrunk and applied.
Short Description	ShrinkTrak Labels, 2-Sided, 1-Slit, Halogen Free, .98" x .24", Polyolefin, White, 10,000/pkg
Global Part Name	TLFX32DS-2x25WH-PO-X-WH
Length L (Imperial)	1.0
Length L (Metric)	25.0
Fixation Method	Others
Variant	Thin-Wall
Width W (Imperial)	1.0
Width W (Metric)	25.0
Thickness T (Imperial)	.0130
Thickness T (Metric)	.29
Height H (Imperial)	0.23

Height H (Metric)	6.0
Width of Liner (Metric)	88.9
Width of Liner (Imperial)	3.50
Outside Diameter Max (Imperial)	0.12
Outside Diameter Max (Metric)	3.04
Wall Thickness WT (Imperial)	0.025
Wall Thickness WT (Metric)	0.635
Material	Polyolefin, cross-linked (PO-X)
Material Shortcut	PO-X
US MIL SPEC	SAE AS5942 3.4.1 MIL-STD-202J
Flammability	Low smoke generation Low generation of toxic gases and corrosive acid UL 224 Halogen-free Limited fire hazard
Halogen Free	Yes
Operating Temperature	-67°F to +221°F (-55°C to +105°C)
Reach Compliant (Article 33)	Yes

ROHS Compliant	Yes
Certification/Specification	ASTM E 662 ASTM E 162 ASTM 1354 DIN EN [45545-2]
Package Quantity (Imperial)	10000
Package Quantity (Metric)	10000
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[553-60021](#)