

Specification Sheet

Part Number: 558-00381



Continuous Colored Signal Panel labels come with yellow or orange stripes for easy printing of caution and warning labels. Continuous labels allow for designing and cutting labels to any length. Various widths are available so that a wide variety of sign sizes can be customized and produced on demand.

Adhesive Labels, Banded Color Continuous Roll, 3.0" x 250', UV Stable, Orange/White, 250 ft/roll

Article Number	558-00381
Type	HT3OE75250UV
Color	Orange (OG)
Quantity Per	roll
Product Description	Banded colored continuous rolls come with a stripe (band) for easy printing of warning labels. Available in different widths, these labels are designed for use with TagPrint® Pro software and HellermannTyton thermal transfer printers and can be customized, produced on demand and cut to any length.
Short Description	Adhesive Labels, Banded Color Continuous Roll, 3.0" x 250', UV Stable, Orange/White, 250 ft/roll

Global Part Name	HT3OE75250UV-840/281-OG
Technical Description	Banded Continuous Colored Signal Panel Roll, 3.0" X 250', UV Stable, Orange/White
Length L (Imperial)	250.0
Length L (Metric)	76.2
Variant	3.2mil, 50lb bleached kraft paper
Width W (Imperial)	3.0
Width W (Metric)	76.2
Thickness T (Metric)	64.0
Width of Liner (Metric)	76.2
Width of Liner (Imperial)	3.0
Material	Type 840/281, Polyester, UV-stabilized, clear polyester laminate (840/281)
Material Shortcut	840/281
Adhesive	Acrylic
Halogen Free	No

Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	CSA 66956 NEC2014 UL 969 ANSI Standard Z535.4 IFC 2012 NEC2011
UL Recognized (US)	Yes
Package Quantity (Imperial)	250
Package Quantity (Metric)	76.20
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[558-00381](#)