

Specification Sheet

Part Number: TAG55L-788



White polyester has a smooth surface, allowing for the highest resolution and print contrast.

The acrylic-based adhesive bonds to a wide variety of substrates and resists abrasion.

LaserTags are sheet fed for easy loading and fast printing.

Laser Tag Label, 5.5" x 4.25", 4 Per Sheet, PET, White, 1000/pkg

Article Number	594-55788
-----------------------	-----------

Type	TAG55L
-------------	--------

Color	White (WH)
--------------	------------

Quantity Per	pack
---------------------	------

Product Description	HellermannTyton white polyester labels are ideal for marking small electrical and electronic components, such as EPROMS', Integrated circuits, as well as the circuit board itself. Printed labels can withstand the soldering process and survive flux removal when the board is washed. HellermannTyton's 788 material is designed for use on flat surfaces and can also be used to identify connectors, buttons and just about anything requiring permanent, general purpose marking.
----------------------------	--

Short Description	Laser Tag Label, 5.5" x 4.25", 4 Per Sheet, PET, White, 1000/pkg
--------------------------	--

Global Part Name	TAG55L-788-WH
Width W (Imperial)	4.25
Width W (Metric)	107.9
Thickness T (Metric)	64.0
Height H (Imperial)	5.5
Height H (Metric)	139.7
Material	Type 788, Polyester (788)
Material Shortcut	788
Adhesive	Acrylic
Halogen Free	No
Adhesive Operating Temperature	-40°F to +199°F (-40°C to +93°C)
Operating Temperature	-40°F to +199°F (-40°C to +93°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes

Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3919905060
Labels per Column	2
Labels per Row	2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[TAG55L-788](#)