

Specification Sheet

Part Number: 596-00830

Placards made with UV stable inks and materials tested to last up to 25 years, even in direct sun exposure.

Aggressive adhesive ensures strong bond, even on powder coated surfaces.

Meets or exceeds NEC & IFC standards for printed text, character height, color and outdoor UV stability.

Optional Paint Shields provide additional protection for pre-printed and variable data placards.



Metal Solar Placard, WARNING GROUNDED..., Hand Writable, 3.75" x 2.0", AA, Orange/Silver, 5/pkg

Article Number	596-00830
Type	WGCMEM5
Color	Orange (OG)
Quantity Per	pack

Product Description	Metal Solar Placards offer maximum durability and ease in code compliance. Perfect for solar applications, a special process seals metallic particles under a clear anodized layer, which results in markings that have been tested and rated to last up to 25 years in outdoor use, even in direct sunlight. Markers are designed to meet the latest National Electrical Code (NEC 2014), with pre-printed warning or caution messaging that conforms to Article 690, as well as ANSI guidelines. Pre-printed placards may be more acceptable to some local Authorities Having Jurisdiction (AHJs), who may have a preference for placard-style identification.
Short Description	Metal Solar Placard, WARNING GROUNDED..., Hand Writable, 3.75" x 2.0", AA, Orange/Silver, 5/pkg
Global Part Name	WGCMEM5-AA-OG
Technical Description	3.75" X 2" Black text on an Orange/Silver Aluminum background that reads as: "WARNING ELECTRICAL SHOCK HAZARD. IF GROUND FAULT IS INDICATED, NORMALLY GROUNDED CONDUCTORS MAY BE UNGROUNDED AND ENERGIZED" - 5 per pack.
Local Order Number 2	Cross Reference = Paint Shield: 596-00793
Length L (Imperial)	3.75
Length L (Metric)	95.25
Width W (Imperial)	3.75
Width W (Metric)	95.25
Height H (Imperial)	2.0
Height H (Metric)	50.80

Material	Anodized Aluminum (AA)
Material Shortcut	AA
Adhesive	Ultra High Bond Permanent Acrylic Adhesive
Halogen Free	No
Adhesive Operating Temperature	from +50°F (from +10°C)
Operating Temperature	-40°F to +203°F (-40°C to +95°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	NEC2014
Warranty (US)	Yes
Package Quantity (Imperial)	5
Package Quantity (Metric)	5
Customs Number	7616995195
Labels per Column	1
Labels per Row	1

© 2022 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[596-00830](#)