

Specification Sheet

Part Number: 596-00867

Placards made with UV stable inks and materials tested to last up to 25 years, even in direct sun exposure.

Aggressive adhesive ensures strong bond, even on powder coated surfaces.

Meets or exceeds NEC & IFC standards for printed text, character height, color and outdoor UV stability.

Optional Paint Shields provide additional protection for pre-printed and variable data placards.

Metal Solar Placard, Blank Plate For Engraving, 4.0" x .75", AA, Black, 5/pkg

Article Number 596-00867

Type BLANK4X75

Color Black (BK)

Quantity Per pack

Product Description Variable data placards are used to mark areas specific to the individual installation, like voltage data. Made of the same durable material as pre-printed metal solar placards, engravable placards are designed to meet industry codes. Engravable placards have a black area that can be engraved using standard engraving equipment.

Short Description	Metal Solar Placard, Blank Plate For Engraving, 4.0" x .75", AA, Black, 5/pkg
Global Part Name	BLANK4X75-AA-BK
Technical Description	4.0" X 0.75" Black surface for engraving custom metal placards - 5 per pack.
Width W (Imperial)	4.0
Width W (Metric)	101.6
Height H (Imperial)	.75
Height H (Metric)	19.05
Material	Anodized Aluminum (AA)
Material Shortcut	AA
Adhesive	Ultra High Bond Permanent Acrylic Adhesive
Halogen Free	No
Adhesive Operating Temperature	from +50°F (from +10°C)
Operating Temperature	-40°F to +203°F (-40°C to +95°C)
Reach Compliant (Article 33)	Yes

RoHS Compliant Yes

Certification/Specification NEC2014 NEC2017

Warranty (US) Yes

Package Quantity (Imperial) 5

Package Quantity (Metric) 5

Customs Number 3919905060

Labels per Column 1

Labels per Row 1

© 2022 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[596-00867](#)