

Specification Sheet

Part Number: 596-00896

Made with UV-stable inks and materials for durability and weather resistance.
Reflective properties to meet applicable NEC code requirements for reflective identification.

Supplied with an aggressive adhesive to ensure long life.

Meets NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.

WARNING: PHOTOVOLTAIC
POWER SOURCE

Solar Label, Reflective, WARNING PHOTOVOLTAIC POWER SOURCE, 6.5" x 1.0", VL, Red, 500/roll

Article Number	596-00896
Type	PVPSR500
Color	Red (RD)
Quantity Per	roll
Product Description	HellermannTyton Pre-Printed Solar Installation Labels are designed to meet the requirements of the National Electrical Code (NEC) and the International Fire Code (IFC) as well as being acceptable to the Authority Having Jurisdiction (AHJ). Labels are made with durable UV-stable materials and adhesives that are designed to stick to both baked enamel and powder coat surfaces. Where applicable, labels are made using reflective materials for first responder safety. Some pre-printed labels are printable using a thermal transfer printer when variable voltage or series data must be printed and displayed.

Short Description	Solar Label, Reflective, WARNING PHOTOVOLTAIC POWER SOURCE, 6.5" x 1.0", VL, Red, 500/roll
Global Part Name	PVPSR500-505/281-RD
Technical Description	Pre-Printed Solar Label, Reflective, "WARNING: PHOTOVOLTAIC POWER SOURCE",6.5" X 1", Red
Local Order Number 2	Cross Reference = 10 per pack: 596-00676
Length L (Imperial)	6.5
Length L (Metric)	165.1
Width W (Imperial)	6.5
Width W (Metric)	165.1
Thickness T (Imperial)	0.0025
Thickness T (Metric)	64.0
Height H (Imperial)	1.0
Height H (Metric)	25.4
Width of Liner (Metric)	28.57
Width of Liner (Imperial)	1.125

Material	Type 505/281, UV-stabilized reflective vinyl with clear polyester laminate (505/281)
Material Shortcut	505/281
Adhesive	Acrylic
Halogen Free	No
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +174°F (-40°C to +79°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	NEC2011 UL 969 IFC 2012
Warranty (US)	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3919905060
Labels per Column	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[596-00896](#)