

Specification Sheet

Part Number: VFA14LCLCOM2

Pre-radiused zirconia ceramic ferrules for precision alignment. Industry standard ST, SC, MTRJ or LC connectors to suit specific applications.

Available in 1–5 meter lengths for a variety of applications.

Color coded for easy identification.

Individually quality tested for insertion and return loss.

Meet ANSI/TIA/EIA 568-B standards.

Product Image

Meet ANSI/TIA/EIA 604 (FOCIS) connector interface requirements.

FT LC - LC Duplex OM2 Fiber Assembly, 14M, Orange, 1/pkg

Article Number	904-00862
Type	VFA14LCLCOM2
Color	Orange (OG)
Quantity Per	box

Product Description

For fiber patching requirements, HellermannTyton offers fiber optic jumpers in various lengths with a wide variety of connector configurations. HellermannTyton offers fiber jumpers in two types—standard and high performance. Our standard jumpers combine quality with value. They meet all ANSI/TIA/EIA fiber optic cable requirements while allowing installers to maximize project budgets. In addition to meeting industry standards, HellermannTyton high performance jumpers have additional features designed for high performance applications. Our high performance jumpers meet Trade Agreement Act (TAA) requirements, making them suitable for use in General Services Administration (GSA) government contract projects.

Short Description	FT LC - LC Duplex OM2 Fiber Assembly, 14M, Orange, 1/pkg
Global Part Name	VFA14LCLCOM2-GF-OG
Technical Description	FT LC - LC Duplex OM2 Fiber Assembly, 14M, Orange
Length L (Imperial)	46.1
Length L (Metric)	14.0
Material	Glass Fiber (GF)
Material Shortcut	GF
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8544700000
Weight (Metric)	1155.8
Weight (Imperial)	4.7

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[VFA14LCLCOM2](#)