






Printed copy for information only/
Ausdruck nur zur Information

- Specification:

 - Performance requirements at equilibrium condition standard atmosphere 23 °C / 50% RH
 - Material: PA6.6
 - Bundle Ø/ Tensile force/
- Spezifikation:

 - Leistungsanforderung im Gleichgewichtszustand Normalklima 23 °C / 50% RH
 - Material: PA6.6
 - Buendel Ø: 1-35 mm
 - Schlaufenhaltekraft: min. 180 N

The manufacturing-related geometry changes (injection point, ejectors marks, etc.) allowed. Design of the details are left to suppliers discretion.

Durch das Herstellverfahren bedingte Geometriaeänderungen (Anspritzung, Auswerfermarkierungen, etc.) zulaessig. Einzelheiten der Ausfuehrung bleiben dem Hersteller ueberlassen.

Revision Level			Revision Record			The copyright of this drawing is reserved by HellermannTyton.	Drawn		Date (YYYY/MM/DD)	Title			
Drawing	State	Part	Material specification changed				I.Langeloh	2006/05/02					
03.2	Design Release	3					Changed		Date (YYYY/MM/DD)	Approved	Date (YYYY/MM/DD)	B.Schiwek	2006/05/02
A.Hiller		2020/03/12		All drawing revisions are stored in CAD PDM database				HellermannTyton www.HellermannTyton.com		Scale 1:1			
Approved		Date (YYYY/MM/DD)										Global Project Number NT 049-05	
B.Schiwek		2020/03/12								Format A2			
												Sheet 1 / 1	
										Drawing-No 14.1963			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[126-00426](#)