



Fixing Elements for Corrugated Tubing, with Fir Tree

CTC-Series


CTC clamps are used for example in the automotive, harness making, electrical industry and wherever corrugated tubing has to be quickly and firmly fixed.

Features and benefits

- CTC clamps for a variety of nominal diameters
- Fir tree foot part can be used for a variety of panel thicknesses
- Suitable for use within threaded holes
- Tube is guided accurately by clicking
- Axial slipping is prevented by the inside profile of the clamp



The tubing is clicked into the CTC clamp and is held firmly.



CTC-Series

CNCTC8FT6.5LG CTCFT6



CNCT8FT6.5LG Clamps

TYPE	Width (W)	Height (H)	Height (H2)	Nominal Ø	Disc Ø	Hole Ø (FH)	Panel Thickness	Material	Colour	Article-No.
CTC4.5FT6LG	8.0	16.1	11.1	4.5	16.0	6.5 - 7.0	0.8 - 6.0	PA66HIRHS	Black (BK)	151-14314
CTC7.5FT6LG	8.0	18.6	11.1	7.5	16.0	6.5 - 7.0	0.8 - 6.0	PA66HIRHS	Black (BK)	151-14313
CTC7.5FT9	8.0	19.9	12.2	7.5	23.0	8.7 - 9.0	3.0 - 5.0	PA66HIRHS	Black (BK)	155-31602
CTC10FT6	8.0	21.4	7.5	10.0	16.0	6.5 - 7.0	0.8 - 3.0	PA66HIRHS	Black (BK)	151-14311
CTC10FT6LG	8.0	21.4	11.1	10.0	16.0	6.5 - 7.0	0.8 - 6.0	PA66HIRHS	Black (BK)	151-00018
CTC10FT9	8.0	22.7	12.2	10.0	23.0	8.7 - 9.0	3.0 - 5.0	PA66HIRHS	Black (BK)	155-17801
CTC13FT6	8.0	25.2	7.5	13.0	16.0	6.5 - 7.0	0.8 - 3.0	PA66HIRHS	Black (BK)	151-14312
CTC13FT6LG	8.0	25.2	11.1	13.0	16.0	6.5 - 7.0	0.8 - 6.0	PA66HIRHS	Black (BK)	151-00019
CTC22FT9	8.0	37.7	12.2	22.0	23.0	8.7 - 9.0	3.0 - 5.0	PA66HIRHS	Black (BK)	155-25201
CTCL4.5FT6LG	10.0	14.3	10.7	4.5	16.0	6.5 - 7.0	0.8 - 6.0	PA66HIRHS	Black (BK)	151-01115

All dimensions in mm. Subject to technical changes.

TYPE	Width (W)	Height (H)	Height (H2)	Nominal Ø	Hole Ø (FH)	Panel Thickness	Material	Colour	Article-No.
CTCFT6	11.0	18.5	9.3	15.0	6.3 - 6.7	0.7 - 4.5	PA66HIRHS	Black (BK)	151-00783

All dimensions in mm. Subject to technical changes.

CNCTC-Series with cover

TYPE	Width (W)	Height (H)	Height (H2)	Nominal Ø	Hole Ø (FH)	Panel Thickness	Material	Colour	Article-No.
CNCTC8FT6.5LG	10.0	11.0	11.4	7.0	6.5 - 6.7	1.0 - 6.0	PA66HIRHS	Black (BK)	151-01038
	10.0	11.0	11.4	7.0	6.5 - 6.7	1.0 - 6.0	PA66HIRHS	Blue (BU)	151-01177
LC9FTOVAL	10.0	37.7	13.2	-	6.2 x 12.2	0.6 - 6.8	PA66HIRHS	Black (BK)	151-01880

All dimensions in mm. Subject to technical changes.

Material Specification Overview

MATERIAL	Material Shortcut	Operating Temperature	Colour**	Flammability	Material Properties*	Material Specifications
Aluminium-alloy	AL	-40 °C to +180 °C	Natural (NA)		- Corrosion resistant - Antimagnetic	RoHS
Chloroprene	CR	-20 °C to +80 °C	Black (BK)		- Weather-resistant - High yield strength	RoHS
Ethylene Tetrafluoroethylene (Tefzel®)	E/TFE	-80 °C to +170 °C	Blue (BU)	UL 94 V0	- Resistance to radioactivity - UV- resistant, not moisture sensitive - Good chemical resistance to: acids, bases, oxidizing agents	RoHS
Polyacetal	POM	-40 °C to +90 °C, (+110 °C, 500 h)	Natural (NA)	UL 94 HB	- Limited brittleness sensitivity - Flexible at low temperature - Not moisture sensitive - Robust on impacts	RoHS
Polyamide 11	PA11	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK)	UL 94 HB	- Bio-plastic, derived from vegetable oil - Strong impact resistance at low temperature - Very low moisture absorption - Weather-resistant - Good chemical resistance	HF RoHS
Polyamide 12	PA12	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK)	UL 94 HB	- Good chemical resistance to: acids, bases, oxidizing agents - UV- resistant	HF RoHS
Polyamide 4.6	PA46	-40 °C to +150 °C (5000 h), +195 °C (500 h)	Natural (NA), Grey (GY)	UL 94 V2	- Resistance to high temperatures - Very moisture sensitive - Low smoke sensitiv	HF LFH RoHS
Polyamide 6	PA6	-40 °C to +80 °C	Black (BK)	UL 94 V2	High yield strength	RoHS
Polyamide 6, high impact modified	PA6HIR	-40 °C to +80 °C	Black (BK)	UL 94 HB	- Limited brittleness sensitivity - Higher flexibility at low temperature	RoHS
Polyamide 6.6	PA66	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK), Natural (NA)	UL 94 V2	High yield strength	HF RoHS
Polyamide 6.6, glass-fibre reinforced	PA66GF13, PA66GF15	-40 °C to +105 °C	Black (BK)	UL 94 HB	Good resistance to: lubricants, vehicle fuel, salt water and a lot of solvent	HF RoHS
Polyamide 6.6, heat and UV stabilised	PA66HSW	-40 °C to +105 °C	Black (BK)	UL 94 V2	- High yield strength - Modified elevated max. temperature - UV-resistant	HF RoHS
Polyamide 6.6, heat stabilised	PA66HS	-40 °C to +105 °C	Black (BK), Natural (NA)	UL 94 V2	- High yield strength - Modified elevated max. temperature	HF RoHS
Polyamide 6.6, high impact modified	PA66HIR	-40 °C to +80 °C, (+105 °C, 500 h)	Black (BK)	UL 94 HB	- Limited brittleness sensitivity - Higher flexibility at low temperature	RoHS
Polyamide 6.6, high impact modified, heat and UV stabilised	PA66HIRHSW	-40 °C to +110 °C	Black (BK)	UL 94 HB	- Limited brittleness sensitivity - Higher flexibility at low temperature - Modified elevated max. temperature - High yield strength, UV-resistant	RoHS
Polyamide 6.6, high impact modified, heat stabilised	PA66HIRHS	-40 °C to +105 °C	Black (BK)	UL 94 HB	- Limited brittleness sensitivity - Higher flexibility at low temperature - Modified elevated max. temperature	RoHS
Polyamide 6.6, high impact modified, ScanBlack	PA66HIR(S)	-40 °C to +80 °C, (+105 °C, 500 h)	Black (BK)	UL 94 HB	- Limited brittleness sensitivity - Higher flexibility at low temperature	RoHS
Polyamide 6.6, UV-resistant	PA66W	-40 °C to +85 °C, (+105 °C, 500 h)	Black (BK)	UL 94 V2	- High yield strength - UV-resistant	HF RoHS

MATERIAL	Material Shortcut	Operating Temperature	Colour**	Flammability	Material Properties*	Material Specifications
Polyamide 6.6, with metal particles	PA66MP	-40 °C to +85 °C, (+105 °C, 500 h)	Blue (BU)	UL 94 HB	- High yield strength - Metal and X-Ray detectable	HF RoHS
Polyamide 6.6, with metal particles	PA66MP+	-40 °C to +85 °C	Blue (BU)	not flame retardant	- High yield strength - Metal and x-ray detectable	HF RoHS
Polyamide 6.6 V0	PA66V0	-40 °C to +85 °C	White (WH)	UL 94 V0	- High yield strength - Low smoke emission	HF LFH RoHS
Polyester	SP	-50 °C to +150 °C	Black (BK)	halogen free	- UV-resistant - Good chemical resistance to: most acids, alkalis and oils	HF LFH RoHS
Polyetheretherketone	PEEK	-55 °C to +240 °C	Beige (BGE)	UL 94 V0	- Resistance to radioactivity - Not moisture sensitive - Good chemical resistance to: acids, bases, oxidizing agents	HF LFH RoHS
Polyethylene	PE	-40 °C to +50 °C	Black (BK), Grey (GY)	UL 94 HB	- Low moisture absorption - Good chemical resistance to: most acids, alcohol and oils	HF RoHS
Polyolefin	PO	-40 °C to +90 °C	Black (BK)	UL 94 V0	Low smoke emissions	HF LFH RoHS
Polypropylene	PP	-40 °C to +115 °C	Black (BK), Natural (NA)	UL 94 HB	- Floats in water - Moderate yield strength - Good chemical resistance to: organic acids	HF RoHS
Polypropylene, Ethylene-Propylene-Dien-Terpolymere-rubber free of Nitrosamine	PP, EPDM	-20 °C to +95 °C	Black (BK)	UL 94 HB	- Good resistance to high temperatures - Good chemical and abrasion resistance	HF RoHS
Polypropylene with metal particles	PPMP	-40 °C to +115 °C	Blue (BU)	UL 94 HB	- Metal and X-Ray detectable - Heat resistant - Moderate yield strength - Good chemical resistance	RoHS
Polypropylene with metal particles	PPMP+	-40 °C to +85 °C	Blue (BU)	not flame retardant	- High yield strength - Metal and x-ray detectable	HF RoHS
Polyvinylchloride	PVC	-10 °C to +70 °C	Black (BK), Natural (NA)	UL 94 V0	- Low moisture absorption - Good chemical resistance to: acids, ethanol and oil	RoHS
Stainless Steel	SS304, SS316	-80 °C to +538 °C	Natural (NA)	non-burning	- Corrosion resistant - Antimagnetic - Weather resistant - Outstanding chemical resistance	HF LFH RoHS
Thermoplastic Polyurethane	TPU	-40 °C to +85 °C	Black (BK)	UL 94 HB	- High elastic - Good chemical resistance to: acids, bases and oxidizing agents	HF RoHS

Tefzel® is a registered trademark of DuPont. General linguistic usage for cable ties made from raw material E/TFE is Tefzel®-Tie. In addition to Tefzel® from DuPont HellermannTyton is also using equivalent E/TFE raw material from other suppliers. *These details are only rough guide values. They should not be regarded as a material specification and are no substitute for a suitability test. Please see our datasheets for further details.

**More colours on request.



N = Minimum Loop Tensile Strength for Cable Ties (Newton)

HF = Halogenfree

LFH = Limited Fire Hazard

RoHS = Restriction of Hazardous Substances

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-14313](#)