

Bundling and Securing

Self-Affixing Cable Ties

TECHNICAL DATA SHEET



Series 6 Solar Tie in PA12

Features and Benefits

- PA12 solar fasteners provide excellent durability in UV-, chemical- and moisture-sensitive environments.
- Can be pre-installed while modules are still on the pallet.
- Barrel and offset head design reduce potential for abrasion and wear.
- Design vetted and recommended by First Solar.



Material	Polyamide 12 (PA12)
Color	Black (BK)
Operating Temperature	-40°F to +248°F (-40°C to +120°C)



PART NO.	TYPE	Mounting Hole Dia. in. (mm)	Panel Thickness in. (mm)	Offset Length (L2) in. (mm)	Length (L) in. (mm)	Max. Bundle Diameter in. (mm)	Min. Tensile Strength lbs. (N)	Height (H) in. (mm)	Width (W) in. (mm)	Pkg. Qty.
157-00348	T50ROSFT5.6SO25R	0.2 (5.6)	0.1 - 0.2 (3.0 - 4.3)	1.0 (25.0)	9.4 (239.0)	2.0 (50.0)	50.0 (225.0)	0.8 (19.3)	0.2 (5.1)	500

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.

Contact HellermannTyton for more information.

Visit www.hellermann.tyton.com or call 800.537.1512

Disclaimer: The information in this datasheet is for informational purposes only. Information is subject to change at any time without notice.

HellermannTyton

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[157-00348](#)