



Carling Technologies®
/// NOW PART OF



Littelfuse®

LS-Series

Rocker Switches

PRODUCT WEBPAGE

request sample, configure part



The LS-Series Softspot illuminated rocker switches feature a three-color high brightness light sequence, from a single lamp. These switches are designed with a standard nylon snap-in bracket and "Drip-Dry" construction that protects the front panel from dust and moisture.

1

Pole

10-15

Amps

125-250

VAC Max

12-28

VDC Max

Typical Applications

• On/Off-Highway • Marine

Tech Specs

Dielectric Strength

1000V - live to dead metal parts

Electrical Life

50,000 cycles - maintained
25,000 cycles - momentary

Operating Temperature

32°F to 185°F (0°C to 85°C)

Ordering Scheme

Sample
Part Number

LS1522 - 13 - BL - BL - 012

Selection

1

2

3

4

5

1. SERIES

10A 250VAC, 15A 125VAC, 3/4 HP 125-250VAC, 15A 12-28VDC

Single Pole	Solder Lug	.250 Tab QC	Screw Terms	Wire Leads
On-None-Off	LS1510	LS1511	LS1514	LS1515
On-None-(Off)	LS1520	LS1521	LS1524	LS1525
(On)-None-Off	LS1530	LS1531	LS1534	LS1535
On-None-On	LS1540	LS1541	LS1544	LS1545
On-None-(On)	LS1550	LS1551	LS1554	LS1555
On-Off-On	LS1560	LS1561	LS1564	LS1565
On--Off-(On)	LS1570	LS1571	LS1574	LS1575
(On)-Off-(On)	LS1580	LS1581	LS1584	LS1585

2. LIGHTING SEQUENCE

	position 1	position 2	position 3				
01	red	red	red	31	green	clear	red
02	amber	amber	amber	32	green	clear	amber
03	green	green	green	33	green	clear	green
10	red	---	none	34	green	clear	blue
11	red	clear	red	35	green	clear	clear
12	red	clear	amber	40	blue	---	none
13	red	clear	green	41	blue	clear	red
14	red	clear	blue	42	blue	clear	amber
15	red	clear	clear	43	blue	clear	green
20	amber	---	none	44	blue	clear	blue
21	amber	clear	red	45	blue	clear	clear
22	amber	clear	amber	50	clear	---	none
23	amber	clear	green	51	clear	clear	red
24	amber	clear	blue	52	clear	clear	amber
25	amber	clear	clear	53	clear	clear	green
30	green	---	none	54	clear	clear	blue
				55	clear	clear	clear

3. ACTUATOR COLOR

BL Black WH White

4. BASE COLOR

BL Black WH White

5. LAMP VOLTAGE 2

incandescent	neon
6V 6 volt	125N 125 volt neon
12V 12 volt	250N 250 volt neon
18V 18 volt	
24V 24 volt	
28V 28 volt	


- 1 Independent lamp is standard. Dependent lamp with ON-OFF function (including momentary) is available with Lighting Sequences 10, 20, 30, 40 and 50. (No light in OFF position.)
- 2 Green and blue not recommended with 125 volt or 250 volt neon lamps.
- 3 Additional terminations available. Consult factory.
- 4 Custom colors available. Consult factory.
- () Indicates momentary function.

[Configure Complete Part Number >](#)

[Browse Standard Parts >](#)

Dimensional Specs

inches [millimeters]



SOLDER LUG	.250 TAB (Q.C.)	.187 TAB (Q.C.)
TERMINAL TYPE		
SCREW (ASSEMBLED)	WIRE LEAD	PRINTED CIRCUIT

* Angled corners are suggested for optimum fit.
Standard rectangular cutout is acceptable.

Authorized Sales Representatives and Distributors

Click on a region of the map below to find your local representatives and distributors or visit www.carlingtech.com/findarep.



About Carling

Founded in 1920, Carling Technologies is a leading manufacturer of electrical and electronic switches and assemblies, circuit breakers, electronic controls, power distribution units, and multiplexed power distribution systems. With six ISO9001 and IATF16949 registered manufacturing facilities and technical sales offices worldwide, Carling Technologies Sales, Service and Engineering teams do much more than manufacture electrical components, they engineer powerful solutions! To learn more about Carling please visit www.carlingtech.com/company-profile.

To view all of Carling's environmental, quality, health & safety certifications please visit www.carlingtech.com/environmental-certifications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Carling Technologies:

<u>LS1511-10-BL-BL-012</u>	<u>LS1511-10-BL-BL-125</u>	<u>LS1571-13-BL-BL-012</u>	<u>LS1511-20-BL-BL-125</u>	<u>LS1531-10-BL-BL-012</u>
<u>LS1541-23-BL-BL-250</u>	<u>LS1541-01-BL-BL-012</u>	<u>LS1513-10-BL-BL-125</u>	<u>LS1514-10-BL-BL-012</u>	<u>LS1514-10-BL-BL-125</u>
<u>LS1571-11-BL-BL-250</u>	<u>LS1584-11-BL-BL-012</u>	<u>LS1511-02-BL-BL-012</u>	<u>LS1581-01-BL-BL-012</u>	<u>LS1561-01-BL-BL-125</u>
<u>LS1561-02-BL-BL-012</u>	<u>LS1511-01-BL-BL-125</u>	<u>LS1511-20-BL-BL-012</u>	<u>LS1514-02-BL-BL-012</u>	<u>LS1510-01-BL-BL-012</u>