



Think Automation and beyond...

LUMIFA LED Lighting



IDEC CORPORATION



LIGHTING YOUR WAY

Our LUMIFA LEDs provide bright, long-lasting illumination for a variety of applications, from machine tools to chemical plants—and everything in between. Thanks to their rugged construction and range of IP ratings, they can withstand even the toughest industrial environment to bring you high-quality, uniform lighting using one-third of the power of traditional fluorescent bulbs.

Technical Features

QUALITY ILLUMINATION

With brightness levels up to 153 lumens/watt, our LEDs cast bright, uniform lighting onto target objects with minimal metal reflection, glare and shadows.

RUGGED

With their solid housing and IP ratings, our units can withstand exposure to dust, water, oil and metal shavings, making them suitable for harsh industrial environments and hazardous applications in oil and gas, mining—and more.

LOW MAINTENANCE

Swapping out a light is quick and easy. Our LEDs offer plug-and-play connection options, including quick-connect and pigtail M12 connections, as well as pre-wired models with removable plug-in or spring-clamp terminals.

VERSATILE

Models are available in a variety of sizes, brightness levels, colors and connections, while optional adjustable or fixed-angle mounting brackets make installation fast and easy. With widths as narrow as 25 mm, they can even be deployed in tight, hard-to-reach spaces.

LUMIFA LF2B

- Control Panels
- Industrial Equipment
- Manufacturing Lines & Work Stations



LF2B Series

The LF2B features a rugged, slim design for industrial applications and installations where space is limited. Its high illuminance, snap-in mounting brackets, range of input voltages, DC-battery compatibility and IP65 rating make this series ideal for a wide variety of lighting applications, from control panels to industrial equipment in wet environments.

- Slim size: 40 mm wide x 29 mm high
- Five lengths: 210, 330, 580, 830 and 1,080 mm
- Clear or white cover options
- 100-240V AC or 12/24V DC rated voltages
- Mounting brackets enable one-step installation process in tight spaces
- IP65-rated for use in wet environments



*UL applies for DC units only.

Optical Specifications

MODEL	LF2B-B (210 mm)		LF2B-C (330 mm)		LF2B-D (580 mm)		LF2B-E (830 mm)		LF2B-F (1,080 mm)	
COVER	Clear	White	Clear	White	Clear	White	Clear	White	Clear	White
Illumination Color	Cool White									
Color Temperature, K	6500									
Luminous Flux (typ.), lm	235	215	465	425	935	860	1380	1270	1860	1710
Reference Illuminance (typ.) at 0.5m directly below, lx	290	265	540	500	1065	980	1385	1275	1520	1400

LED modules and illumination units may vary in illumination colors and illuminance.

Part Number Structure (use for interpreting part numbers only)

LF2B - C 3 P - ATHWW2 - 1M			
LENGTH		COVER	RATED VOLTAGE
B: 210mm (8.27")	E: 830mm (32.68")	3: Clear	A: 100-240 VAC
C: 330mm (12.99")	F: 1,080mm (42.52")	4: White	B: 12V/24V DC
D: 580mm (22.83")			
			DC12V/24V Length
			B: (210mm)
			C: (330mm)
			D: (580mm) only

LUMIFA LF1D & LF2D

- Machine Tools
- Food & Beverage Processing Equipment
- Pharmaceutical & Chemical
- Automotive



LF1D & LF2D Series

Thanks to their rugged construction and high brightness levels up to 3,000 lumens, the LF1D and LF2D series are ideal for machine tools, food and beverage processing equipment and automotive, pharmaceutical and chemical applications. With their IP67, IP67F, IP67G and IP69K ratings, stainless-steel cover and diecast aluminum housing, they can even be used in the presence of high-pressure, high-temperature washdown.

MINI (LF1D-C)

- Compact size: 100 x 50 x 25 mm
- Single LED module design eliminates multiple shadows

SLIM & WIDE (LF1D/2D-EN, EH, FH)

- Durable polycarbonate or reinforced glass options
- No glare, shadows or strip effect
- M12 Quick Connect available
- Surface or recessed mount options

LONG (LF1D-H/J)

- Two lengths: 365 and 510 mm
- Extremely bright illumination—2,000 lumens (LF1D-H) or 3,000 lumens (LF1D-J)
- M12 Quick Disconnect option (Pig Tail)

Optical Specifications



MODEL	MINI	SLIM		WIDE	LONG	
	LF1D-C	LF1D/2D-EN	LF1D/2D-EH	LF1D/2D-FH	LF1D-H	LF1D-J
Illumination Color	Cool White				Neutral White	
Total Luminous Flux, lm	560	1530	1260	1540	2000	3000
Color Temperature, k	5700				4700	
Reference Illuminance at 1.0m, lx	180	1700	1800	1500	560	840

LED modules and illumination units may vary in color and brilliance. Luminous flux, color temperature, and illuminance values shown are typical.

Part Number Structure (use for interpreting part numbers only)

LF1D - EN 2F - 2W - A			
SHAPE 1: Surface Mount 2: Recessed Mount	SIZE (LED Arrangement) C: Mini 100mm (3.94") EN: Slim Model (48 LEDs x 1 Row) EH: Slim Model (10 LEDs x 1 Row) FH: Wide Model (7 LEDs x 2 Rows) H: Long 365mm (14.37") J: Long 510mm (20.08")	LENS TYPE DEGREE OF PROTECTION 2F: Reinforced glass 3G: Polycarbonate (EH, FH only) 21F: Reinforced Glass/ Diffused (EN only)	CABLE OPTIONS (see chart in datasheet) ILLUMINATION COLOR W: Cool White N: Neutral White

LUMIFA EF1A

- Hazardous Locations
- Oil & Gas
- Waste Water Treatment
- Painting & Chemical Plants



EF1A Series

Thanks to its rugged construction and Type 4X enclosure rating, the EF1A series is ideal for demanding applications in oil and gas, water treatment, chemical plants—and more. Units integrate heavy-duty aluminum housing with a reinforced glass lens, as well as UL-rated LED flood lights (Class 1, Zones 1 and 2). With their variety of mounting options, including adjustable, fixed angle or no mounting brackets, the EF1A can be installed virtually anywhere.


- Heavy-duty aluminum housing with reinforced glass lens
- Optional clear or translucent lenses
- Fixed or angle adjustable mounting bracket options
- Long-lasting, maintenance-free LEDs
- ON/OFF switch option

Optical Specifications



LENS TYPE	Clear		Diffused	
COLLECTING LENS (Optical Dispersion)	With	Without	With	Without
Illumination Color	Cool White			
Color Temperature (typ.), K	5700			
Total Luminous Flux (typ.), lm	960			
Reference Illuminance (typ.) at 1.0m directly below, lx	1100	450	205	175



Part Number Structure (use for interpreting part numbers only)





LUMIFA LED APPLICATIONS

- Food & beverage processing machines
- Packaging machines
- Semiconductor manufacturing equipment
- Machine tools
- Automotive manufacturing machines
- Oil & gas (other hazardous locations)
- Control panels
- Printing machines
- Production systems
- Test equipment
- Solar power equipment
- Cosmetic manufacturing equipment
- Chemical manufacturing equipment
- Show cases
- Foundries
- Photosensitive devices
- Advertising displays
- Assembly & robotics
- Work stations



Selection Guide

	LF1B-N					
Protection Class	IP65					
Cover Options	Clear/White					
Application List	Industrial Machines, Machine Tool, Plant Equipment, Test Equipment, Control Panel, Food Processing Machines, Cosmetic Plant, Chemical Plant, Show Cases, Semiconductor Manufacturing Equipment, Ic Foundry, Photosensitive Material, Darkroom Experiment, Advertising Display, Light Ornaments					
Illumination Color ¹	Cool White (6500K)	Warm White (3000K)	Blue (455nm)	Yellow (590nm)	Red (620nm)	Green (525nm)
Reference Illumination ²	LF1B-NA: 95lx LF1B-NF: 1350lx	LF1B-NA:90lx LF1B-NF: 1300lx	LF1B-NA: 10lx LF1B-NF: 80lx	LF1B-NA: 20lx LF1B-NF: 180lx		LF1B-NA: 30lx LF1B-NF: 300lx
Power Consumption	LF1B-NA: 1.5W LF1B-NB: 2.9W LF1B-NC: 4.4W LF1B-ND: 8.7W LF1B-NE: 13.0W LF1B-NF: 17.3W			LF1B-NA: 1.0W LF1B-NB: 2.0W LF1B-NC: 2.9W LF1B-ND: 5.8W LF1B-NE: 8.7W LF1B-NF: 11.6W		
Operating Voltage	24V DC					

	LF2B	
Protection Class	IP65	
Cover Options	Clear	White
Application List	Various Machines And Systems, Control Panel, Manufacturing Lines, Work Stations	
Illumination Color ¹	Cool White (6500K)	
Reference Illumination ²	LF2B-B: 290lx LF2B-C: 540lx LF2B-D: 1065lx LF2B-E: 1385lx LF2B-F: 1520lx	LF2B-B: 265lx LF2B-C: 500lx LF2B-D: 980lx LF2B-E: 1275lx LF2B-F: 1400lx
Power Consumption	LF2B-B: 2.6W LF2B-C: 4.9W LF2B-D: 10.6W	LF2B-B: 2.2W LF2B-C: 4.4W LF2B-D: 7.8W LF2B-E: 12.2W LF2B-F: 15.9W
Operating Voltage	12/24V DC	100 to 240V AC

1. K: Color Temperature (typ.), mm: Dominant Wavelength (typ.).

2. Directly below at 0.5m unless otherwise noted.

	LF1D-C	LF1D/2D Wide-angle and high luminance		LF1D-H	LF1D-J
Form Factor	Mini	Slim	Wide	Long	
Protection Class ³	IP67 / IP67F / IP69K	P67 (all models), IP67F/IP67G (see note 4), IP69K (LF1D only)		IP67 / IP67F / IP69K	
Application List	Machine Tools, Food and Beverage Processing Machines, Automotive, Chemical/Pharmaceutical, Production System, Test Equipment				
Illumination Color ¹	White (5700K)	White (5700K)		Neutral White (4700K) ³	
Reference Illumination ²	180lx	1800lx	1500lx	560lx	840lx
Power Consumption	4.6W	10W	12.5W	18.4W	27.6W
Operating Voltage	24V DC				

	EF1A	
Protection Class	Type 4X (IP67) without switch, Type 3S (IP65) with switch	
Application List	For Hazardous Locations: Oil, Gas And Mining Industries, Printing Factory, Gas Station, Chemical Complex Control Panel, Waste Water Treatment	
Illumination Color ¹	White (5700K)	
Reference Illumination ²	Clear glass surface: 1,100lx (condensing light), 205lx (diffused light) Translucent glass: 450lx (condensing light), 175lx (diffused light)	
Power Consumption	19W	17W
Operating Voltage	100 to 240V AC	24V DC

1. K: Color Temperature (typ.), mm: Dominant Wavelength (typ.).

2. Directly below at 0.5m unless otherwise noted.

3. Degree of protection: IEC60529 (IP67), JIS C 0920 (IP67F/IP67G), and DIN40050-9 (IP69K).

IP67F: LF1D-C/H/J, LF1D/LF2D-EN/EH, LF1D/LF2D-FH (reinforced glass), IP67G: LF1D/LF2D-EN, IP69K: LF1D only



LUMIFA.IDEC.COM



Think Automation and beyond...

800.262.4332

www.IDEC.com/usa

www.IDEC.com

USA

IDEC Corporation
Tel: (408) 747-0550
opencontact@IDEC.com

Canada

IDEC Canada Ltd.
Tel: (905) 890-8561
sales@ca.IDEC.com

Australia

IDEC Australia Pty. Ltd.
Tel: +61-3-8523-5900
sales@au.IDEC.com

Japan

IDEC Corporation
Tel: +81-6-6398-2527
marketing@IDEC.co.jp

Thailand

IDEC Asia (Thailand) Co., Ltd
Tel: +66-2-392-9765
sales@th.IDEC.com

Germany

APEM GmbH
Tel: +49-40-25 30 54-0
service@eu.IDEC.com

Hong Kong

IDEC Izumi (H.K.) Co., Ltd.
Tel: +852-2803-8989
info@hk.IDEC.com

China/Beijing

IDEC (Beijing) Corporation
Tel: +86-10-6581-6131
idec@cn.IDEC.com

China/Shanghai

IDEC (Shanghai) Corporation
Tel: +86-21-6135-1515
idec@cn.IDEC.com

China/Shenzhen

IDEC (Shenzhen) Corporation
Tel: +86-755-8356-2977
idec@cn.IDEC.com

Singapore

IDEC Asia Pte. Ltd.
Tel: +65-6746-1155
info@sg.IDEC.com

Taiwan

IDEC Taiwan Corporation
Tel: +886-2-2698-3929
service@tw.IDEC.com

©2018 IDEC Corporation. All Rights Reserved.
Catalog No. LF9Y-B100-5 8/18 5K

Specifications and other descriptions in this catalog are subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

IDEC:

[LF1D-EH3G-2W-401](#) [LF1D-E2F-2W-101](#) [LF1D-F2F-2W-101](#) [LF1D-FH3G-2W-300](#) [LF1D-F2F-2W-450](#) [LF1D-F5G-2W-200](#) [LF1D-FH3G-2W-450](#) [LF1D-E2F-2W-A](#) [LF1D-F5G-2W-400](#) [LF1D-J2F-2N-3B0](#) [LF1D-F5G-2W-451](#) [LF1D-F3G-2W-200](#) [LF1D-F3G-2W-201](#) [LF1D-J2F-2N-450](#) [LF1D-E3G-2W-400](#) [LF1D-F5G-2W-450](#) [LF1D-E2F-2W-201](#) [LF1D-E3G-2W-401](#) [LF1D-EH3G-2W-301](#) [LF1D-F5G-2W](#) [LF1D-E5G-2W-200](#) [LF1D-F5G-2W-A](#) [LF1D-E2F-2W-401](#) [LF1D-EH2F-2W-401](#) [LF1D-F3G-2W](#) [LF1D-F9F-2W-451](#) [LF1D-E3G-2W](#) [LF1D-E3G-2W-451](#) [LF1D-E2F-2W-450](#) [LF1D-EH2F-2W-350](#) [LF1D-F2F-2W-451](#) [LF1D-F3G-2W-450](#) [LF1D-C2F-2W-350](#) [LF1D-E9F-2W-401](#) [LF1D-EH2F-2W-451](#) [LF1D-E2F-2W-451](#) [LF1D-FH2F-2W-400](#) [LF1D-E5G-2W-101](#) [LF1D-FH2F-2W-300](#) [LF1D-E5G-2W-300](#) [LF1D-FH3G-2W-350](#) [LF1D-E9F-2W-350](#) [LF1D-EH2F-2W-450](#) [LF1D-EH3G-2W-451](#) [LF1D-FH2F-2W-200](#) [LF1D-FH3G-2W-451](#) [LF1D-FH3G-2W-400](#) [LF1D-E9F-2W-400](#) [LF1D-EH2F-2W-A](#) [LF1D-E9F-2W-300](#) [LF1D-H2F-2N-3B0](#) [LF1D-E5G-2W-451](#) [LF1D-F2F-2W-300](#) [LF1D-E9F-2W-101](#) [LF1D-FH3G-2W-101](#) [LF1D-EH3G-2W-A](#) [LF1D-EH2F-2W](#) [LF1D-F9F-2W-A](#) [LF1D-E3G-2W-200](#) [LF1D-F2F-2W-400](#) [LF1D-FH2F-2W-301](#) [LF1D-E3G-2W-301](#) [LF1D-FH2F-2W-450](#) [LF1D-EN2F-2W-56S01](#) [LF1D-F9F-2W-301](#) [LF1D-F9F-2W-101](#) [LF1D-EH2F-2W-300](#) [LF1D-E2F-2W-300](#) [LF1D-E9F-2W-A](#) [LF1D-E5G-2W](#) [LF1D-FH3G-2W-A](#) [LF1D-F5G-2W-301](#) [LF1D-E9F-2W-201](#) [LF1D-FH2F-2W-101](#) [LF1D-E3G-2W-300](#) [LF1D-EN21F-2W-451](#) [LF1D-EH3G-2W-200](#) [LF1D-F3G-2W-401](#) [LF1D-F3G-2W-350](#) [LF1D-C2F-2W-450](#) [LF1D-F3G-2W-A](#) [LF1D-E2F-2W-301](#) [LF1D-H2F-2N-350](#) [LF1D-F9F-2W-200](#) [LF1D-E9F-2W](#) [LF1D-EH2F-2W-200](#) [LF1D-F2F-2W-350](#) [LF1D-F9F-2W-401](#) [LF1D-E3G-2W-A](#) [LF1D-EH2F-2W-201](#) [LF1D-E5G-2W-400](#) [LF1D-F5G-2W-201](#) [LF1D-FH2F-2W-A](#) [LF1D-F3G-2W-101](#) [LF1D-EH3G-2W-350](#) [LF1D-EH3G-2W-450](#) [LF1D-J2F-2N-350](#) [LF1D-F3G-2W-300](#) [LF1D-EH3G-2W-400](#) [LF1D-F2F-2W](#)