




SERVO MOUNT/BALL BEARING
MODEL 1201

7/8" TO 3" DIAMETER SERVO MOUNT

WIREWOUND SINGLE-TURN PRECISION POTENTIOMETERS

SERVO MODEL	1201
ELECTRICAL	
Actual Electrical Travel	354° ± 2°
Normal Resistance Range	100Ω to 25K
Extended Resistance Range (1)	15Ω to 75K
Resistance Tolerance: Standard %	± 3
Best Practical %	± 1
Power Rating At 70°C, Derating To 0 At 125°C (Watts)	1.25
Linearity, Independent, Tolerance, Standard %	± 0.5
Best Practical %	± 0.2
Equivalent Noise Resistance (ENR) Max. (Ohms)	100
End Voltage Max. (% Of Total Applied Voltage)	
Insulation Resistance At 500 VDC, Min. (Megohms)	1000
Dielectric Withstanding Voltage (Volts RMS)	1000
Max. Applied Voltage (Volts DC)(2)	400
Temperature Coefficient Of Potentiometer, Max. % / °C	± .007
MECHANICAL	
Total Mechanical Travel	
Mechanical Life, Shaft Revolutions	2 million
Ganged Cups, Max. (Number)	6
Taps, Max., Excluding End Terminations	9
Moment Of Inertia, Per Cup (gm-cm ²)	0.2
Weight: Single Cup (oz.)	0.6
Each Additional Cup (oz.)	0.2
Torque, Max. Per Cup (oz.-in)	0.1
Pilot Diameter Runout, Max.	.0015
Lateral Runout, Max.	.0015
Shaft Runout, Max.	.001
Shaft Radial Play, Max.	.002
Shaft End Play, Max.	.004
Dimension For Each Additional Cup	.500 ± .002
ENVIRONMENTAL	
Temperature Range (°C) Standard	- 55 to + 125

- (1) All specifications listed apply to units with a total resistance within the normal resistance range. Higher or lower resistances may require some degradation of listed specifications because of resistance wire composition or size.
- (2) Not to exceed specified power rating.




THEORETICAL RESOLUTION—For typical coil characteristics by model number and resistance value, see Resolution Tables, page 52.

ALL MODELS are manufactured to meet or exceed applicable characteristics of MIL-R-12934. For MILITARY-APPROVED (QPL) Listings, see page 52.

TOLERANCES UNLESS OTHERWISE SPECIFIED:

FRACTIONAL: ± 1/64" DECIMAL: ± .005" ANGULAR: ± 1°

1201



BEI SENSORS

Tel: 805-968-0782 / 800-350-2727 | Fax: 805-968-3154 / 800-960-2726
7230 Hollister Ave., Goleta, CA 93117-2807 | www.beisensors.com

These commodities, technology or software if exported from the United States must be in accordance with the Bureau of Industry, and Security, Export Administration regulations. Diversion contrary to U.S law is prohibited.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Sensata:](#)

[1201R10KL.5](#)