

SSF215 SERIES

LONG REACH EXTERNAL MOUNT FLOAT SWITCH VIA 1/2"NPT



The SSF215 series of floatswitches are externally mounted horizontal switches. This series has an extended reach to provide a solution for extra thick tank walls or for mounting in welded on 1/2"NPT bosses.

The 1/2"NPT thread enables the switches to be fitted through the wall of a tank from the outside, so does not require access to the inside of the tank.

The floatswitch can be fitted to achieve either N/O (make on rise) or N/C (make on fall) switching action by simply rotating the switch through 180° .

Features

- Long reach for thick walled tanks and boss mounting
- Available with flying lead or M12 plug connection
- Float material SS 316, stem material SS 304
- External mount via 1/2"NPT thread, so does not require access to the inside of the tank for fitting.
- N/O or N/C switching action



Technical

Mounting Style	External	
Mounting Thread	1/2"NPT	
Float & Stem Material	316/304 grade SS	
Maximum Temperature	SSF215X100 180°C	
Maximum Pressure	10 bar	
Float SG	0.7	
Minimum Fluid SG	0.8	
Cable Length - Standard	100cm or plug	
Cable Size	17/0.10 - AWG22	
Cable Conductor Material	Tinned copper	
Cable Sheath Material	Teflon	
Cable Temperature Rating	200°C	

Tightening torque should be adequate to ensure a good seal.

Electrical

Contact Form		N/O (N/C)
Switching Power Max	VA	50
Switching Voltage AC Max	V	300
Switching Voltage DC Max	V	300
Switching Current Max	А	0.5

All ratings are for resistive load only.






	Stem Material	Float Material	Connection
SSF215X100	SS 304	SS 316	100cm Teflon AWG 22
SSF215XPM12	SS 304	SS 316	M12 Plug connection
SSF215XPL	SS 304	SS 316	DIN43650

Custom versions can be made for particular applications. Please contact Sensata with your requirements.

DIMENSIONS

All dimensions are in millimeters.



Made in the UK

Datasheets provided by Sensata Technologies, Inc., its subsidiaries and/or affiliates ("Sensata") are solely intended to assist third parties ("Buyers") who are developing systems that incorporate Sensata products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, valuation, and judgment in designing Buyer's systems and products. Sensata datasheets have been created using standard laboratory conditions and engineering practices. Sensata has not conducted any testing other than that specifically described in the published documentation for a particular datasheet. Sensata may make corrections, enhancements, improvements, and other changes to its datasheets or components without notice. Buyers are authorized to use Sensata datasheets with the Sensata component(s) identified in each particular datasheet. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER SENSATA INTELLECTUAL PROPERTY RIGHT, SGRANTED HEREIN. SENSATA DATASHEETS ARE PROVIDED "AS IS". SENSATA MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE DATASHEETS OR USE OF THE DATASHEETS, EXPRESS, IMPLIED, OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. SENSATA DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO SENSATA DATASHEETS OR USE THEREOF.

All products are sold subject to Sensata's terms and conditions of sale supplied at www.sensata.com. SENSATA ASSUMES NO LIABILITY FOR APPLICATIONS ASSISTANCE OR THE DESIGN OF BUYERS' PRODUCTS. BUYER ACKNOWLEDGES AND AGREES THAT IT IS SOLELY RESPONSIBLE FOR COMPLIANCE WITH ALL LEGAL, REGULATORY, AND SAFETY-RELATED REQUIREMENTS CONCERNING ITS PRODUCTS, AND ANY USE OF SENSATA COMPONENTS IN ITS APPLICATIONS, NOTWITHSTANDING ANY APPLICATIONS-RELATED INFORMATION OR SUPPORT THAT MAY BE PROVIDED BY SENSATA.

Mailing Address: Sensata Technologies, Inc., 529 Pleasant Street, Attleboro, MA 02703, USA

CONTACT US

+44 (0)1202 897969 support@sensata.com Cynergy3 Components Ltd. 7 Coham Road, Ferndown Industrial Estate, Wimborne, Dorset, BH21 7PE, United Kingdom Page 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sensata:

SSF215X100 SSF215XPL SSF215XPM12