

The history of revision change for the specification

Document	REV.	Modified date	Description
CYNVC-19Y-032	A0	2019.11.12	New approval
CYNVC-19Y-032	A1	2020.1.15	1. Nov., 2019 -> Jan., 2020 2. Year code 2019 = 9 -> 2020 = 0 3. Remove frequency: (1MHz) from Features
CYNVC-19Y-032	A2	2020.2.14	1. Jan., -> Feb., 2. Add 1R0, 1R5, 2R2 spec and curve.
CYNVC-19Y-032	A3	2020.4.7	1. Feb., -> Apr., 2. Add R47 spec and curve.
CYNVC-19Y-032	A4	2020.4.10	1. Add "AEC-Q200" logo 2. Add notice "AEC-Q200 qualified" in Features 3. Remove Notice "Preliminary specification"
CYNVC-19Y-032	A5	2021.6.10	1. Apr., 2020 -> Jun., 2021 2. Year code 2020 = 0 -> 2021 = 1 3. Update carrier size Width: 16.0 -> 12.0 ; F: 7.5 -> 5.5 (From sprocket hole to carrier hole) 4. Update Reel size A: 16.0 ± 0.5 -> 12.5 ± 0.5

Power Choke Coil VCMT053T MN52M type

AEC-Q200


■ Features

High performance (Isat) realized by metal dust core.
 Low profile : Thickness max. 3.0mm
 Low loss realized with low DCR
 Capable of corresponding high frequency
 Compliance with RoHS and Halogen Free
 AEC-Q200 qualified

■ Application

Automotive applications


■ Outline Dimensions



Code	Dimensions (mm)
L	5.45 ± 0.35
W	5.25 ± 0.20
T	2.8 ± 0.2
A1	1.02 ± 0.30
A'	1.5 ± 0.1
B	2.540 ± 0.254
B'	3.5 ± 0.2
H	$0 \sim +0.15$

■ Recommend Land Pattern Dimensions

The customer shall determine the land dimensions shown below after confirming and safety.



A	2.79
B	2.946
C	6.756

Unit : mm

■ Marking and Date Code

The point on the top surface represents winding direction of choke.

(1) Marking

The inductor is marked with a 3-digit code

Example -- $4.7\mu\text{H}$ → 4R7

(2) Date Code

X XX

(1) (2)

XXX

(3)

Where (1) Year Code

Ex : 2021 = 1


(2) Weekly Code

Serial number : 01 ~ 53

(3) Taping No.

Serial number : 001 ~ ZZZ

Upside of Chip



Specifications

Part Number	L0 ◇ Inductance (μH) @ (0A)	R _{dc} (mΩ) ◇		Heat Rating Current DC Amps. I _{dc} (A)		Saturation Current DC Amps. I _{sat} (A)		Rated voltage (V)
		Typical	Maximum	Typical	Maximum	Typical	Maximum	Maximum
VCMT053T-R33MN52M	0.33	4.5	5.0	16.7	15.0	11.2	9.6	50
VCMT053T-R47MN52M	0.47	6.9	7.9	12.4	11.2	14.0	12.0	50
VCMT053T-R68MN52M	0.68	8.6	9.74	11.3	10.2	11.7	10.0	50
VCMT053T-1R0MN52M	1.0	10.0	11.5	10.8	9.7	8.0	6.5	50
VCMT053T-1R5MN52M	1.5	15.4	17.7	8.2	7.4	7.1	5.9	50
VCMT053T-2R2MN52M	2.2	20.0	23.0	7.1	6.4	6.3	5.1	50
VCMT053T-3R3MN52M	3.3	33.0	38.0	5.5	5.0	5.5	4.7	50
VCMT053T-4R7MN52M	4.7	51.0	59.0	4.4	3.9	4.5	3.9	50
VCMT053T-6R8MN52M	6.8	80.0	92.0	3.5	3.1	3.5	3.0	50
VCMT053T-100MN52M	10.0	112.6	129.5	2.8	2.5	2.35	2.0	50
VCMT053T-150MN52M	15.0	170.0	196.0	2.4	2.2	2.2	1.9	50

◇ : Significant Characteristic

* : If you require another part number please contact with us.

** : Inductance Tolerance $\pm 20\%$

Note 1. : All test data is referenced to 25°C ambient.

Note 2. : Test Condition; 100KHz, 1.0Vrms

Note 3. : I_{dc} : DC current (A) that will cause an approximate ΔT of 40°C

Note 4. : I_{sat} : DC current (A) that will cause L0 to drop approximately 20%

Note 5. : Operating Temperature Range -55°C to +155°C

Note 6. : The part temperature (ambient + temp rise) should not exceed 155°C under the worst case operating conditions. Circuit design, component placement, PCB trace size and thickness, airflow and other cooling provision all affect the part temperature. Part temperature should be verified in the end application.

Note 7. : The rated current as listed is either the saturation current or the heating current depending on which value is lower.









Note 8. : Cleaning Process Note




(a) If this power choke is dipped in the cleaning agent, such as toluene, xylene, ketone, and ether system, there is a possibility that the performance decreases greatly

(b) The high power ultrasonic washing may damage the choke body.

(c) Please contact us if you need the cleaning via the above agents or ultrasonic washing.


Current Characteristic





■ Packaging


(1) Tape packaging dimensions




Dimensions Code (mm)				UNITS/REEL
A0	B0	K0	t	
5.75 ± 0.10	6.05 ± 0.10	3.6 ± 0.1	0.35 ± 0.05	2,000

(2) Tape Direction

The direction shall be seen from the top cover tape side.




(1) Reel dimensions



(2) Peel force of top cover tape


The peel speed shall be about 300 mm/minute.

The peel force of top cover tape shall be between 0.1 to 1.3N.



■ Reflow Profile

Power Choke Coil Type



(1) Reflow Soldering Method :

Reflow Soldering	Tp:255~260°C	Max.30 seconds (tp)
	217°C	60~150 seconds
Pre-Heat	150 ~ 200°C	60~120 seconds
Time 25°C to peak temperature	8 minutes max.	

(2) Soldering iron Method : 350 ± 5°C max.3 seconds

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delta Electronics:](#)

[VCMT053T-4R7MN52M](#)