



KE SERIES

HIGH PERFORMANCE IEC INLET FILTERS



INTRODUCTIONS

1. Applications for UL 544 & UL 2601 health care equipment.
2. Specially designed with ground choke providing most effective EMI suppression for high frequency noise (ranged 5-25MHz).
3. Bleeder resistor can be added with suffix "-R" on part numbers.
4. With optional 0.1uF X capacitor instead of 0.047uF.
5. With optional solder lug connection instead of fast on terminal.

COMPONENTS

PART NO.	L (mH)	Cx (uF)	Lg (uH)
03KEEG3DAM/03KEEW3DAM	3.1	0.047	100
03KEEG3EAM/03KEEW3EAM	3.1	0.1	
*08KEEG3DAM/08KEEW3DAM	0.8	0.047	
*08KEEG3EAM/08KEEW3EAM	0.8	0.1	
**10KEEG3DAM/10KEEW3DAM	0.4	0.047	
**10KEEG3EAM/10KEEW3EAM	0.4	0.1	

** UL, CSA & VDE approved to 9A 115/250VAC
* VDE approved to 6A 250V

MINIMUM INSERTION LOSS IN dB

COMMON MODE (L-G) IN 50 OHM SYSTEM						
CURRENT RATING	FREQUENCY-MHz					
	.15	.50	1.0	5.0	10	30
3A	20	30	30	30	25	10
8A	10	12	15	15	15	10
10A	5	10	12	12	12	10
DIFFERENTIAL MODE (L-L) IN 50 OHM SYSTEM						
3A	0	10	12	25	25	20
8A	0	10	12	25	25	20
10A	0	10	12	25	25	20

MECHANICAL CONSTRUCTION



G3DAM






W3DAM


SPECIFICATIONS

1. Maximum leakage current each line-to-ground @ 115VAC 60Hz: 2uA @ 250VAC 50Hz: 5uA
2. Hipot rating (one minute) line-to-ground: 2250VDC line-to-line: 1450VDC
3. Operating frequency: 50/60Hz
4. Rated voltage: 115/250VAC

ELECTRICAL SCHEMATIC



SUGGESTED MOUNTING CUTOUT



SUGGESTED MOUNTING CUTOUT

ALL WIRE LEADS 4.0" LONG MIN.

UNIT: INCH
mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Delta Electronics:

[08KEEW3DAM](#) [10KEEW3EAM](#) [03KEEG3EAM-R](#) [08KEEG3DAM](#) [10KEEW3EAM-R](#) [10KEEG3EAM-R](#)
[10KEEG3DAM](#) [10KEEW3DAM-R](#) [03KEEW3DAM](#) [08KEEG3EAM-R](#) [10KEEW3DAM](#) [03KEEW3EAM](#) [03KEEG3EAM](#)
[03KEEW3DAM-R](#) [03KEEG3DAM](#) [03KEEW3EAM-R](#) [10KEEG3EAM](#) [08KEEW3EAM](#) [03KEEG3DAM-R](#)
[08KEEG3EAM](#) [08KEEW3EAM-R](#) [08KEEW3DAM-R](#) [08KEEG3DAM-R](#) [10KEEG3DAM-R](#)