



SOLENOID PRODUCT SPECIFICATION

PART No.	VOLTAGE	DUTY CYCLE	POWER (W)	CURRENT (A)	DCR (Ω) *
DSOL-1333-48A	48 VAC	100%	10	0.21	224
DSOL-1333-36A	36 VAC	100%	10	0.28	130
DSOL-1333-24A	24 VAC	100%	10	0.33	73
DSOL-1333-18A	18 VAC	100%	10	0.60	30
DSOL-1333-12A	12 VAC	100%	10	0.89	13.5


* OPERATION: POWER TO PULL

* DCR VALUES ARE $\pm 10\%$ AT 25°C


1. MECHANICAL DIMENSIONS :



2. SCHEMATIC AND CONSTRUCTION :



2.1 DIODE CONSTRUCTION :



UNIT : INCH.

A = 1.25

B = 1.38

C = 0.44

D = 0.75

E = 1.60

F = 0.46

G = 0.86

H = 1.28

I = 1.00


J = 0.69 REF.

K = 1.65

L = 0.65

M = 0.55

N = 0.50

TOLERANCE: ± 0.02 

LAYER TEST	IR. @500 Vdc.	HI-POT
(S-F): 1KVp. MIN.	COIL TO CASE	@50/60Hz., 2mA
TEST ONLY COIL	100 MOHM MIN.	COIL TO CASE
		1500Vac., 60s

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delta Electronics:](#)

[DSOL-1333-12](#) [DSOL-1333-18](#) [DSOL-1333-24](#) [DSOL-1333-36](#) [DSOL-1333-48](#)