

AVQ400 Series

396 Watts

Data Sheet

Total Power: 396 Watts
Input Voltage: 36 - 75 V
of Outputs: Single

SPECIAL FEATURES

- 2:1 wide input range
- Optimised for high density, small space applications
- Low ripple and noise
- Fixed switching frequency
- High efficiency
- High capacitive load capability
- Basic insulation system
- Openframe structure with baseplate option
- Output over current protection

SAFETY

- UL, cUL: UL62368
- TUV/CE: IEC/EN62368



Electrical Specifications

Input	
Input range	36 - 75 VDC
Efficiency	95% @ 12 Vo
Output	
Voltage tolerance	+/-1.6%
Line regulation	24 mV
Load regulation	60 mV
Noise/ripple	3.3 Vo: 150 mV
Overvoltage protection	Hiccup
Overtemperature protection	Auto-restart
Switching frequency	140 KHz
Temperature co-efficient	±0.02/°C
Isolation	
I/O isolation	1500 VDC (2121 VDC for AVQ400-48S12B-6LN)

Environmental Specifications


Operating ambient temperature range	-40° C to +85° C
Storage temperature	-55 °C to +125 °C
Humidity	5% to 95% (non-condensing)
MTBF	1.5 Million hours
RoHS Compliant	

Ordering Information

Model number	Input voltage	Output voltage	Power
AVQ400-48S12B-4L	36 - 75 Vin	12 V @ 33 A	396 W
AVQ400-48S12B-6L	36 - 75 Vin	12 V @ 33 A	396 W
AVQ400-48S12PB-4L	36 - 75 Vin	12 V @ 33 A	396 W
AVQ400-48S12PB-6L	36 - 75 Vin	12 V @ 33 A	396 W
AVQ400-48S12B-6LN	36 - 75 Vin	12 V @ 33 A	396 W

- Standard version is negative enable
- “-6” = 3.8 mm pin length
- “-4” = 4.8 mm pin length
- “-L” = RoHS 6 compliance
- “-P” = Positive enable
- “B” = Baseplate

Mechanical Drawings



Bottom view: pin on upsi

Tolerance: X.Xmm±0.5mm[X.X in.±0.02in.]

X.XXmm±0.25mm[X.XX in.±0.01in.]

Pin Assignments

Pin #	Function
1	+V in
2	Enable
3	-V in
4	-V out
5	+V out

Notes:

1. All specifications are subject to change without notice. Mechanical drawings are for reference only.
2. Warranty: 2 years
3. Label and logo appearance may vary from what is shown on mechanical drawings.

WORLDWIDE OFFICES

Americas

2900 S.Diablo Way
Tempe, AZ 85282
USA
+1 888 412 7832

Europe (UK)

Waterfront Business Park
Merry Hill, Dudley
West Midlands, DY5 1LX
United Kingdom
+44 (0) 1384 842 211

Asia (HK)

14/F, Lu Plaza
2 Wing Yip Street
Kwun Tong, Kowloon
Hong Kong
+852 2176 3333

ARTESYN[™]
EMBEDDED TECHNOLOGIES

www.artesyn.com

Artesyn Embedded Technologies, Artesyn and the Artesyn Embedded Technologies logo are trademarks and service marks of Artesyn Embedded Technologies, Inc. All other names and logos referred to are trade names, trademarks, or registered trademarks of their respective owners. Specifications are subject to change without notice. © 2019 Artesyn Embedded Technologies, Inc. All rights reserved. For full legal terms and conditions, please visit www.artesyn.com/legal.

For more information: www.artesyn.com/power
For support: productsupport.ep@artesyn.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Artesyn Embedded Technologies:](#)

[AVQ400-48S12B-4L](#) [AVQ400-48S12PB-4L](#)