




Raspberry Pi 3 Model A+

Published April 2024



The terms HDMI, HDMI High-Definition Multimedia Interface, and the HDMI Logo are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Overview




Raspberry Pi 3 Model A+, like Raspberry Pi 3 Model B+, has a 64-bit quad-core processor running at 1.4GHz, together with dual-band 2.4GHz and 5GHz wireless LAN, and Bluetooth 4.2/BLE. The dual-band wireless LAN comes with modular compliance certification.

Raspberry Pi 3 Model A+ has the same mechanical footprint as Raspberry Pi 1 Model A+.

Specification

Processor:	Broadcom BCM2837B0, Cortex-A53 64-bit SoC @ 1.4 GHz
Memory:	512MB LPDDR2 SDRAM
Connectivity:	2.4 GHz and 5 GHz IEEE 802.11.b/g/n/ac wireless LAN, Bluetooth 4.2/BLE 1 × USB 2.0 port
Access:	Extended 40-pin GPIO header
Video & sound:	<ul style="list-style-type: none">• 1 × full size HDMI• MIPI DSI display port• MIPI CSI camera port• 4 pole stereo output and composite video port
Multimedia:	H.264, MPEG-4 decode (1080p30); H.264 encode (1080p30); OpenGL ES 1.1, 2.0 graphics
SD card support:	Micro SD format for loading operating system and data storage
Input power:	<ul style="list-style-type: none">• 5 V/2.5 A DC via micro USB connector• 5 V DC via GPIO header
Environment:	Operating temperature, 0–50°C
Compliance:	For a full list of local and regional product approvals, please visit pip.raspberrypi.com
Production lifetime:	Raspberry Pi 3 Model A+ will remain in production until at least January 2030

Physical Specification




WARNINGS

- This product should only be connected to an external power supply rated at 5 V/2.5 A DC. Any external power supply used with Raspberry Pi 3 Model A+ shall comply with relevant regulations and standards applicable in the country of intended use.
- This product should be operated in a well-ventilated environment and, if used inside a case, the case should not be covered.
- While in use, this product should be placed on a stable, flat, non-conductive surface and should not be contacted by conductive items.
- The connection of incompatible devices to the GPIO connection may affect compliance, result in damage to the unit, and invalidate the warranty.
- All peripherals used with this product should comply with relevant standards for the country of use and be marked accordingly to ensure that safety and performance requirements are met. These articles include but are not limited to keyboards, monitors, and mice when used in conjunction with Raspberry Pi.
- The cables and connectors of all peripherals used with this product must have adequate insulation so that relevant safety requirements are met.

SAFETY INSTRUCTIONS

To avoid malfunction or damage to this product, please observe the following:

- Do not expose to water or moisture, or place on a conductive surface while in operation.
- Do not expose to heat from any source; Raspberry Pi 3 Model A+ is designed for reliable operation at normal ambient temperatures.
- Take care while handling to avoid mechanical or electrical damage to the printed circuit board and connectors.
- While it is powered, avoid handling the printed circuit board, or only handle it by the edges to minimise the risk of electrostatic discharge damage.





Raspberry Pi is a trademark of Raspberry Pi Ltd

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Raspberry Pi:](#)

[SC0130\(J\)](#)