




USB-C100 / C101 Turn-Key Module for USB-C Connected Headphones & Headsets

Applications

The USB-C100 / C101 Modules are the absolute simplest conversion path for ANY Tier 1, Tier 2, or Tier 3 ODM or OEM to convert their current 3.5mm Headphones or Headsets designs that are “Android™-compatible” with 1 or 3-button resistor-ladder network solutions into a fully functional all-digital USB-C connected solution with support for the following functions REGARDLESS of a device’s operating system.

Near Universal Operating System Support


- Android 7.0 and later
- macOS X 10.0.0 and later
- Microsoft® Windows® CE, XP, Vista, 7, 8, 8.1, 10 and later
- Any modern Linux® distribution (Kernel 2.73) and later



Features

- Functions for 1-button or 3-button* Android-compliant Headsets as indicated below via:
 - Volume Up (volume up button)*
 - Volume Down (volume down button) *
 - Pause / Play / Answer / Hangup (single short press of Pause / Play button)
 - Voice Assistant “OK Google”, “Hey Bixby”, “Hi Cortana” (long press of Pause / Play button)
 - Skip from Current Track to Next Track (quick double press of Pause / Play button)
 - Scan Current Track Forward (quick press of Pause / Play button followed by long press)
 - Skip Current Track to Previous Track (quick triple press of Pause / Play button)
 - Scan Current Track Forward (quick double press of Pause / Play button followed by long press)
- 24-bit stereo digital audio playback and audio capture capability at 48kHz
- Supports high-resolution telephony sessions
- Integrated support for low-cost resistor ladder networks three button interface
- Simplest and fastest time-to-market solution available
- Pre-programmed USB Audio Bridge with no coding required
- Zero development time
- Secure bootloader ensures there is no possible way to load any sort of malware / virus / trojan / spyware / etc. via USB-C port
- TSCS25xx low-power 32-bit Stereo Audio Codec with integrated ground-center referenced HP amplifier
- Lowest measured power for any equivalent performance & feature solution on the market

3.5mm Headphone or Headset Conversion / USB-C Headphone or Headset Design Process



- Cut the 3.5mm jack from current Headphone or Headset and exposes all four of the wires.
- Solder these 4 wires to the respective soldering pads (Left, Right, Ground, Mic - from top to bottom) on the USB-C100 / USB-C101 module as shown in the picture to the left.
- Cover USB-C100 / USB-C101 module and secure wire with stress relief in plastic, rubber or non-static material.

Technical Details

- Tempo Semiconductor TSCS25xx - Low-Power Audio Codec - 96kHz / 32-bit with integrated 24-bit signal processing engine
- 32-bit, 90dB SNR ADC / 96kHz-capable enables support for external analog mics for telephony support
- 32-bit DAC, 96kHz-capable, with a combined capless HP amplifier with 124dB SNR
- Ultra-low-latency ensures optimal A/V sync performance for all applications and mobile or VoIP-based calls
- Complimentary Android App enables customization of a wide variety of DSP audio enhancements with end-user personalization capability inside the app (USB-C101 module only)

Where to Buy

- The USB-C100 and USB-C101 turn-key modules are currently sampling directly from the factory.

Please contact sales@temposemi.com to request product pricing & samples. The modules are available in mass-production quantities with 8-week leadtimes.

**Note: The USB-C100 / USB-C1010 modules have been designed to meet the exacting needs of customers that are looking to replace the same level of functionality their 3.5mm headphones or 3.5mm Android-compatible headsets with either 1, 2, or 3 buttons that meet the following specification: <https://source.android.com/devices/accessories/headset/plug-headset-spec>.*

***Note: The latest firmware in the CP2615 has been confirmed to 100% compliant to the latest available Android USB Headset specification: <https://source.android.com/devices/accessories/headset/usb-headset-spec> (last updated on July 27th, 2017). The USB-C100 and USB-101 modules include support, via a "long press" of the Play/Pause (Function A) button to bring up the Google Voice Assistant, for Android 7.0 and later.*

The USB-C101 turn-key module differs from the USB-C100 module in that it includes such premium differentiating features like access to a DSP-based implementation in the TSCS25xx Audio Codec such as multiband EQ (up to 12 bands of stereo parametric EQ) to enable a flat frequency response of the headphone and/or enable content EQ settings (e.g. "Rock", "Pop", "Jazz", etc.) or a combination thereof (e.g. stereo bands for Speaker EQ and 6 stereo bands for Content EQ), a 3D stereo enhancement for surround encoded content, a psychoacoustic bass enhancement, a high-frequency content restoration enhancement, wideband DRC, and a multiband compressor / limiter / expander. All of these features can be controlled via a complementary and customizable Android App that enables the consumer to adjust and save these parameters inside the app.

macOS is a trademark of Apple, Inc., registered in the U.S. and other countries. Microsoft®, Windows®, Windows CE®, Windows XP®, Windows Vista™, Windows 7®, Windows 8®, Windows 8.1® and Windows 10® are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. Android is a trademark of Google Inc. Linux® is the registered trademark of Linus Torvalds in the U.S. and other countries. TSI and the TSI logo are trademarks or registered trademarks of Tempo Semiconductor, Inc. All rights reserved. Copyright 2017 Tempo Semiconductor, Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tempo Semiconductor:](#)

[TSI-USB-C100-MODULE-A](#)