

ReliaGATE 10-11

- ARM Powered
- IoT Ready
- Industrial and Automotive Grade
- Field Protocol Support
- Cloud Certified
- Open Platform
- Customizable



FEATURES

ARM Powered - Powered by TI AM335X CPU: optimum performance for intensive workloads at just 2W

IoT Ready - Breadth of connectivity options: 3G cellular modem, GPS, Wi-Fi, BLE, Fast Ethernet and Fieldbus interfaces, including CAN bus ports, optoisolated digital I/Os, protected USB and serial ports

Industrial and Automotive Grade - Wide operating temperature, wide range power supply with transient protection, and E-Mark certification

Field Protocol Support - Native support for Modbus, S7 and OPC UA, the extensible, secure, and platform-independent industrial interoperability standard

Cloud Certified - Seamless integration with Eurotech Everyware Cloud, Microsoft Azure, Amazon Web Services IoT and other Cloud services

Open Platform - Provides a Java/OSGi gateway middleware, to free the developer from proprietary solutions

Customizable - Personalization and full customization options are available, ranging from branding ("skins" and color) to deep HW/SW configurations

ReliaGATE 10-12 is a Multi-service IoT Gateway that has been designed to comply with global certification requirements for industrial and lightly rugged applications.

Based on the TI AM335X Cortex-A8 processor family, with 512MB of RAM and 4GB of eMMC, the ReliaGATE 10-11 is a low power gateway suitable for industrial and automotive applications: it supports a 9 to 36V power supply with transient protection and vehicle ignition sense, two protected RS-232/RS-485 serial ports, two CAN Bus interfaces, and much more.

The ReliaGATE 10-11 features a wide range of connectivity capabilities: it integrates a global cellular modem with GPS, Wi-Fi, Bluetooth, and two Fast Ethernet ports. A dedicated internal GPS is also available as a factory option.

The ReliaGATE 10-11 comes with Everyware Software Framework (ESF), a commercial, enterprise-ready edition of Eclipse Kura, the open source Java/OSGi middleware for IoT gateways.

Distributed and supported by Eurotech, ESF supports ready-to-use field protocols (including Modbus, OPC-UA, S7), MQTT connectivity, web-based visual data flow programming and deep configuration.

ESF is also integrated with Everyware Cloud (EC), Eurotech's IoT Integration Platform (separately available), enabling advanced diagnostics, provisioning, and full remote device access and management.

The ReliaGATE 10-11 is Microsoft Azure certified and can also be integrated with 3rd party cloud services such as Amazon Web Services IoT.

ReliaGATE 10-11

Specifications

Ordering code: REGATE-10-11-XX

XX		- 31	- 32	- 33	- 36	- 37
PROCESSOR	CPU	TI AM3352 800MHz, 1 Core				
MEMORY	RAM	512MB DDR3				
STORAGE	Embedded	4GB eMMC				
	Other	microSD Slot (User Accessible)				
I/O INTERFACES	Ethernet	1x 10/100Mbps - RJ45		2x 10/100Mbps - RJ45		
	USB	3x Host 2.0 (Noise and Surge Protected) - Type A	2x Host 2.0 (Noise and Surge Protected) - Type A		3x Host 2.0 (Noise and Surge Protected) - Type A	2x Host 2.0 (Noise and Surge Protected) - Type A
	Serial	2x RS-232/RS-485 (Surge Protected, RS-485 Termination and Fail-safe Resistors) - 1x Serial Console TTL				
	CAN 2.0B	No	2x CAN bus with 5V (100mA) Power Out			
	Digital I/O	2x Digital Input 5V (TTL), 1KV Optoisolated - 2x Digital Output (40VDC), 30mA Sink				
RADIO INTERFACES	Cellular	No	3G Global		ReliaCELL Option	3G Japan Only
	GPS	No	Integrated		ReliaCELL Option	Integrated
	Wi-Fi / BT	No		b/g/n, BLE		
	Antennas (External)	No	2x SMA Cell/GPS	2x SMA Cell/GPS 1x RSMA Wi-Fi/BT	1x RP-SMA Wi-Fi/BT	2x SMA Cell/GPS 1x RSMA Wi-Fi/BT
OTHER	RTC	Yes (User Accessible Battery)				
	Watchdog	Yes (Dedicated Chip)				
	EEPROM	256kbit				
	Sensors	Temperature		Temperature, Accelerometer		
	LEDs	1x Power, 4x Programmable	1x Power, 1x Cellular 4x Programmable		1x Power, 4x Programmable	1x Power 1x Cellular 4x Programmable
	Buttons	1x Reset, 1x Programmable				
	SIM Slot	No	1x microSIM (User Accessible)		No	1x microSIM (User Accessible)
POWER	Input	9-36VDC, with Transient Protection, Vehicle Ignition Sense				
	Consumption	2W Idle (15W Max)				
ENVIRONMENT	Operating Temp	- 20 to +70°C				
	Storage Temp	- 40 to +85°C				
CERTIFICATIONS (*)	Regulatory	CE, FCC, ISED, JATE, TELEC, E-Mark				
	Safety	EN 62368, UL [§] 60950				
	Environmental	RoHS2; REACH				
	Wi-Fi / BT Radio	No		RED, FCC, JATE, TELEC		
	Cellular Radio	No	RED, FCC, PTCRB, AT&T		ReliaCELL Cert.	JATE, TELEC
	IoT Platform	Microsoft Azure Certified				
MECHANICAL	Ingress	IP40				
	Enclosure	Material: ABS - Color: Aluminum				
	Dimensions	140x95x45mm (LxWxH) - with SMA Connectors				

*Additional Country Certifications for REGATE-10-11-33 are: NOM and IFETEL (Mexico), RCM (Australia / New Zealand), CCC (China)

SOFTWARE

OS	Yocto Linux
SDK	Yocto-based Eclipse Tooling
IoT Framework	Oracle Java SE Embedded Version 8 - Everyware Software Framework (Java/OSGi)

Note: The information in this document is subject to change without notice and should not be construed as a commitment by EUROTECH. While reasonable precautions have been taken, EUROTECH assumes no responsibility for any error that may appear in this document. All trademarks or registered trademarks are the properties of their respective companies. © UL, NRTL listing Factory Option.

ETH_ReliaGATE 10-11_DS_EN_Rev 07_11/2017

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eurotech:](#)

[REGATE-10-11-36](#) [REGATE-10-11-33](#) [REGATE-10-11-31](#) [REGATE-10-11-32](#)