

96PR-127-USP-D

300 dpi Desktop Barcode Printer, 4.17",
5 ips, USB/Serial/Parallel, SD Card Slot



Features

- 4" desktop barcode label printer
- Resolution: 300 dpi
- Max. print speed: 127mm (5")/sec
- USB, Serial, Parallel
- 4 MB Flash memory and 8 MB SDRAM memory
- microSD Flash memory expansion up to 4 GB

Specifications

Resolution	12 dots/mm (300 dpi)	
Printing method	Thermal Transfer & Direct Thermal	
Max. print speed	127 mm (5")/second	
Max. print width	106 mm (4.17")	
Max. print length	1,016 mm (40")	
Enclosure	Double-walled plastic	
Physical dimension (W x H x D)	213 x 188 x 314 mm (8.39" x 7.40" x 12.36")	
Weight	2.8 kg (6.17 lbs)	
Label roll capacity	127 mm (5") OD	
Ribbon	300 m long, max. OD 67 mm, 1" core (ink coated outside)	
Ribbon width	40 ~ 110 mm (1.6" ~ 4.3")	
Processor	32-bit RISC CPU	
Memory	4 MB Flash memory 8 MB SDRAM - SD card reader for Flash memory expansion, up to 4 GB	
Interface	- USB 2.0 - Centronics - Bluetooth (option)	- RS-232 - Internal Ethernet, 10/100 Mbps (option) - External 802.11 b/g/n wireless (option)
Power	External universal switching power supply - Input: AC 100-240V, 2.5A, 50-60Hz - Output: DC 24V, 3.75A, 90W	
Operation switch, button, LED	1 power switch, 1 feed button & 1 LED (3 colors: green, amber & red)	
Sensors	- Gap transmissive sensor (position adjustable) - Ribbon end sensor	- Black mark reflective sensor (position adjustable) - Head open sensor
Real time clock	- Transmissive gap sensor - Ribbon end sensor	- Black mark reflective sensor (position adjustable) - Head open sensor
Internal fonts	8 alpha-numeric bitmap fonts - Monotype Image® true type font engine with one CG Triumvirate Bold Condensed scalable font	
Bar code	1D bar code - Code 39, Code 93, Code 128UCC, Code 128 subset A, B, C, Codabar, Interleave 2 of 5, EAN-8, EAN-13, EAN-128, UPC-A, UPC-E, EAN and UPC 2 (5) digits add-on, MSI, PLESSEY, POSTNET, RSS-Stacked, GS1 DataBar, Code 11 2D bar code - PDF-417, Maxicode, DataMatrix, QR Code, Aztec	
Font and barcode rotation	0, 90, 180, 270 degree	
Printer language	TSPL-EZ™ (Compatible to EPL, ZPL, ZPL II)	
Media type	Continuous, die-cut, black mark, fan-fold, notched (outside wound)	
Media width	20 ~ 112 mm (0.78" ~ 4.4")	
Media thickness	0.06 ~ 0.19 mm (2.36 ~ 7.48 mil)	
Media core diameter	25.4 ~ 76.2 mm (1" ~ 3")	
Label length	10 ~ 1,016 mm (0.39" ~ 40")	
Environment condition	Operation: 5 ~ 40°C, 25 ~ 85% non-condensing Storage: -40 ~ 60°C, 10~ 90% non-condensing	
Safety regulation	FCC Class B, CE Class B, C-Tick Class B, UL, CUL, TÜV/Safety, CCC	
Environmental concern	Comply with RoHS, WEEE	
Accessories	- Windows labeling software CD disk - USB cable - External universal switching power supply - Ribbon spindle x 2	- Quick start guide - Power cord - Label spindle, fixing tab x 2, 1.5" core adapter x 2 - Ribbon paper core
Options	- Internal Ethernet interface (10/100 Mbps) - Peel-off module - Bluetooth module (serial interface) - External roll mount, media OD. 214 mm (8.4") on a 1" or 3" core - KP-200 Plus keyboard display unit	- Real time clock - Guillotine cutter (full cut or partial cut) 802.11 b/g/n wireless module (serial interface) 3" core label spindle - KU-007 Plus programmable smart keyboard

Ordering Information

Part Number	Description
96PR-127-USP-D	Desktop Barcode Printer, 300dpi, 4.17", 5 ips, USB/Serial/Parallel, SD card slot, US power cord

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[96PR-127-USP-D](#)