

96PR-203-UXH-D

**203 dpi Desktop Barcode Printer, 4.25",
8 ips, USB/Serial/Ethernet/USB Host,
SD Card Slot**



Features

- 4" desktop barcode label printer
- Resolution: 203 dpi
- Max. print speed: 203mm (8")/sec
- USB, Serial, Ethernet, USB Host
- 128 MB Flash memory and 128 MB SDRAM memory
- microSD Flash memory expansion up to 32 GB

Specifications

Resolution	8 dots/mm (203 dpi)	
Printing method	Thermal Transfer & Direct Thermal	
Max. print speed	203 mm (8")/second	
Max. print width	108 mm (4.25")	
Max. print length	25,400 mm (1,000")	
Enclosure	Clamshell with double-walled plastic	
Physical dimension (W x H x D)	226 x 198 x 332 mm (8.90" x 7.80" x 13.07")	
Weight	3.75 kg (8.27 lbs)	
Label roll capacity	127 mm (5") OD	
Ribbon	300 m long, max. OD 67 mm, 1" core (ink coated outside)	
Ribbon width	40 ~ 110 mm (1.6" ~ 4.3")	
Processor	32-bit RISC CPU	
Memory	• 128 MB Flash memory • 128 MB SDRAM • microSD card reader for Flash memory expansion, up to 32 GB	
Interface	• USB 2.0 • Internal Ethernet, 10/100 Mbps • Centronics (option) • Slot-in 802.11 a/b/g/n wireless (option) • RS-232 • USB Host • External Bluetooth (option)	
Operation switch, button, LED/LCD	• 1 power switch • 1 feed/pause button • LED panel with 8 big icons	
Power	• External universal switching power supply • Input: AC 100-240V, 2.5A, 50-60Hz • Output: DC 24V, 3.75A, 90W	
Sensors	• Transmissive gap sensor • Ribbon encode sensor • Black mark reflective sensor (position adjustable) • Head open sensor	
Real time clock	Option	
Internal fonts	• 8 alpha-numeric bitmap fonts • Monotype Image® true type font engine with one CG Triumvirate Bold Condensed scalable font	
Bar code	• 1D bar code - Code 39, Code 93, Code128UCC, Code128 subsets A,B,C, Codabar, Interleaved 2 of 5, EAN 8, EAN 13, EAN 128, UPC-A, UPC-E, EAN and UPC 2(5) digits add-on, MSI, PLESSEY, POSTNET, China post, ITF14, EAN14, Code 11, TELEPEN, TELEPENN, PLANET, Code 49, Deutsche Post Identcode, Deutsche Post Leitcode, LOGMARS • 2D bar code - TL39, CODABLOCK F mode, PDF-417, Maxicode, DataMatrix, QR code, Aztec, Micro PDF 417, GS1 DataBar (RSS barcode)	
Font and barcode rotation	0, 90, 180, 270 degree	
Printer language	TSPL-EZTM (Compatible to EPL, ZPL, ZPL II)	
Media type	Continuous, die-cut, black mark, fan-fold, notch (outside wound)	
Media width	19 ~112 mm (0.75" ~ 4.4")	
Media thickness	0.055 ~ 0.254 mm (2.17 ~ 10 mil)	
Media core diameter	25.4 ~ 38.1 mm (1" ~ 1.5")	
Label length	3 ~ 25,400 mm (0.1" ~ 1,000")	
Environment condition	Operation: 5 ~ 40°C, 25 ~ 85% non-condensing Storage: -40 ~ 60°C, 10 ~ 90% non-condensing	
Safety regulation	FCC Class B, CE Class B, RCM, UL, cUL, TÜV/Safety, CCC, BIS, EAC, ENERGY STAR®	
Environmental concern	Comply with RoHS, WEEE	
Accessories	• Windows labeling software CD disk • USB cable • External universal switching power supply • Quick start guide • Power cord	
Options	• Centronics parallel interface • 3.5" color TFT display (includes real time clock) • Peel-off module • 802.11 a/b/g/n wireless module (slot-in) • External label roll mount • KU-007 Plus programmable smart keyboard • Real time clock • Ribbon end sensor • Guillotine cutter (full cut) • Bluetooth module (serial interface) • KP-200 Plus keyboard display unit	

Ordering Information

Part Number	Description
96PR-203-UXH-D	Desktop Barcode Printer, 203dpi, 4.25", 8 ips, USB/Serial/Ethernet/USB Host, SD card slot, US power cord
96PR-203-UXH-D-E	Desktop Barcode Printer, 203dpi, 4.25", 8 ips, USB/Serial/Ethernet/USB Host, SD card slot, EU power cord
96PR-203-UXH-D-C	Desktop Barcode Printer, 203dpi, 4.25", 8 ips, USB/Serial/Ethernet/USB Host, SD card slot, CN power cord

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[96PR-203-UXH-D](#)