


SERIES: PCN1-M | DESCRIPTION: DC-DC CONVERTER
FEATURES

- up to 1 W isolated output
- industry standard surface mount package
- nominal input voltages: 5, 12 Vdc
- single/dual unregulated output
- 1,500 Vdc isolation voltage
- low ripple and noise
- -40 to 100°C
- efficiency up to 81%
- designed to meet EN 62368-1


MODEL

MODEL	input voltage		output voltage (Vdc)	output current		output power max (W)	ripple & noise ¹ max (mVp-p)	efficiency typ (%)
	typ (Vdc)	range (Vdc)		min (mA)	max (mA)			
PCN1-S5-S5-M	5	4.5~5.5	5	0	200	1	75	79
PCN1-S5-S12-M	5	4.5~5.5	12	0	84	1	75	79
PCN1-S5-S15-M	5	4.5~5.5	15	0	67	1	75	79
PCN1-S5-D5-M	5	4.5~5.5	±5	0	±100	1	75	74
PCN1-S5-D12-M	5	4.5~5.5	±12	0	±42	1	75	78
PCN1-S5-D15-M	5	4.5~5.5	±15	0	±33	1	75	78
PCN1-S12-S5-M	12	10.8~13.2	5	0	200	1	75	80
PCN1-S12-S12-M	12	10.8~13.2	12	0	84	1	75	81
PCN1-S12-S15-M	12	10.8~13.2	15	0	67	1	75	81
PCN1-S12-D5-M	12	10.8~13.2	±5	0	±100	1	75	77
PCN1-S12-D12-M	12	10.8~13.2	±12	0	±42	1	75	80
PCN1-S12-D15-M	12	10.8~13.2	±15	0	±33	1	75	81

Notes: 1. At full load, nominal input, 20 MHz bandwidth oscilloscope, with a 0.33 μ F ceramic capacitor on the output.
 2. Required to add a 2.2 μ F ceramic capacitor to the input to reduce input voltage stress.
 3. All specifications are measured at Ta=25°C, nominal input voltage, and rated output load unless otherwise specified.

PART NUMBER KEY


INPUT

parameter	conditions/description	min	typ	max	units
operating input voltage	5 Vdc input models	4.5	5	5.5	Vdc
	12 Vdc input models	10.8	12	13.2	Vdc
surge voltage	for maximum of 100 ms				
	5 Vdc input models			9	Vdc
	12 Vdc input models			18	Vdc
current	5 Vdc input models		250		mA
	12 Vdc input models		110		mA
filter	capacitive				
input reverse polarity protection	no				
input fuse	0.5 A time delay fuse for all models (recommended)				

Notes: 1. Required to add a 2.2 μ F ceramic capacitor to the input to reduce input voltage stress.

OUTPUT

parameter	conditions/description	min	typ	max	units
maximum capacitive load	single output models			220	μ F
	dual output models			100	μ F
voltage accuracy				± 3.0	%
line regulation	1.0% change in input voltage			± 1.2	%
load regulation	from 20% load to full load			± 10	%
switching frequency	at nominal Vin, full load		100		kHz
temperature coefficient				± 0.05	%/ $^{\circ}$ C

PROTECTIONS

parameter	conditions/description	min	typ	max	units
short circuit protection	momentary			1	s

SAFETY AND COMPLIANCE

parameter	conditions/description	min	typ	max	units
isolation voltage	input to output for 1 minute	1,500			Vdc
isolation resistance	input to output	1,000			M Ω
isolation capacitance	input to output		10		pF
conducted emissions	EN 55022 Class B (external circuit required, see Figure 4)				
MTBF	as per MIL-HDBK-217F, full load, GB, 25 $^{\circ}$ C		1,500,000		hours
RoHS	yes				


ENVIRONMENTAL

parameter	conditions/description	min	typ	max	units
operating temperature	see derating curve	-40		100	$^{\circ}$ C
storage temperature		-55		125	$^{\circ}$ C
operating humidity	non-condensing			95	%

SOLDERABILITY

parameter	conditions/description	min	typ	max	units
reflow soldering	see reflow solder profile			245	°C

- Notes:
1. Soldering paste: SHENMAO PF610-P (Sn/Ag/Cu)
 2. Ramp up rate during preheat: 1.79°C/second (from 30°C~155°C)
 3. Soaking temperature: 0.33°C/second (from 155°C~185°C)
 4. Ramp up rate during reflow: 0.71°C/second (from 220°C~245°C)
 5. Peak temperature: 245°C (10 seconds max), above 220°C 40 to 70 seconds
 6. Ramp up rate during cooling: -1.75°C/second (from 220°C~150)



MECHANICAL

parameter	conditions/description	min	typ	max	units
dimensions	single output models: 0.54 x 0.36 x 0.29 [13.7 x 9.2 x 7.4 mm] dual output models: 0.64 x 0.36 x 0.29 [16.2 x 9.2 x 7.4 mm]				inches inches
case material	non-conductive black plastic				
weight	single output models dual output models		1.4 1.5		g g

MECHANICAL DRAWING

Single output models



units: inches [mm]

tolerance: X.XX ±0.01 [±0.25]



X.XXX ±0.005 [±0.13]

pin section tolerance: ±0.002[±0.05]

PIN CONNECTIONS	
PIN	Function
	Single
1	-Vin
2	+Vin
3	No pin
4	-Vout
5	+Vout
6	No pin
7	No pin
8	NC



Recommended PCB Layout
Top View



NC=no connection

MECHANICAL DRAWING (CONTINUED)

Dual output models

units: inches [mm]





tolerance: X.XX ±0.01 [±0.25]

X.XXX ±0.005 [±0.13]

pin section tolerance: ±0.002[±0.05]


PIN CONNECTIONS	
PIN	Function
	Dual
1	-Vin
2	+Vin
3	No pin
4	Common
5	-Vout
6	No pin
7	+Vout
8	No pin
9	No pin
10	NC

NC=no connection




DERATING CURVE

TEMPERATURE DERATING CURVE




EFFICIENCY CURVES


EFFICIENCY VS OUTPUT LOAD
PCN1-S5-S5-M




EFFICIENCY VS OUTPUT LOAD
PCN1-S5-S12-M




EFFICIENCY VS OUTPUT LOAD
PCN1-S5-S15-M




EFFICIENCY VS OUTPUT LOAD
PCN1-S12-D5-M



EFFICIENCY VS OUTPUT LOAD
PCN1-S5-D12-M




EFFICIENCY VS OUTPUT LOAD
PCN1-S5-D15-M



EFFICIENCY CURVES (CONTINUED)

EFFICIENCY VS OUTPUT LOAD
PCN1-S12-S5-M




Key

10.8 Vdc

12 Vdc

13.2 Vdc

EFFICIENCY VS OUTPUT LOAD
PCN1-S12-S12-M




Key

10.8 Vdc

12 Vdc

13.2 Vdc

EFFICIENCY VS OUTPUT LOAD
PCN1-S12-S15-M




Key

10.8 Vdc

12 Vdc

13.2 Vdc

EFFICIENCY VS OUTPUT LOAD
PCN1-S12-D5-M




Key

10.8 Vdc

12 Vdc

13.2 Vdc

EFFICIENCY VS OUTPUT LOAD
PCN1-S12-D12-M




Key

10.8 Vdc

12 Vdc

13.2 Vdc

EFFICIENCY VS OUTPUT LOAD
PCN1-S12-D15-M



Key

10.8 Vdc

12 Vdc

13.2 Vdc


PACKAGING (TUBE)

units: mm

Tube Size: 14 x 14 x 535 mm

Single Output Models QTY: 36 pcs per tube

Dual Output Models QTY: 30 pcs per tube




PACKAGING (TAPE & REEL)

Single output models

units: mm

Reel Size: Ø13"

QTY: 430 pcs per reel




Dual output models

units: mm

Reel Size: Ø13"

QTY: 430 pcs per reel



TEST CONFIGURATIONS

Input Ripple Current & Output Noise

Figure 1
Measuring Input Ripple Current




Figure 2
Measuring Output Ripple & Noise for Single Output Models




Figure 3
Measuring Output Ripple & Noise for Dual Output Models




Table 1

L1	12 µH
C1	2.2 µF tantalum capacitor
C2	NC

Table 2

Input Voltage (Vdc)	Cin
5	2.2 µF ceramic capacitor
12	2.2 µF ceramic capacitor

EMC RECOMMENDED CIRCUIT

Test Condition

Input Voltage: Nominal

Output Load: Full Load

Figure 4
Conducted Emissions Test Circuit




Table 3

EN55022 Class B Recommended External Circuit Components			
Input Voltage (Vdc)	C1 ¹	C2 ¹	L1
5	4.7 µF / 25 V	4.7 µF / 25 V	10 µH
12	4.7 µF / 25 V	4.7 µF / 25 V	10 µH

Notes: 1. Ceramic Capacitor

REVISION HISTORY

rev.	description	date
1.0	initial release	07/26/2016
1.01	added tube packaging option	06/09/2017
1.02	removed tube packaging option	02/14/2020
1.03	safeties updated	05/26/2021
1.04	derating curve, efficiency curves and circuit figures updated	07/01/2021
1.05	CE certification updated	11/03/2022
1.06	safeties updated	10/08/2024

The revision history provided is for informational purposes only and is believed to be accurate.



CUI INC
a bel group

Headquarters

15575 SW Sequoia Pkwy #100
Portland, OR 97224
800.275.4899

Fax 503.612.2383

cui.com

techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CUI Inc.:](#)

[PCN1-S12-D12-M](#) [PCN1-S5-S5-M](#) [PCN1-S5-D15-M](#) [PCN1-S5-D5-M](#) [PCN1-S12-D15-M](#) [PCN1-S12-S15-M](#) [PCN1-S12-S5-M](#) [PCN1-S5-S15-M](#) [PCN1-S5-S12-M](#) [PCN1-S12-D5-M](#) [PCN1-S12-S12-M](#) [PCN1-S5-D12-M](#) [PCN1-S12-D12-M-TR](#) [PCN1-S5-S15-M-TR](#) [PCN1-S5-S5-M-TR](#) [PCN1-S12-S12-M-TR](#) [PCN1-S5-D12-M-TR](#) [PCN1-S12-S5-M-TR](#) [PCN1-S12-D15-M-TR](#) [PCN1-S12-D5-M-TR](#) [PCN1-S5-D15-M-TR](#) [PCN1-S5-S12-M-TR](#) [PCN1-S5-D5-M-TR](#) [PCN1-S12-S15-M-TR](#)