

**SERIES:** PDRB-30 | **DESCRIPTION:** AC-DC DIN RAIL POWER SUPPLY

**FEATURES**

- universal input range (85 ~ 264 Vac)
- IEC/EN/UL 62368 certified
- designed to meet 61558 system requirements
- over Voltage Category (OVC) III design
- over voltage, over current, and short circuit protections
- 4kVac isolation input to output
- withstand up to 300 Vac input surge events
- Class B emissions



| MODEL      | output <sup>1</sup><br>voltage |                | output<br>current<br>max<br>(A) | output<br>power<br>max<br>(W) | ripple<br>and noise <sup>2</sup><br>max<br>(mVp-p) | efficiency <sup>3</sup><br>typ<br>(%) |
|------------|--------------------------------|----------------|---------------------------------|-------------------------------|----------------------------------------------------|---------------------------------------|
|            | (Vdc)                          | range<br>(Vdc) |                                 |                               |                                                    |                                       |
| PDRB-30-5  | 5                              | 4.9 ~ 5.5      | 3.0                             | 15                            | 80                                                 | 82                                    |
| PDRB-30-12 | 12                             | 10.8 ~ 13.8    | 2.0                             | 24                            | 120                                                | 88                                    |
| PDRB-30-15 | 15                             | 13.5 ~ 18.0    | 2.0                             | 30                            | 120                                                | 89                                    |
| PDRB-30-24 | 24                             | 21.6 ~ 29.0    | 1.5                             | 36                            | 150                                                | 88                                    |
| PDRB-30-48 | 48                             | 43.2 ~ 55.2    | 0.75                            | 36                            | 240                                                | 90                                    |

Notes:

1. Output adjustable via built-in trimpot. The actual adjustment range may extend beyond the values listed and care should be taken to ensure the output voltage and output power do not exceed stated limits.
2. At full load, nominal input, 20 MHz bandwidth oscilloscope.
3. At 230 Vac input.

**PART NUMBER KEY**


## INPUT

| parameter       | conditions/description | min | typ | max  | units |
|-----------------|------------------------|-----|-----|------|-------|
| input voltage   | ac input               | 85  |     | 264  | Vac   |
|                 | dc input               | 120 |     | 370  | Vdc   |
| frequency       |                        | 47  |     | 63   | Hz    |
| current         | at 115 Vac             |     |     | 0.9  | A     |
|                 | at 230 Vac             |     |     | 0.5  | A     |
| inrush current  | at 115 Vac             |     | 25  |      | A     |
|                 | at 230 Vac             |     | 45  |      | A     |
| leakage current | at 264 Vac             |     |     | 0.25 | mA    |

## OUTPUT

| parameter                  | conditions/description              | min | typ   | max    | units |
|----------------------------|-------------------------------------|-----|-------|--------|-------|
| capacitive load            | 5 Vdc output model                  |     |       | 12,000 | μF    |
|                            | 12 Vdc output model                 |     |       | 6,000  | μF    |
|                            | 15 Vdc output model                 |     |       | 5,000  | μF    |
|                            | 24 Vdc output model                 |     |       | 1,400  | μF    |
|                            | 48 Vdc output model                 |     |       | 600    | μF    |
| initial set point accuracy | 0% ~ 100% load                      |     | ±2    |        | %     |
| line regulation            | at rated load                       |     | ±0.5  |        | %     |
| load regulation            | at 230 Vac                          |     | ±1.5  |        | %     |
| start-up time              |                                     |     |       | 3      | s     |
| hold-up time               | at 115 Vac                          |     | 12    |        | ms    |
|                            | at 230 Vac                          |     | 60    |        | ms    |
| switching frequency        |                                     |     | 65    |        | kHz   |
| temperature coefficient    |                                     |     | ±0.02 |        | %/°C  |
| no load power consumption  | at 230 Vac                          |     |       |        |       |
|                            | 5 Vdc, 12 Vdc, 15 Vdc output models |     |       | 0.3    | W     |
|                            | 24 Vdc output model                 |     |       | 0.8    | W     |
|                            | 48 Vdc output model                 |     |       | 0.4    | W     |

## PROTECTIONS

| parameter                | conditions/description            | min | typ | max | units |
|--------------------------|-----------------------------------|-----|-----|-----|-------|
| over voltage protection  | clamp or hiccup                   |     |     |     |       |
|                          | 5 Vdc output model                |     |     | 7.5 | Vdc   |
|                          | 12 Vdc output model               |     |     | 16  | Vdc   |
|                          | 15 Vdc output model               |     |     | 20  | Vdc   |
|                          | 24 Vdc output model               |     |     | 36  | Vdc   |
|                          | 48 Vdc output model               |     |     | 60  | Vdc   |
| over current protection  | auto recovery                     | 120 |     |     | %     |
| short circuit protection | continuous, auto recovery, hiccup |     |     |     |       |

## SAFETY & COMPLIANCE

| parameter                     | conditions/description                                                          | min     | typ | max | units |
|-------------------------------|---------------------------------------------------------------------------------|---------|-----|-----|-------|
| isolation voltage             | input to output 5 mA for 1 minute                                               | 4,000   |     |     | Vac   |
| safety approvals              | certified to 62368: IEC, EN, UL/cUL                                             |         |     |     |       |
| safety class                  | Class II                                                                        |         |     |     |       |
| conducted emissions           | CISPR32/EN55032 CLASS B                                                         |         |     |     |       |
| radiated emissions            | CISPR32/EN55032 CLASS B                                                         |         |     |     |       |
| ESD                           | IEC/EN61000-4-2 Contact $\pm 6\text{KV}$ /Air $\pm 8\text{KV}$ perf. Criteria A |         |     |     |       |
| radiated immunity             | IEC/EN61000-4-3 10V/m perf. Criteria A                                          |         |     |     |       |
| EFT/burst                     | IEC/EN61000-4-4 $\pm 2\text{KV}$ perf. Criteria A                               |         |     |     |       |
| surge                         | IEC/EN61000-4-5 line to line $\pm 2\text{KV}$ perf. Criteria A                  |         |     |     |       |
| conducted immunity            | IEC/EN61000-4-6 10Vr.m.s perf. Criteria A                                       |         |     |     |       |
| voltage dips and interruption | IEC/EN61000-4-11 0%, 70% perf. Criteria A                                       |         |     |     |       |
| MTBF                          | as per MIL-HDBK-217F at 25°C                                                    | 300,000 |     |     | hours |
| RoHS                          | yes                                                                             |         |     |     |       |

## ENVIRONMENTAL

| parameter             | conditions/description | min | typ | max   | units |
|-----------------------|------------------------|-----|-----|-------|-------|
| operating temperature | see derating curve     | -40 |     | 70    | °C    |
| storage temperature   |                        | -40 |     | 85    | °C    |
| storage humidity      | non-condensing         | 0   |     | 95    | %     |
| altitude              |                        |     |     | 2,000 | m     |



## MECHANICAL

| parameter  | conditions/description            | min | typ | max | units |
|------------|-----------------------------------|-----|-----|-----|-------|
| dimensions | 92.66 x 35.00 x 58.00             |     |     |     | mm    |
| material   | plastic, heat-resistant (UL94V-0) |     |     |     |       |
| weight     |                                   |     | 115 |     | g     |
| cooling    | natural convection                |     |     |     |       |


## MECHANICAL DRAWING

units: mm [inch]  
 ADJ: built-in trimpot  
 wire range: 24-12 AWG  
 tightening torque: Max 0.4 N·m  
 mounting rail: TS35  
 general tolerances:  $\pm 1.0$  [ $\pm 0.039$ ]


| TERMINAL CONNECTIONS |          |
|----------------------|----------|
| TERMINAL             | Function |
| 1                    | AC (N)   |
| 2                    | AC (L)   |
| 3                    | -Vo      |
| 4                    | +Vo      |



## DERATING CURVE



## EFFICIENCY CURVES



## REVISION HISTORY

| rev. | description                                                   | date       |
|------|---------------------------------------------------------------|------------|
| 1.0  | initial release                                               | 11/25/2020 |
| 1.01 | correction to 24 Vdc efficiency and no-load power consumption | 06/23/2021 |
| 1.02 | derating curves updated                                       | 02/22/2022 |
| 1.03 | UKCA mark added                                               | 05/26/2022 |

The revision history provided is for informational purposes only and is believed to be accurate.



**Headquarters**  
20050 SW 112th Ave.  
Tualatin, OR 97062  
**800.275.4899**

Fax 503.612.2383  
**cui.com**  
techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CUI Inc.:](#)

[PDRB-30-12](#) [PDRB-30-15](#) [PDRB-30-24](#) [PDRB-30-48](#) [PDRB-30-5](#)