

BB-232CAM

BB-232CAM3

RS-232 Modem Cable

DB9 Female to DB25 Male



Features

- Converts 25-pin serial to 9-pin AT serial
- Fully molded back shell with strain relief for added protection
- 26 AWG stranded conductors for flexibility
- 9-wire, all pins terminated
- PC-AT modem cable

Introduction

Make easy connections between your serial equipment with this reliable, quality built, D-subminiature serial modem cable.

Signal Pinouts

DB9 Female	DB9 Male
1	8
2	3
3	2
4	20
5	7
6	6
7	4
8	5
9	22
G	G


Ordering Information

Model No.	Connector 1	Connector 2	Length	Color
BB-232CAM	DB9 Female	DB25 Male	1.8m (6 ft)	Beige
BB-232CAM3	DB9 Female	DB25 Male	0.9m (3 ft)	Beige

Modem Cable - Straight Conversion DB9 to DB25

		DB9 DTE to DCE		DB25	
RS-232 Signal Names	Pin#	Connections	Pin#		
Carrier Detector (DCD)	CD #1		#1	FGND	
Receive Data (Rx)	RD #2		#2	TD	
Transmit Data (Tx)	TD #3		#3	RD	
Data Terminal Ready	DTR #4		#4	RTS	
Signal Ground/Common (SG)	GND #5		#5	CTS	
Data Set Ready	DSR #6		#6	DSR	
Request to Send	RTS #7		#7	GND	
Clear to Send	CTS #8		#8	CD	
Ring Indicator	RI #9		#20	DTR	
Soldered to DB9 Metal - Shield	FGND		#22	RI	

Product Drawing



- ① D-subminiature 9-pin female with gold plating contacts
- ② Beige-color molded PVC hood, fully shielded with aluminum foil
- ③ D-subminiature 25-pin male with gold plating contacts
- ④ Beige-color molded PVC hood, fully shielded with aluminum foil
- ⑤ 4/40 molded thumbscrew, beige-color
- ⑥ 28 AWG, 9 conductors + drain wire, single-shielded with aluminum foil, beige-color outer PVC jacket

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[BB-232CAM](#)