

SERIES: PQS075-S | **DESCRIPTION:** DC-DC CONVERTER


FEATURES

- 0.75W isolated output
- single regulated output
- high efficiency up to 74%
- continuous short circuit protection
- 1500 Vdc isolation
- EN 62368 approved
- meets UL 62368 standards


MODEL

	input voltage		output voltage	output current		output power	ripple & noise ¹	efficiency
	typ (Vdc)	range (Vdc)	(Vdc)	min (mA)	max (mA)	max (W)	max (mVp-p)	typ (%)
PQS075-S5-S3-S	5	4.75~5.25	3.3	20	200	0.66	75	68
PQS075-S5-S5-S	5	4.75~5.25	5.0	15	150	0.75	75	72
PQS075-S5-S9-S	5	4.75~5.25	9.0	9	83	0.75	75	72
PQS075-S5-S12-S	5	4.75~5.25	12.0	7	62	0.74	75	73
PQS075-S5-S15-S	5	4.75~5.25	15.0	5	50	0.75	75	74
PQS075-S12-S3-S	12	11.4~12.6	3.3	20	200	0.75	100	68
PQS075-S12-S5-S	12	11.4~12.6	5	15	150	0.75	100	72
PQS075-S12-S12-S	12	11.4~12.6	12	7	62	0.75	100	73
PQS075-S12-S15-S	12	11.4~12.6	15	5	50	0.75	150	74
PQS075-S24-S3-S	24	22.8~25.2	3.3	20	200	0.75	100	68
PQS075-S24-S5-S	24	22.8~25.2	5	15	150	0.75	100	72
PQS075-S24-S12-S	24	22.8~25.2	12	7	62	0.75	100	73
PQS075-S24-S15-S	24	22.8~25.2	15	5	50	0.75	150	74

Notes: 1. Ripple and noise are measured at 20 MHz BW by "parallel cable" method.

PART NUMBER KEY


INPUT

parameter	conditions/description		min	typ	max	units
operating input voltage			4.75	5.0	5.25	Vdc
			11.4	12	12.6	Vdc
			22.8	24	25.2	Vdc
current	5 Vdc input full load / no load	3.3 Vdc, 5 Vdc output		209/5	221/10	mA
		9 Vdc, 12 Vdc output		208/12	221/20	mA
		15 Vdc output		202/18	215/30	mA
	12 Vdc input full load / no load	3.3 Vdc output		92/8	98/-	mA
		5 Vdc output		87/8	92/-	mA
		12 Vdc output		86/8	91/-	mA
		15 Vdc output		85/8	90/-	mA
	24 Vdc input full load / no load	3.3 Vdc output		46/8	51/-	mA
		5 Vdc output		44/8	48/-	mA
		12 Vdc output		43/8	47/-	mA
		15 Vdc output		43/8	46-	mA
filter	capacitance filter					

OUTPUT

parameter	conditions/description		min	typ	max	units
maximum capacitive load	3.3 Vdc output				2,400	μF
	5 Vdc output				2,400	μF
	9 Vdc output				1,000	μF
	12 Vdc output				560	μF
	15 Vdc output				560	μF
voltage accuracy					±3	%
line regulation					±0.25	%
load regulation	10%~100% load					
	3.3 Vdc output other outputs				±3 ±2	% %
switching frequency	at full load, nominal input voltage			270		kHz
temperature coefficient	at full load			±0.02		%/°C

PROTECTIONS

parameter	conditions/description	min	typ	max	units
short circuit protection	continuous, auto recovery				

SAFETY AND COMPLIANCE

parameter	conditions/description	min	typ	max	units
isolation voltage	input to output, for 1 minute with 1 mA max	1,500			Vdc
isolation resistance	input to output at 500 Vdc	1,000			MΩ
isolation capacitance	input to output, 100 kHz / 0.1 V		20		pF
safety approvals	EN/IEC 62368				
EMI/EMC	CISPR32/EN 55032 Class B (see recommended circuit)				
ESD	IEC/EN 61000-4-2 Air ±8kV, Contact ±4kV, perf. Criteria B				
MTBF	as per MIL-HDBK-217F, 25°C	3,500			K hours
RoHS	yes				

ENVIRONMENTAL

parameter	conditions/description	min	typ	max	units
operating temperature	see derating curve	-40		85	°C
storage temperature		-55		125	°C
storage humidity	non-condensing	0		95	%
vibration	10-155Hz, 5G, 30 min. along X, Y and Z				

MECHANICAL


parameter	conditions/description	min	typ	max	units
dimensions	11.60 x 6.00 x 10.16 [0.457 x 0.236 x 0.4 inch]				mm
case material	black plastic				
weight			1.3		g

MECHANICAL DRAWING

units: mm [inch]


pin section tolerance: $\pm 0.10 [\pm 0.004]$ general tolerance: $\pm 0.25 [\pm 0.010]$

PIN Out	
PIN	Function
1	GND
2	Vin
3	0V
4	+Vo



DERATING CURVES

TEMPERATURE DERATING CURVE



APPLICATION CIRCUIT

Figure 1




Table 1

Vin (Vdc)	Cin (μF / V)	Vo (Vdc)	Cout (μF / V)
5	4.7 μF	3.3/5	10 μF
--	--	9/12	2.2
--	--	15	1
12	2.2 μF / 25	3.3/5	10 μF /16V
24	1 μF /50V	12	2.2 μF /25V
--	--	15	1 μF /25V

EMC RECOMMENDED CIRCUIT

Figure 2




Table 2

Input voltage 5 Vdc	Output voltage (Vdc)		3.3/5/9	12/15
	EMI	C1/C2	4.7μF/25V	
		CY	--	1nF/4KVdc Vishay HGZ10102MBP TDK CD45-E2GA102M-GKA
		C3	Refer to the Cout in table 1	
		LDM	6.8μH	
Input voltage 12, 24 Vdc		C1/C2	4.7μF/50V	
	CY	270pF/2kV		
	C3	Refer to the Cout in table 1		
	LDM	6.8μH		

REVISION HISTORY

rev.	description	date
1.0	initial release	08/17/2020
1.01	mechanical tolerances updated	09/22/2020
1.02	derating curve and circuits updated	06/29/2021
1.03	datasheet updated	09/08/2021

The revision history provided is for informational purposes only and is believed to be accurate.



Headquarters
20050 SW 112th Ave.
Tualatin, OR 97062
800.275.4899

Fax 503.612.2383
cui.com
techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CUI Inc.:](#)

[PQS075-S12-S12-S](#) [PQS075-S12-S15-S](#) [PQS075-S12-S3-S](#) [PQS075-S12-S5-S](#) [PQS075-S24-S12-S](#) [PQS075-S24-S15-S](#) [PQS075-S24-S3-S](#) [PQS075-S24-S5-S](#)