


**SERIES: SDI30-U | DESCRIPTION: AC-DC POWER SUPPLY**
**FEATURES**

- up to 30 W continuous power
- DoE Level VI, CoC Tier 2 efficiency
- universal input voltage range
- compact size
- no load power consumption < 0.075 W
- over voltage and short circuit protections
- UL/cUL and PSE safety approvals
- custom designs available



| MODEL      | output voltage<br>(Vdc) | output current<br>max<br>(A) | output power<br>max<br>(W) | ripple and noise <sup>1</sup><br>max<br>(mVp-p) | efficiency level <sup>2</sup> |
|------------|-------------------------|------------------------------|----------------------------|-------------------------------------------------|-------------------------------|
| SDI30-12-U | 12                      | 2.5                          | 30                         | 200                                             | VI                            |
| SDI30-15-U | 15                      | 2                            | 30                         | 200                                             | VI                            |
| SDI30-19-U | 19                      | 1.6                          | 30                         | 300                                             | VI                            |
| SDI30-24-U | 24                      | 1.25                         | 30                         | 300                                             | VI                            |

Notes: 1. Measured at 100~240 Vac input, full load, 20 MHz bandwidth oscilloscope, output terminated with a 10  $\mu$ F aluminum electrolytic and 0.1  $\mu$ F ceramic capacitor.  
 2. CoC Tier 2 compliant

**PART NUMBER KEY**


## INPUT

| parameter                 | conditions/description | min | typ | max   | units |
|---------------------------|------------------------|-----|-----|-------|-------|
| voltage                   |                        | 90  |     | 264   | Vac   |
| frequency                 |                        | 47  |     | 63    | Hz    |
| current                   |                        |     |     | 1     | A     |
| leakage current           |                        |     |     | 3.5   | mA    |
| no load power consumption |                        |     |     | 0.075 | W     |

## OUTPUT

| parameter       | conditions/description | min | typ | max | units |
|-----------------|------------------------|-----|-----|-----|-------|
| load regulation |                        |     | ±5  |     | %     |

## PROTECTIONS

| parameter                | conditions/description          | min | typ | max | units |
|--------------------------|---------------------------------|-----|-----|-----|-------|
| over voltage protection  | 12 Vdc output model             |     |     | 16  | Vdc   |
|                          | 15 Vdc output model             |     |     | 22  | Vdc   |
|                          | 19 Vdc output model             |     |     | 27  | Vdc   |
|                          | 24 Vdc output model             |     |     | 32  | Vdc   |
| over current protection  | 12 Vdc output model             |     |     | 4   | A     |
|                          | 15 Vdc output model             |     |     | 4   | A     |
|                          | 19 Vdc output model             |     |     | 4   | A     |
|                          | 24 Vdc output model             |     |     | 2.8 | A     |
| short circuit protection | output shut down, auto recovery |     |     |     |       |

## SAFETY & COMPLIANCE

| parameter            | conditions/description                | min | typ            | max | units      |
|----------------------|---------------------------------------|-----|----------------|-----|------------|
| isolation voltage    | input to output at 10 mA for 1 minute |     | 1,500<br>2,121 |     | Vac<br>Vdc |
| isolation resistance | input to output at 500 Vdc            | 100 |                |     | MΩ         |
| safety approvals     | UL/cUL, PSE                           |     |                |     |            |
| EMI/EMC              | FCC Part 15B Class B                  |     |                |     |            |
| RoHS                 | 2011/65/EU                            |     |                |     |            |

## ENVIRONMENTAL


| parameter             | conditions/description | min | typ | max | units |
|-----------------------|------------------------|-----|-----|-----|-------|
| operating temperature |                        | 0   |     | 40  | °C    |
| storage temperature   |                        | -10 |     | 70  | °C    |
| operating humidity    | non-condensing         | 20  |     | 80  | %     |
| storage humidity      | non-condensing         | 10  |     | 90  | %     |

## MECHANICAL

| parameter  | conditions/description | min | typ | max | units |
|------------|------------------------|-----|-----|-----|-------|
| dimensions | 111 x 52 x 32.3        |     |     |     | mm    |
| inlet plug | IEC320/C14             |     |     |     |       |
| weight     | without AC cord        |     | 240 |     | g     |
|            | with AC cord           |     | 270 |     | g     |

## MECHANICAL DRAWING


units: mm



Note: 1. LED indicator is not present on 24 Vdc output model.

## DC CORD

units: mm



**Table 1**

| MODEL NO.  | CABLE          | CORD LENGTH   |
|------------|----------------|---------------|
| SDI30-12-U | UL2468, 16 AWG | 1,530 mm ±100 |
| SDI30-15-U | UL2468, 18 AWG | 1,530 mm ±100 |
| SDI30-19-U | UL2468, 20 AWG | 1,530 mm ±100 |
| SDI30-24-U | UL2468, 20 AWG | 1,530 mm ±100 |

## AC CORD

units: mm



**Table 2**

| AC INPUT       | CORD LENGTH       |
|----------------|-------------------|
| North America  | 1,830 mm +200/-30 |
| Europe         | 1,830 mm +200/-30 |
| United Kingdom | 1,830 mm +200/-30 |
| Australia      | 1,830 mm +200/-30 |
| China          | 1,830 mm +200/-30 |
| South Korea    | 1,830 mm ±30      |
| Brazil         | 1,830 mm ±30      |
| South Africa   | 1,830 mm ±30      |
| Japan          | 1,830 mm ±30      |

## DC PLUG TYPE PART NUMBER KEY

**XXX**

**Plug Polarity:**  
 P = Center Positive  
  
 N = Center Negative  



**Plug Code:**  
 X = Choose a code from the options below

**Plug Angle:**  
 "blank" = Straight  
 R = Right Angle


| Plug Polarity |             | Code   |                   | Dimensions (mm) |      |     | Plug Angle |       |
|---------------|-------------|--------|-------------------|-----------------|------|-----|------------|-------|
| Center Pos.   | Center Neg. | Option | Type              | A               | B    | C   | Straight   | Right |
| •             | •           | 5      | Standard          | 5.5             | 2.1  | 9.5 | •          | •     |
| •             | •           | 6      | Standard          | 5.5             | 2.5  | 9.5 | •          | •     |
| •             | •           | 7      | Standard          | 3.5             | 1.35 | 9.5 | •          | •     |
| •             | •           | 8      | Standard          | 3.8             | 1.35 | 9.5 | •          | •     |
| •             | •           | 9      | Standard          | 3.8             | 1.05 | 9.5 | •          | •     |
| •             | •           | 10     | Locking           | 5.5             | 2.1  | 9.5 | •          | N/A   |
| •             | •           | 11     | Locking           | 5.5             | 2.5  | 9.5 | •          | N/A   |
| •             | •           | 12     | EIAJ-1            | 2.35            | 0.7  | 9.5 | •          | •     |
| •             | •           | 13     | EIAJ-2            | 4.0             | 1.7  | 9.5 | •          | •     |
| •             | •           | 14     | EIAJ-3            | 4.75            | 1.7  | 9.5 | •          | •     |
| N/A           | N/A         | ST     | Stripped & Tinned |                 |      |     | N/A        | N/A   |

Note: 1. Contact CUI for additional plug options


### Standard




### EIAJ



### Locking



### Stripped & Tinned



## REVISION HISTORY

| rev. | description          | date       |
|------|----------------------|------------|
| 1.0  | initial release      | 11/15/2016 |
| 1.01 | updated datasheet    | 03/14/2018 |
| 1.02 | company logo updated | 09/30/2020 |
| 1.03 | safeties updated     | 12/09/2020 |

The revision history provided is for informational purposes only and is believed to be accurate.



**CUI INC**  
a bel group

**Headquarters**  
20050 SW 112th Ave.  
Tualatin, OR 97062  
**800.275.4899**

Fax 503.612.2383  
**cui.com**  
techsupport@cui.com

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions:

- (1) This device may not cause harmful interference, and
- (2) this device must accept any interference received, including interference that may cause undesired operation.

CUI offers a one (1) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CUI Inc.:

[SDI30-15-U-P5](#) [SDI30-12-U-P5](#) [SDI30-19-U-P6](#) [SDI30-24-U-P6](#) [SDI30-15-U-P5R](#) [SDI30-15-U-P6](#) [SDI30-19-UC-P5](#)  
[SDI30-24-UC-P5](#) [SDI30-12-U-P6](#) [SDI30-24-U-P5](#) [SDI30-12-U-P5R](#) [SDI30-19-U-P5R](#) [SDI30-15-UC-P5](#) [SDI30-12-](#)  
[UC-P5](#) [SDI30-19-U-P5](#) [SDI30-24-U-P5R](#)