


SERIES: SDI50-U | DESCRIPTION: AC-DC POWER SUPPLY
FEATURES

- DoE Level VI, CoC Tier 2 efficiency
- 50 W power
- universal input (90~264 Vac)
- compact size
- single regulated output from 9~48 Vdc
- over voltage and short circuit protections
- UL/cUL and PSE safety approvals
- custom designs available
- certified to 60950-1 and 62368-1 standards



MODEL	output voltage (Vdc)	output current max (A)	output power max (W)	ripple and noise ¹ max (mVp-p)	efficiency level ²
SDI50-9-U	9	5	45	100	VI
SDI50-12-U	12	4.2	50	120	VI
SDI50-15-U	15	3.34	50	150	VI
SDI50-18-U	18	2.78	50	180	VI
SDI50-19-U	19	2.64	50	190	VI
SDI50-24-U	24	2.1	50	240	VI
SDI50-48-U	48	1.05	50	480	VI

Notes: 1. At full load, nominal input, 20 MHz bandwidth oscilloscope, each output terminated with 0.1 μ F multilayer ceramic and 10 μ F low ESR electrolytic capacitors.
 2. CoC Tier 2 compliant

PART NUMBER KEY


INPUT

parameter	conditions/description	min	typ	max	units
voltage		90		264	Vac
frequency		47		63	Hz
current				1.2	A
inrush current	at 230 Vac, full load, 25°C, cold start			70	A
leakage current				3.5	mA
no load power consumption	at 230 Vac			0.10	W
	9 Vdc model			0.15	W
	all other models				

OUTPUT

parameter	conditions/description	min	typ	max	units
regulation			±5		%

PROTECTIONS

parameter	conditions/description	min	typ	max	units
over voltage protection	output latch off			180	%
over current protection	output shut down, auto recovery			180	%
short circuit protection	output shut down, auto recovery				

SAFETY & COMPLIANCE

parameter	conditions/description	min	typ	max	units
isolation voltage	input to output at 10 mA for 1 minute		3,000		Vac
	input to frame ground at 10 mA for 1 minute		1,500		Vac
isolation resistance	input to output at 500 Vdc	10			MΩ
	input to frame ground at 500 Vdc	10			MΩ
safety approvals	UL/cUL (60950-1, 62368-1), PSE, LPS, UKCA				
EMI/EMC	FCC Part 15B Class B, CE				
MTBF	as per Telcordia SR-332, 25°C	300,000			hours
RoHS	yes				

ENVIRONMENTAL


parameter	conditions/description	min	typ	max	units
operating temperature		0		40	°C
storage temperature		-20		80	°C
operating humidity	non-condensing	20		80	%
storage humidity	non-condensing	10		90	%

MECHANICAL

parameter	conditions/description	min	typ	max	units
dimensions	115 x 53 x 38				mm
inlet plug	IEC320/C14				
weight	without ac cord		310		g

MECHANICAL DRAWING

units: mm
tolerance: ±1.0 mm



DC CORD

units: mm




Table 1

MODEL NO.	CABLE	CORD LENGTH
SDI50-9-U	UL2468, 16 AWG	1,500 mm ±30
SDI50-12-U	UL2468, 18 AWG	1,500 mm ±30
SDI50-15-U	UL2468, 18 AWG	1,500 mm ±30
SDI50-18-U	UL2468, 18 AWG	1,500 mm ±30
SDI50-19-U	UL2468, 18 AWG	1,500 mm ±30
SDI50-24-U	UL2468, 18 AWG	1,500 mm ±30
SDI50-48-U	UL2468, 20 AWG	1,500 mm ±30

AC CORD

units: mm





Table 2

AC INPUT	CORD LENGTH
North America	1,830 mm ±30
Europe	1,830 mm ±30
United Kingdom	1,830 mm ±30
Australia	1,830 mm ±30
China	1,830 mm ±30
South Korea	1,830 mm ±50
Brazil	1,830 mm ±30
South Africa	1,830 mm ±50
Japan	1,830 mm ±30

DC PLUG TYPE PART NUMBER KEY

XXX

Plug Polarity:
 P = Center Positive

 N = Center Negative


Plug Code:
 X = Choose a code from the options below

Plug Angle:
 "blank" = Straight
 R = Right Angle


Plug Polarity		Code		Dimensions (mm)			Plug Angle	
Center Pos.	Center Neg.	Option	Type	A	B	C	Straight	Right
•	•	5	Standard	5.5	2.1	9.5	•	•
•	•	6	Standard	5.5	2.5	9.5	•	•
•	•	7	Standard	3.5	1.35	9.5	•	•
•	•	8	Standard	3.8	1.35	9.5	•	•
•	•	9	Standard	3.8	1.05	9.5	•	•
•	•	10	Locking ²	5.5	2.1	9.5	•	N/A
•	•	11	Locking ²	5.5	2.5	9.5	•	N/A
•	•	12	EIAJ-1	2.35	0.7	9.5	•	•
•	•	13	EIAJ-2	4.0	1.7	9.5	•	•
•	•	14	EIAJ-3	4.75	1.7	9.5	•	•
N/A	N/A	ST	Stripped & Tinned				N/A	N/A

Note: 1. Contact CUI for additional plug options
 2. Maximum insertion depth is 10mm


Standard




EIAJ



Locking



Stripped & Tinned



REVISION HISTORY

rev.	description	date
1.0	initial release	05/13/2015
1.01	updated datasheet	09/15/2016
1.02	added 62368-1 standard	08/31/2018
1.03	removed GS safety approval	03/02/2020
1.04	dc cord AWG updated	06/09/2020
1.05	UKCA added to specification	08/11/2021
1.06	plug polarity symbols updated	09/16/2021
1.07	dc plugs updated	05/23/2022

The revision history provided is for informational purposes only and is believed to be accurate.



Headquarters
20050 SW 112th Ave.
Tualatin, OR 97062
800.275.4899

Fax 503.612.2383
cui.com
techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CUI Inc.:](#)

[SDI50-15-U-P5R](#) [SDI50-18-U-P5](#) [SDI50-12-U-P6](#) [SDI50-9-U-P6](#) [SDI50-48-U-P5R](#) [SDI50-19-U-P6](#) [SDI50-15-U-P5](#)
[SDI50-48-UC-P5](#) [SDI50-24-U-P6](#) [SDI50-24-U-P5R](#) [SDI50-12-U-P5](#) [SDI50-24-U-P5](#) [SDI50-9-U-P5R](#) [SDI50-19-U-](#)
[P5R](#) [SDI50-9-U-P5](#) [SDI50-18-U-P6](#) [SDI50-15-U-P6](#) [SDI50-12-UC-P5](#) [SDI50-12-U-P5R](#) [SDI50-48-U-P5](#) [SDI50-24-](#)
[UC-P5](#) [SDI50-19-U-P5](#) [SDI50-18-U-P5R](#) [SDI50-48-U-P6](#) [SDI50-19-U2-P6R](#) [SDI50-12-UC-P6](#) [SDI50-18-UC-P6R](#)
[SDI50-19-UC-P6R](#) [SDI50-15-UC-P6](#) [SDI50-12-UC-P6R](#) [SDI50-48-U2-P5R](#) [SDI50-15-UC-P5R](#) [SDI50-9-UC-P5R](#)
[SDI50-48-U2-P6R](#) [SDI50-18-UC-P5R](#) [SDI50-15-U2-P6](#) [SDI50-48-UC-P6](#) [SDI50-18-U2-P6R](#) [SDI50-19-UC-P5](#)
[SDI50-15-U2-P5](#) [SDI50-15-UC-P5](#) [SDI50-9-UC-P5](#) [SDI50-18-UC-P5](#) [SDI50-18-UC-P6](#) [SDI50-24-U2-P5](#) [SDI50-18-](#)
[U2-P6](#) [SDI50-12-U2-P6R](#) [SDI50-19-UC-P5R](#) [SDI50-12-UC-P5R](#) [SDI50-19-UC-P6](#) [SDI50-24-U2-P6](#) [SDI50-9-U2-](#)
[P5R](#) [SDI50-24-UC-P5R](#) [SDI50-48-U2-P6](#) [SDI50-15-UC-P6R](#) [SDI50-15-U2-P5R](#) [SDI50-15-U2-P6R](#) [SDI50-48-UC-](#)
[P5R](#) [SDI50-9-UC-P6R](#) [SDI50-9-U2-P6R](#) [SDI50-24-U2-P6R](#) [SDI50-9-U2-P5](#) [SDI50-24-U2-P5R](#) [SDI50-24-UC-P6R](#)
[SDI50-18-U2-P5](#) [SDI50-19-U2-P6](#) [SDI50-9-UC-P6](#) [SDI50-24-UC-P6](#) [SDI50-12-U2-P5R](#) [SDI50-19-U2-P5R](#) [SDI50-](#)
[19-U2-P5](#) [SDI50-48-UC-P6R](#) [SDI50-12-U2-P6](#) [SDI50-48-U2-P5](#) [SDI50-18-U2-P5R](#) [SDI50-12-U2-P5](#) [SDI50-9-U2-P6](#)
[SDI50-48-U-P8](#)