


EWM-G110H

Embedded Multi-GPS/ GNSS + G sensor Module Half-size Mini PCIe Card

NEW



Features

- 72-Ch u-blox NEO-M8 engine (GPS, GLONASS, BeiDou, Galileo, QZSS and SBAS)
- Untethered Dead Reckoning (UDR)
- Including 3D inertial sensors
- 1.5 second TTFF for Hot Starts, Open sky code start 26 second.
- Accuracy SBAS 2.0 m CEP
- Operating temperature: -40 to +85° C

Specifications

Main Chipset	u-blox NEO-M8U
Receiver Type	72 Channels GPS/QZSS L1 C/A, GLONASS L1 L10F, BeiDou B1, SBAS L1 C/A: WAAS/EGNOS/MSAS, Galileo-ready E1B/C
Time-To-First-Fix (GPS + GLONASS)	Cold Start: 26 s Hot Start: 1.5 s Aiding Start: 2 s
Sensitivity (GPS + GLONASS)	Tracking & Navigation: -167 dBm Reacquisition: -160 dBm Cold Start: -148 dBm
Horizontal Position Accuracy	SBAS: 2.0 m
Accuracy of Time Pulse Signal	RMS: 30 ns 99%: 60 ns Time Pulse Configurable: f=0.25...10M Hz
Velocity Accuracy	0.05 m/s
Heading Accuracy	0.3 degrees
Dynamics	< 4 g
Operational Limits	Altitude: 50000 m, Velocity: 500 m/s
Operating Temperature	-40 to +85° C

Ordering Information

Part No.	Product Description
EWM-G110H01E	Industrial GPS NEO-M8U, GPS/BeiDou/Galileo/GLONASS + G sensor, Half-size Mini PCIe Card

Suggested Antenna and Cable

Part No.	Specifications
1750007991-01	GPS antenna 1575 MHz, Antenna 3 dBi, (Zenith) L1: 1575.42 MHz, B2: 1561.098 MHz, GNSS: 1602 MHz antenna 4.94 x 3.93 x 1.49, RHCP and SMA male (cm)
1750006264	Coaxial Cable, 15 cm, SMA (F) to MHF
1750006009	Coaxial Cable, 25 cm, SMA (F) to MHF

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[EWM-G110H01E](#)