


SERIES: VOF-250C

DESCRIPTION: AC-DC POWER SUPPLY

FEATURES

- universal input voltage (85 ~ 264 Vac)
- operating temperature range -40~70 °C with derating
- active power factor correction
- certified to 62368 safety standards
- suitable for safety class I or class II installations
- over voltage, over current, over temperature, and short circuit protections
- 12 V fan output
- operating altitude 5,000 m
- 300 W peak power capability



MODEL	output voltage	output current ¹	output power ¹	ripple and noise ²	efficiency ³
	(Vdc)	max (A)	max (W)	max (mVp-p)	typ (%)
VOF-250C-12	12	20.8	250	108	91
VOF-250C-15	15	16.7	250	135	91
VOF-250C-19	19	13.2	250	170	91
VOF-250C-24	24	10.4	250	210	92
VOF-250C-30	30	8.33	250	270	92
VOF-250C-36	36	6.94	250	300	93
VOF-250C-48	48	5.21	250	300	93


Notes:

1. 8 CFM forced air, 150 W max output power with natural convection.

2. At full load, nominal input, 20 MHz bandwidth oscilloscope, tip & barrel method, output terminated with 47 µF electrolytic and 0.1 µF ceramic capacitors.

3. Efficiency is measured at rated load, and nominal line.

PART NUMBER KEY



INPUT

parameter	conditions/description	min	typ	max	units
voltage		85	100~240	264	Vac
frequency		47	50~60	63	Hz
current	low line, at 100 Vac, full load		3.1		A
	high line, at 240 Vac, full load		1.3		A
inrush current	low line, at 100 Vac, full load, cold start, 25°C			20	A
	high line, at 240 Vac, full load, cold start, 25°C			40	A
leakage current	at 240 Vac, 60 Hz		0.25		mA
power factor correction	at full load	0.9		1	
no load power consumption			0.21		W

OUTPUT

parameter	conditions/description	min	typ	max	units
line regulation ⁴	at 100~120 Vac or 200~240 Vac, full load			1	%
load regulation ⁵			±3		%
start-up time	at 100~240 Vac, full load		1		s
hold-up time ⁶	at 110 Vac, full load			10	ms
temperature coefficient				±0.04	%/°C
fan output voltage ⁷			7~12		Vdc
fan output current			0.5		A

Notes:

4. Line regulation is defined by changing ±10% of input voltage from nominal line at rated load.
5. Load regulation is defined by changing ±40% of measured output load from 60% rated load.
6. Hold up time is measured from the end of the last charging pulse to the time which the main output drops down to low limit of main output at rated load and nominal line.
7. Temperature controlled fan output voltage: 7V-12V.
8. At factory, in 60% rated load condition, each output is checked to be within voltage accuracy.

PROTECTIONS

parameter	conditions/description	min	typ	max	units
over voltage protection	latching	112		132	%
over current protection	auto recovery	120		150	%
over temperature protection	auto recovery				

SAFETY & COMPLIANCE

parameter	conditions/description	min	typ	max	units
isolation voltage	input to output 10 mA max			4,000	Vac
	input to ground 10 mA max			1,500	Vac
safety approvals	certified to 62368: UL, EN, BS EN				
safety class ⁹	class I, II				
conducted emissions	EN 55011, EN55032 Class B				
radiated emissions	EN 55011, EN55032 Class B				
harmonic current	EN 61000-3-2, Class A, Class D				
ESD	IEC 61000-4-2 15 kV air discharge, 8 kV contact discharge, perf. Criteria A				
radiated immunity	IEC 61000-4-3, perf. Criteria A				
EFT/burst	IEC610000-4-4 Power line 2 kV, 5 or 100 kHz, perf. Criteria A				
surge	IEC 61000-4-5 1 kV line to neutral, 2 kV line to PE, neutral to PE, perf. Criteria A				
conducted immunity	IEC 61000-4-6 3 Vrms, 6 Vrms, perf. Criteria A				
PFMF	IEC 61000-4-8 30 A/m, 50 Hz, perf. Criteria A				
voltage dips	IEC 61000-4-11 100% reduction for 0.5 cycle at 50 Hz, perf. Criteria A				
	IEC 61000-4-11 100% reduction for 1 cycle at 50 Hz, perf. Criteria A				
	IEC 61000-4-11 30% reduction for 25/30 cycles at 50/60 Hz, perf. Criteria A				
voltage interruptions	IEC 61000-4-11, 100% reduction for 250/300 cycles at 50/60 Hz, perf. Criteria B				

SAFETY & COMPLIANCE (CONTINUED)




parameter	conditions/description	min	typ	max	units
MTBF	as per MIL-HDBK-217F at 25°C	300,000			hours
RoHS	yes				

Notes: 9. Safety Class II operation may require external EMI/EMC components.

ENVIRONMENTAL


parameter	conditions/description	min	typ	max	units
operating temperature	see derating curves	-40		70	°C
storage temperature	10~95% RH	-40		85	°C
operating humidity	non-condensing	0		95	%
storage humidity	non-condensing	0		95	%
vibration	10~500 Hz, 10 min/1 cycle, 60 min. each along X, Y, Z axes			5	g
altitude				5,000	m

DERATING CURVES




DERATING CURVES (CONTINUED)

PEAK CYCLE DIAGRAM
(natural convection)



PEAK CYCLE DIAGRAM
(8 CFM airflow)



REVISION HISTORY

rev.	description	date
1.0	initial release	07/11/2024

The revision history provided is for informational purposes only and is believed to be accurate.



CUI INC
a bel group

Headquarters

15575 SW Sequoia Pkwy #100
Portland, OR 97224
800.275.4899

Fax 503.612.2383

cui.com

techsupport@cui.com

CUI offers a two (2) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

CUI products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CUI Inc.:](#)

[VOF-250C-19](#) [VOF-250C-30](#) [VOF-250C-15](#) [VOF-250C-12](#) [VOF-250C-48](#) [VOF-250C-24](#) [VOF-250C-36](#)